



Product Change Notification / SYST-05WMIF490

Date:

06-Apr-2021

Product Category:

Linear Regulators

PCN Type:

Document Change

Notification Subject:

Data Sheet - MIC5380 Data Sheet

Affected CPNs:

[SYST-05WMIF490_Affected_CPN_04062021.pdf](#)

[SYST-05WMIF490_Affected_CPN_04062021.csv](#)

Notification Text:

SYST-05WMIF490

Microchip has released a new Product Documents for the MIC5380 Data Sheet of devices. If you are using one of these devices please read the document located at [MIC5380 Data Sheet](#).

Notification Status: Final

Description of Change: 1) Converted Micrel document MIC5380/1 to Microchip data sheet template DS20006525A. 2) Minor grammatical text changes throughout. 3) All schematic and BOM references removed as they are found in the User's Guide for these parts.

Impacts to Data Sheet: None

Reason for Change: Conversion of Micrel datasheet to Microchip datasheet conventions.

Change Implementation Status: Complete

Date Document Changes Effective: 06 Apr 2021

NOTE: Please be advised that this is a change to the document only the product has not been changed.

Markings to Distinguish Revised from Unrevised Devices: N/A

Attachments:

[MIC5380 Data Sheet](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

Terms and Conditions:

If you wish to receive Microchip PCNs via email please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to change your PCN profile, including opt out, please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.

Affected Catalog Part Numbers (CPN)

MIC5380-G4YFT-TR

MIC5380-KHYFT-TR

MIC5380-LLYFT-TR

MIC5380-M4YFT-TR

MIC5380-MGYFT-TR

MIC5380-NGYFT-TR

MIC5380-PPYFT-TR

MIC5380-SSYFT-TR

MIC5381-G4YFT-TR

MIC5381-M4YFT-TR

MIC5381-MGYFT-TR

MIC5381-PPYFT-TR

MIC5381-SSYFT-TR

High Performance Dual 150 mA LDOs

Features

- 6-Lead 1 mm x 1 mm FTQFN Package
- 2.5V to 5.5V Input Voltage Range
- 150 mA Output Current per LDO
- High Output Accuracy $\pm 1\%$ Typical
- Low Quiescent Current of 32 μA per LDO
- Stable with 0402 1 μF Ceramic Output Capacitors
- Low Dropout Voltage 155 mV at 150 mA
- Output Discharge Circuit on MIC5381
- Independent Enable Pins
- Thermal Shutdown Protection
- Current Limit Protection

Applications

- Bluetooth Headsets
- Mobile Phones
- GPS, PMP, PDAs, DSCs
- USB Thumb Drive
- Medical Handheld
- Portable Handheld Electronics

General Description


The MIC5380 and MIC5381 are advanced dual LDOs that are ideal for powering space-constrained portable devices. The MIC5380/1 provide two independently controlled, high performance 150 mA LDOs in an ultra-small 1 mm x 1 mm FTQFN package.

Ideal for battery powered applications, the MIC5380/1 offer $\pm 1\%$ typical accuracy, low dropout voltage (155 mV at 150 mA), and low ground current. The MIC5380/1 can also be put into a zero-off-mode current state, drawing virtually no current when disabled.

The MIC5380/1 offer fast transient response and high PSRR while consuming minimal operating current. When the MIC5381 is disabled, an internal resistive load is automatically applied to the output to discharge the output capacitor.


The MIC5380/1 are available with fixed output voltages in a lead-free (RoHS compliant) 6-lead 1 mm x 1 mm FTQFN package.

Package Type




MIC5380/1

Typical Application Circuit



Functional Block Diagrams



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings †

| | |
|--|--------------------|
| Supply Voltage (V_{IN}) | –0.3V to +6V |
| Enable Voltage (V_{EN1} , V_{EN2}) | –0.3V to V_{IN} |
| Power Dissipation (P_D) (Note 1) | Internally Limited |
| ESD Rating (Note 2) | 2 kV |

Operating Ratings ††

| | |
|--|-------------------|
| Supply Voltage (V_{IN}) | +2.5V to +5.5V |
| Enable Voltage (V_{EN1} , V_{EN2}) | –0.3V to V_{IN} |

† **Notice:** Stresses above those listed under “Absolute Maximum Ratings” may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

†† **Notice:** The device is not guaranteed to function outside its operating ratings.

Note 1: The maximum allowable power dissipation of any T_A (ambient temperature) is $P_{D(MAX)} = (T_{J(MAX)} - T_A)/\theta_{JA}$. Exceeding the maximum allowable power dissipation will result in excessive die temperature, and the regulator will go into thermal shutdown.

2: Devices are ESD sensitive. Handling precautions recommended. Human body model, 1.5 k Ω in series with 100 pF.

ELECTRICAL CHARACTERISTICS

Electrical Characteristics: $V_{IN} = V_{EN1} = V_{EN2} = V_{OUT} + 1V$; higher of the two regulator outputs; $I_{OUTLDO1} = I_{OUTLDO2} = 100 \mu A$; $C_{OUT1} = C_{OUT2} = 1 \mu F$; $T_J = +25^\circ C$, **bold** values valid for $-40^\circ C$ to $+125^\circ C$, unless noted. [Note 1](#)

| Parameter | Symbol | Min. | Typ. | Max. | Units | Conditions |
|--------------------------------|---|-------------|---------|------------|---------------|---|
| Output Voltage Accuracy | — | — | ± 1 | — | % | Variation from nominal V_{OUT} |
| | | –3.0 | — | 3.0 | % | Variation from nominal V_{OUT} ; $-40^\circ C$ to $+85^\circ C$ |
| Line Regulation | $\Delta V_{OUT}/(V_{OUT} \times \Delta V_{IN})$ | — | 0.02 | 0.3 | %/V | $V_{IN} = V_{OUT} + 1V$ to 5.5V, $I_{OUT} = 100 \mu A$ |
| Load Regulation | $\Delta V_{OUT}/V_{OUT}$ | — | 0.3 | 1 | % | $I_{OUT} = 100 \mu A$ to 150 mA |
| Dropout Voltage | V_{DROP} | — | 55 | 110 | mV | $I_{OUT} = 50$ mA |
| | | — | 155 | 310 | mV | $I_{OUT} = 150$ mA |
| Ground Pin Current | I_{GND} | — | 32 | 45 | μA | $V_{EN1} = \text{High}$; $V_{EN2} = \text{Low}$; $I_{OUT} = 0$ mA |
| | | — | 32 | 45 | μA | $V_{EN1} = \text{Low}$; $V_{EN2} = \text{High}$; $I_{OUT} = 0$ mA |
| | | — | 59 | 85 | μA | $V_{EN1} = V_{EN2} = \text{High}$; $I_{OUT1} = I_{OUT2} = 0$ mA |
| Ground Pin Current in Shutdown | I_{SHDN} | — | 0.05 | 1 | μA | $V_{EN1} = V_{EN2} = 0V$ |
| Ripple Rejection | PSRR | — | 60 | — | dB | $f = 1$ kHz; $C_{OUT} = 1 \mu F$ |
| Current Limit | I_{LIMIT} | 200 | 325 | 550 | mA | $V_{OUT} = 0V$ |
| Output Voltage Noise | e_N | — | 200 | — | μV_{RMS} | $C_{OUT} = 1 \mu F$, 10 Hz to 100 kHz |

Note 1: Specification for packaged product only.

MIC5380/1

ELECTRICAL CHARACTERISTICS (CONTINUED)

Electrical Characteristics: $V_{IN} = V_{EN1} = V_{EN2} = V_{OUT} + 1V$; higher of the two regulator outputs; $I_{OUTLDO1} = I_{OUTLDO2} = 100 \mu A$; $C_{OUT1} = C_{OUT2} = 1 \mu F$; $T_J = +25^\circ C$, **bold** values valid for $-40^\circ C$ to $+125^\circ C$, unless noted. [Note 1](#)

| Parameter | Symbol | Min. | Typ. | Max. | Units | Conditions |
|--------------------------------|----------|------------|------|------------|----------|--|
| Auto-Discharge NFET Resistance | R_{DS} | — | 30 | — | Ω | MIC5381 Only; $V_{EN1} = V_{EN2} = 0V$; $V_{IN} = 3.6V$ |
| Enable Inputs (EN1/EN2) | | | | | | |
| Enable Input Voltage | V_{EN} | — | — | 0.2 | V | Logic Low |
| | | 1.2 | — | — | V | Logic High |
| Enable Input Current | I_{EN} | — | 0.01 | 1 | μA | $V_{IL} \leq 0.2V$ |
| | | — | 0.01 | 1 | μA | $V_{IH} \geq 1.2V$ |
| Turn-On Time | t_{ON} | — | 50 | 125 | μs | $C_{OUT} = 1 \mu F$ |

Note 1: Specification for packaged product only.

TEMPERATURE SPECIFICATIONS

| Parameters | Sym. | Min. | Typ. | Max. | Units | Conditions |
|------------------------------------|---------------|------|------|------|--------------|--------------------|
| Temperature Ranges | | | | | | |
| Junction Temperature Range | T_J | -40 | — | +125 | $^\circ C$ | — |
| Storage Temperature Range | T_S | -65 | — | +150 | $^\circ C$ | — |
| Lead Temperature | — | — | — | +260 | $^\circ C$ | Soldering, 10 sec. |
| Package Thermal Resistances | | | | | | |
| Thermal Resistance, FTQFN 6-Ld | θ_{JA} | — | 150 | — | $^\circ C/W$ | — |

Note 1: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T_A , T_J , θ_{JA}). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum $+125^\circ C$ rating. Sustained junction temperatures above $+125^\circ C$ can impact the device reliability.

2.0 TYPICAL PERFORMANCE CURVES

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.




FIGURE 2-1: Power Supply Rejection Ratio.




FIGURE 2-4: Ground Current vs. Input Voltage.




FIGURE 2-2: Output Voltage vs. Input Voltage.




FIGURE 2-5: Ground Current vs. Output Current.




FIGURE 2-3: Output Voltage vs. Output Current.




FIGURE 2-6: Ground Current vs. Temperature.




FIGURE 2-7: Dropout Voltage vs. Output Current.




FIGURE 2-10: Enable Voltage vs. Input Voltage.




FIGURE 2-8: Dropout Voltage vs. Temperature.




FIGURE 2-11: Output Noise Spectral Density.




FIGURE 2-9: Current Limit vs. Input Voltage.




FIGURE 2-12: Turn-On Time.




FIGURE 2-13: Line Transient.




FIGURE 2-15: Load Transient.




FIGURE 2-14: Load Transient.




FIGURE 2-16: Turn-Off Time MIC5381 (Auto-Discharge).

MIC5380/1

3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in [Table 3-1](#).

TABLE 3-1: PIN FUNCTION TABLE

| Pin Number | Pin Name | Description |
|------------|----------|---|
| 1 | VOUT1 | Regulator Output – LDO1. |
| 2 | VOUT2 | Regulator Output – LDO2. |
| 3 | EN2 | Enable Input (regulator 2). Active-High Input. Logic High = On; Logic Low = Off; Do not leave floating. |
| 4 | EN1 | Enable Input (regulator 1). Active-High Input. Logic High = On; Logic Low = Off; Do not leave floating. |
| 5 | GND | Ground. |
| 6 | VIN | Supply Input. |

4.0 APPLICATION INFORMATION

MIC5380/1 is a dual 150 mA LDO in a small 1 mm x 1 mm FTQFN package. The MIC5381 includes an auto-discharge circuit for each of the LDO outputs that is activated when the output is disabled. The MIC5380/1 regulator is fully protected from damage due to fault conditions through linear current limiting and thermal shutdown.

4.1 Input Capacitor

The MIC5380/1 is a high-performance, high bandwidth device. An input capacitor of 1 μ F capacitor is required from the input-to-ground to provide stability. Low-ESR ceramic capacitors provide optimal performance at a minimum of space. Additional high-frequency capacitors, such as small-valued NPO dielectric-type capacitors, help filter out high-frequency noise and are good practice in any RF-based circuit. X5R or X7R dielectrics are recommended for the input capacitor. Y5V dielectrics lose most of their capacitance over temperature and are therefore, not recommended.

4.2 Output Capacitor

The MIC5380/1 requires an output capacitor of 1 μ F or greater to maintain stability. The design is optimized for use with low-ESR ceramic chip capacitors. High ESR capacitors may cause high frequency oscillation. The output capacitor can be increased, but performance has been optimized for a 1 μ F ceramic output capacitor and does not improve significantly with larger capacitance.

X7R/X5R dielectric-type ceramic capacitors are recommended because of their temperature performance. X7R-type capacitors change capacitance by 15% over their operating temperature range and are the most stable type of ceramic capacitors. Z5U and Y5V dielectric capacitors change value by as much as 50% and 60%, respectively, over their operating temperature ranges. To use a ceramic chip capacitor with Y5V dielectric, the value must be much higher than an X7R ceramic capacitor to ensure the same minimum capacitance over the equivalent operating temperature range.

4.3 No Load Stability

Unlike many other voltage regulators, the MIC5380/1 will remain stable and in regulation with no load. This is especially important in CMOS RAM keep-alive applications.

4.4 Enable/Shutdown

The MIC5380/1 comes with two active-high enable pins that allow each regulator to be disabled independently. Forcing the enable pin low disables the regulator and sends it into a “zero” off-mode-current state. In this state, current consumed by the regulator goes nearly to zero. When disabled the MIC5381 switches a 30 Ω (typical) load on the regulator output to discharge the external capacitor.

Forcing the enable pin high enables the output voltage. The active-high enable pin uses CMOS technology and the enable pin cannot be left floating; a floating enable pin may cause an indeterminate state on the output.

4.5 Thermal Considerations

The MIC5380/1 is designed to provide 150 mA of continuous current for both outputs in a very small package. Maximum ambient operating temperature can be calculated based upon the output current and the voltage drop across the part. For example, if the input voltage is 3.6V, and the output voltage 3.0V for V_{OUT1} , 3.0V for V_{OUT2} and output current equals 150 mA, then the actual power dissipation of the regulator circuit can be calculated using the equation:

EQUATION 4-1:

$$P_D = (V_{IN} - V_{OUT1})I_{OUT1} + (V_{IN} - V_{OUT2})I_{OUT2} + V_{IN}I_{GND}$$

Because this device is CMOS and the ground current is typically <100 μ A over the load range, the power dissipation contributed by the ground current is <1% and can be ignored for this calculation.

EQUATION 4-2:

$$P_D = (3.6V - 3.0V) \times 150mA + (3.6V - 3.0V) \times 150mA = 0.18W$$

To determine the maximum ambient operating temperature of the package, use the junction-to-ambient thermal resistance of the device and the following basic equation:

EQUATION 4-3:

$$P_{D(MAX)} = \frac{T_{J(MAX)} - T_A}{\theta_{JA}}$$

Where:

$T_{J(MAX)} = 125^{\circ}\text{C}$

θ_{JA} = Thermal resistance of 150°C/W .

Substituting P_D for $P_{D(MAX)}$ and solving for the ambient operating temperature will give the maximum operating conditions for the regulator circuit. The junction-to-ambient thermal resistance for the minimum footprint is 150°C/W .

The maximum power dissipation must not be exceeded for proper operation.

For example, when operating the MIC5380-PPYFT at an input voltage of 3.6V and 150 mA loads at each output with a minimum footprint layout, the maximum ambient operating temperature T_A can be determined as follows:

EQUATION 4-4:

$$0.18\text{ W} = (125^{\circ}\text{C} - T_A) / (150^{\circ}\text{C/W})$$


$$T_A = 98^{\circ}\text{C}$$

Therefore, a 3.0V/3.0V application, with 150 mA at each output current, can accept an ambient operating temperature of 98°C in a 1 mm x 1 mm FTQFN package. For a full discussion of heat sinking and thermal effects on voltage regulators, refer to the "Regulator Thermals" section of Microchip's [Designing with Low-Dropout Voltage Regulators handbook](#).


5.0 PACKAGING INFORMATION

5.1 Package Marking Information

6-Lead FTQFN*



Example



| | | |
|----------------|--|--|
| Legend: | XX...X | Product code or customer-specific information |
| | Y | Year code (last digit of calendar year) |
| | YY | Year code (last 2 digits of calendar year) |
| | WW | Week code (week of January 1 is week '01') |
| | NNN | Alphanumeric traceability code |
| | (e3) | Pb-free JEDEC® designator for Matte Tin (Sn) |
| | * | This package is Pb-free. The Pb-free JEDEC designator ((e3)) can be found on the outer packaging for this package. |
| | •, ▲, ▼ | Pin one index is identified by a dot, delta up, or delta down (triangle mark). |
| Note: | In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo. | |
| | Underbar (_) and/or Overbar (¯) symbol may not be to scale. | |

TABLE 5-1: MARKING CODES

| Part Number | Marking Code | Voltage 1 | Voltage 2 | Auto-Discharge |
|---------------|--------------|-----------|-----------|----------------|
| MIC5380-SSYFT | S2 | 3.3V | 3.3V | No |
| MIC5380-PPYFT | 2P | 3.0V | 3.0V | No |
| MIC5380-NGYFT | NG | 2.85V | 1.8V | No |
| MIC5380-MGYFT | GM | 2.8V | 1.8V | No |
| MIC5380-M4YFT | 4M | 2.8V | 1.2V | No |
| MIC5380-LLYFT | 2L | 2.7V | 2.7V | No |
| MIC5380-KHYFT | KH | 2.6V | 2.0V | No |
| MIC5380-G4YFT | 4G | 1.8V | 1.2V | No |
| MIC5381-SSYFT | MK | 3.3V | 3.3V | Yes |
| MIC5381-PPYFT | MF | 3.0V | 3.0V | Yes |
| MIC5381-MGYFT | MG | 2.8V | 1.8V | Yes |
| MIC5381-M4YFT | M4 | 2.8V | 1.2V | Yes |
| MIC5381-G4YFT | G4 | 1.8V | 1.2V | Yes |


MIC5380/1

6-Lead 1 mm x 1 mm FTQFN Package Outline & Recommended Land Pattern

TITLE

6 LEAD FTQFN 1.0 x1.0 mm PACKAGE (Flip Chip) OUTLINE & RECOMMENDED LAND PATTERN

| DRAWING # | FTQFN1010-6LD-PL-1 | UNIT | MM |
|------------|--------------------|-------------|--------|
| LEAD FRAME | NiPdAu | LEAD FINISH | NiPdAu |




TOP VIEW

NOTE: 1, 2, 3

BOTTOM VIEW

NOTE: 1, 2, 3



END VIEW

NOTE: 1, 2, 3

NOTE:


1. MAX PACKAGE WARPAGE IS 0.05 MM
2. MAX ALLOWABLE BURR IS 0.076MM IN ALL DIRECTIONS
3. PIN #1 IS ON TOP WILL BE LASER MARKED
4. GREEN RECTANGLES (SHADED AREA) REPRESENT SOLDER STENCIL OPENING ON EXPOSED METAL TRACE

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>.


POD-Land Pattern drawing #FTQFN1010-6LD-PL-1

RECOMMENDED LAND PATTERN


NOTE: 4



STACKED-UP



EXPOSED METAL TRACE



SOLDER STENCIL OPENING

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>.

NOTES:

APPENDIX A: REVISION HISTORY

Revision A (April 2021)

- Converted Micrel document MIC5380/1 to Microchip data sheet template DS20006525A.
- Minor grammatical text changes throughout.
- All schematic and BOM references removed as they are found in the User's Guide for these parts.

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

| Device | -X | X | XX | -XX |
|------------------------------------|--|--|---------|------------|
| Part No. | Output Voltages | Junction Temp. Range | Package | Media Type |
| Device: | MIC5380: MIC5381: | High Performance Dual 150mA LDO High Performance Dual 150mA LDO with Auto-Discharge | | |
| Output Voltages: | SS = PP = NG = MG = M4 = LL = KH = G4 = | 3.3V/3.3V 3.0V/3.0V 2.85V/1.8V (MIC5380 Only) 2.8V/1.8V 2.8V/1.2V 2.7V/2.7V (MIC5380 Only) 2.6V/2.0V (MIC5380 Only) 1.8V/1.2V | | |
| Junction Temperature Range: | Y = | -40°C to +125°C | | |
| Package: | MT = | 6-Lead 1 mm x 1 mm FTQFN | | |
| Media Type: | TR = | 5,000/Reel | | |

Examples:

a) MIC5380-SSYFT-TR: MIC5380, 3.3V/3.3V Output Voltages, -40°C to +125°C Temperature Range, 6-Lead FTQFN, 5,000/Reel

b) MIC5381-M4YFT-TR: MIC5381, 2.8V/1.2V Output Voltages, -40°C to +125°C Temperature Range, 6-Lead FTQFN, 5,000/Reel

c) MIC5380-LLYFT-TR: MIC5380, 2.7V/2.7V Output Voltages, -40°C to +125°C Temperature Range, 6-Lead FTQFN, 5,000/Reel

d) MIC5381-G4YFT-TR: MIC5381, 1.8V/1.2V Output Voltages, -40°C to +125°C Temperature Range, 6-Lead FTQFN, 5,000/Reel

e) MIC5381-MGYFT-TR: MIC5381, 2.8V/1.2V Output Voltages, -40°C to +125°C Temperature Range, 6-Lead FTQFN, 5,000/Reel

f) MIC5380-NGYFT-TR: MIC5380, 2.85V/1.8V Output Voltages, -40°C to +125°C Temperature Range, 6-Lead FTQFN, 5,000/Reel

Note 1: Tape and Reel identifier only appears in the catalog part number description. This identifier is used for ordering purposes and is not printed on the device package. Check with your Microchip Sales Office for package availability with the Tape and Reel option.

NOTES:

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods being used in attempts to breach the code protection features of the Microchip devices. We believe that these methods require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Attempts to breach these code protection features, most likely, cannot be accomplished without violating Microchip's intellectual property rights.
- Microchip is willing to work with any customer who is concerned about the integrity of its code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable." Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication is provided for the sole purpose of designing with and using Microchip products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUENTIAL LOSS, DAMAGE, COST OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2021, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-8007-5

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

Worldwide Sales and Service

AMERICAS

Corporate Office
2355 West Chandler Blvd.
Chandler, AZ 85224-6199
Tel: 480-792-7200
Fax: 480-792-7277
Technical Support:
<http://www.microchip.com/support>
Web Address:
www.microchip.com

Atlanta
Duluth, GA
Tel: 678-957-9614
Fax: 678-957-1455

Austin, TX
Tel: 512-257-3370

Boston
Westborough, MA
Tel: 774-760-0087
Fax: 774-760-0088

Chicago
Itasca, IL
Tel: 630-285-0071
Fax: 630-285-0075

Dallas
Addison, TX
Tel: 972-818-7423
Fax: 972-818-2924

Detroit
Novi, MI
Tel: 248-848-4000

Houston, TX
Tel: 281-894-5983

Indianapolis
Noblesville, IN
Tel: 317-773-8323
Fax: 317-773-5453
Tel: 317-536-2380

Los Angeles
Mission Viejo, CA
Tel: 949-462-9523
Fax: 949-462-9608
Tel: 951-273-7800

Raleigh, NC
Tel: 919-844-7510

New York, NY
Tel: 631-435-6000

San Jose, CA
Tel: 408-735-9110
Tel: 408-436-4270

Canada - Toronto
Tel: 905-695-1980
Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney
Tel: 61-2-9868-6733

China - Beijing
Tel: 86-10-8569-7000

China - Chengdu
Tel: 86-28-8665-5511

China - Chongqing
Tel: 86-23-8980-9588

China - Dongguan
Tel: 86-769-8702-9880

China - Guangzhou
Tel: 86-20-8755-8029

China - Hangzhou
Tel: 86-571-8792-8115

China - Hong Kong SAR
Tel: 852-2943-5100

China - Nanjing
Tel: 86-25-8473-2460

China - Qingdao
Tel: 86-532-8502-7355

China - Shanghai
Tel: 86-21-3326-8000

China - Shenyang
Tel: 86-24-2334-2829

China - Shenzhen
Tel: 86-755-8864-2200

China - Suzhou
Tel: 86-186-6233-1526

China - Wuhan
Tel: 86-27-5980-5300

China - Xian
Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

China - Zhuhai
Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore
Tel: 91-80-3090-4444

India - New Delhi
Tel: 91-11-4160-8631

India - Pune
Tel: 91-20-4121-0141

Japan - Osaka
Tel: 81-6-6152-7160

Japan - Tokyo
Tel: 81-3-6880-3770

Korea - Daegu
Tel: 82-53-744-4301

Korea - Seoul
Tel: 82-2-554-7200

Malaysia - Kuala Lumpur
Tel: 60-3-7651-7906

Malaysia - Penang
Tel: 60-4-227-8870

Philippines - Manila
Tel: 63-2-634-9065

Singapore
Tel: 65-6334-8870

Taiwan - Hsin Chu
Tel: 886-3-577-8366

Taiwan - Kaohsiung
Tel: 886-7-213-7830

Taiwan - Taipei
Tel: 886-2-2508-8600

Thailand - Bangkok
Tel: 66-2-694-1351

Vietnam - Ho Chi Minh
Tel: 84-28-5448-2100

EUROPE

Austria - Wels
Tel: 43-7242-2244-39
Fax: 43-7242-2244-393

Denmark - Copenhagen
Tel: 45-4485-5910
Fax: 45-4485-2829

Finland - Espoo
Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching
Tel: 49-8931-9700

Germany - Haan
Tel: 49-2129-3766400

Germany - Heilbronn
Tel: 49-7131-72400

Germany - Karlsruhe
Tel: 49-721-625370

Germany - Munich
Tel: 49-89-627-144-0
Fax: 49-89-627-144-44

Germany - Rosenheim
Tel: 49-8031-354-560

Israel - Ra'anana
Tel: 972-9-744-7705

Italy - Milan
Tel: 39-0331-742611
Fax: 39-0331-466781

Italy - Padova
Tel: 39-049-7625286

Netherlands - Drunen
Tel: 31-416-690399
Fax: 31-416-690340

Norway - Trondheim
Tel: 47-7288-4388

Poland - Warsaw
Tel: 48-22-3325737

Romania - Bucharest
Tel: 40-21-407-87-50

Spain - Madrid
Tel: 34-91-708-08-90
Fax: 34-91-708-08-91

Sweden - Gothenberg
Tel: 46-31-704-60-40

Sweden - Stockholm
Tel: 46-8-5090-4654

UK - Wokingham
Tel: 44-118-921-5800
Fax: 44-118-921-5820