I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

General Description

The MAX25512 is a four-channel white LED backlight driver with an integrated current-mode boost converter which operates over a switching frequency range of 400kHz to 2.2MHz and incorporates spread spectrum. Phase-shifting of the output channels is included as an option to further reduce electromagnetic interference (EMI).

The device provides up to 120mA per channel and includes a control output for an external nMOS series switch. It is capable of operating down to 3V after startup.

The MAX25512 has an I²C interface to enable flexibility of control and detailed diagnostics.

The MAX25512 is available in a compact TQFN package and operates over the temperature range -40°C to +125°C.

Applications

- Automotive Instrument Clusters
- Automotive Central Information Displays
- Automotive Head-Up Displays

Benefits and Features


- Operates Down to 3V on Battery Input After Startup
 Wide Boost Duty Cycle to Support Low Input Voltage
- Boost or SEPIC Current-Mode DC/DC Controller
- 400kHz to 2.2MHz Operating Frequency RangeSpread Spectrum Available
- Ability to Synchronize to an External Clock
- LED Current Sinks
 - Up to 120mA Output Current per String
 - Low OUT_ Regulation Voltage for Best Efficiency
 - Optional Phase-Shifting of Outputs
- I²C Control for Enhanced Flexibility
- 16667:1 Dimming Ratio at 200Hz
- NTC Input For LED Current Foldback at High Temperature
- Hybrid Dimming Capable
- Built-in Programmable Automatic Fading Functionality
- Detailed Diagnostic using I²C and FLTB Output
 - Shorted or Open LEDs
 - Thermal Shutdown
 - Output Undervoltage
- Compact 4x4mm TQFN Package
- AECQ100 Grade 1

Ordering Information appears at end of data sheet.



I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Simplified Block Diagram



I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

TABLE OF CONTENTS

General Description	1
Applications	1
Benefits and Features	1
Simplified Block Diagram	2
Absolute Maximum Ratings	7
Package Information	7
TQFN	7
Electrical Characteristics	7
Typical Operating Characteristics	3
Pin Configuration	5
MAX25512	5
Pin Description	3
Functional Diagrams	7
MAX25512	7
Detailed Description	3
Enable	3
Undervoltage Lockout	3
High-Voltage Operation	3
Low-Voltage Operation	3
Operating Modes	9
Disabling Individual Strings	9
Current-Mode DC-DC Controller	9
9-Bit Digital-to-Analog Converter)
LED Current Control)
Analog Dimming)
Dimming	C
Low-Dimming Mode)
Phase-Shift Dimming)
Automatic Fade-In/Fade-Out During Dimming)
Hybrid Dimming	1
Hybrid Dimming Operation	2
Hybrid Dimming Operation Modes	2
Startup Sequence	3
Stage 1	3
Stage 2	3
Stage 3	3
Boost Startup	
Oscillator Frequency/External Synchronization	1
Spread Spectrum	1

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

TABLE OF CONTENTS (CONTINUED)

Fault Protection	25
Open-LED Management and Overvoltage Protection.	25
OUT_Short-to-GND Detection	25
Shorted-LED Detection	25
Thermal Warning	26
Thermal Shutdown	26
Temperature Foldback	26
Above Temperature T1	26
Temperature Foldback Curve	27
TEMP External Circuit	27
I2C Interface	27
Slave Address	28
Register Map	29
MAX25512	29
Register Details	29
Applications Information	37
DC-DC Converter	
Power-Circuit Design	37
Boost Configuration	37
SEPIC Configuration	38
Output Capacitor Selection	39
Rectifier Diode Selection	
Feedback Compensation	39
External Disconnect MOSFET Selection	40
V _{OUT} to OUT_Bleed Resistors	40
Thermal Considerations	41
PCB Layout Considerations	41
Typical Application Circuits	42
MAX25512 Application Circuit	42
MAX25512 Application Circuit - SEPIC	43
Ordering Information	43
Revision History	44

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

LIST OF FIGURES

Figure 1. Boost Converter Operating Modes.	19
Figure 2. Hybrid Dimming Operation with HDIM[1:0]=10 (25%)	22
Figure 3. Hybrid Dimming Operation Modes	22
Figure 4. Boost Startup Waveforms	24
Figure 5. Temperature Foldback Curve	27
Figure 6. TEMP External Circuit	27

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

LIST OF TABLES

Table 1. I ² C Slave Address		28
---	--	----

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Absolute Maximum Ratings

IN, EN to GND -0.3V to +- NGATE to IN -0.3V to +- NGATE to GND -0.3V to +- OUT_ to LEDGND -0.3V to +- DRAIN to PGND -0.3V to +- V18, BSTMON to GND -0.3V to +- SDA, SCL to GND -0.3V to OUT_ to LEDGND -0.3V to +- OUT_ to LEDGND -0.3V to +-	$6V$ LEDGND to GND $-0.3V$ to $+0.3V$ $42V$ DRAIN Current $\pm 4.5A$ $40V$ OUT_ Continuous Current ± 150 mA $40V$ Continuous Power Dissipation (Multilayer Board) ($T_A = +70^{\circ}C$, $40V$ derate 24.2mW/°C above $+70^{\circ}C$.)mW to 1938mW $40V$ Operating Temperature Range $-40^{\circ}C$ to $+125^{\circ}C$ $40V$ Junction Temperature $-40^{\circ}C$ to $+150^{\circ}C$
RT, COMP, ISET, TEMP, RSDT to GND0.3V to V18+0	

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Package Information

TQFN

T2444+4C
<u>21-0139</u>
<u>90-0022</u>
48°C/W
3°C/W
36°C/W
3°C/W

For the latest package outline information and land patterns (footprints), go to <u>www.maximintegrated.com/packages</u>. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

Package thermal resistances were obtained using the method described in JEDEC specification JESD51-7, using a four-layer board. For detailed information on package thermal considerations, refer to <u>www.maximintegrated.com/thermal-tutorial</u>.

Electrical Characteristics

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
POWER SUPPLY						
Operating Voltage Range	V _{IN}		4.5		36	V
Operating Voltage Range After Start-up		Maximum duration 100ms	3		36	V
Supply Current	I _{IN}	No switching		1.3	1.8	mA
Shutdown Supply Current		V _{EN} = 0V, 25°C		0.1	5	μA
IN Undervoltage Lockout, Rising	V _{INUVR}		4.15	4.29	4.4	V
IN Undervoltage Lockout, Falling	V _{INUVF}		2.77	2.9	2.95	V

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Electrical Characteristics (continued)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Threshold for Low- Voltage Operation Mode, Falling	V _{LVF}		5.4	5.5	5.7	v
Threshold for Low- Voltage Operation Mode, Rising	V _{LVR}		5.55	5.72	5.85	v
V18 REGULATOR	•					
V18 Voltage			1.75	1.8	1.85	V
V18 Undervoltage Lockout, Rising	UVLOVCCR		1.6	1.65	1.69	v
V18 Undervoltage Lockout, Falling	UVLOVCCF		1.54	1.575	1.61	V
V18 Short-Circuit Current Limit	I _{SCV18}	V18 shorted to GND		50		mA
NGATE OUTPUT						
NGATE Source Current			30	50		μA
NGATE Sink Current			0.5	1		mA
NGATE Output Voltage		Above V _{IN} , 3V < V _{IN} < 33V, I _{NGATE} = 0μA	4.3	5.25	6.3	v
NGATE Output Voltage		Above V _{IN} , $3V < V_{IN} < 33V$, $I_{NGATE} = 10 \mu A$	3.8	4.6	6	
NGATE Output Voltage at High Input Voltage		Above V _{IN} , V _{IN} > 35.5V, I _{NGATE} = 1µA	-0.05		0	V
VIN OV Comparator Threshold for NGATE, Rising	V _{LDUMP_TH}		33		35.5	v
VIN OV Comparator Hysteresis for NGATE				0.7		V
NGATE Start Delay		Delay between NGATE charge-pump turning on and the boost converter starting		2	2.2	ms
RT OSCILLATOR	1					•
Switching Frequency Range	f _{SW}	Frequency dithering disabled	400		2200	kHz
Oscillator Frequency Accuracy		f _{SW} = 400kHz to 2200kHz, frequency dithering disabled	-10		10	%
Boost Converter Maximum Duty Cycle, High Frequency		1.3MHz to 2.2MHz	89	92	95	%
Boost Converter Maximum Duty Cycle, Low Frequency		fSW = 400kHz to 1.3MHz	94		98	%
Boost Minimum On- Time				60		ns

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Electrical Characteristics (continued)

PARAMETER	SYMBOL	CON	DITIONS	MIN	TYP	MAX	UNITS
Frequency Dither, High Setting		SSL = 0	SSL = 0				%
Frequency Dither, Low Setting	SS	SSL = 1	SSL = 1				%
RT Output Voltage	V _{RT}	$R_{RT} = 65k\Omega \text{ or } R_{RT}$	_Γ = 10kΩ		0.9		V
RT Out-Of-Range Lower Limit					5	6.4	kΩ
RT Out-Of-Range Upper Limit				90	111		kΩ
Sync Falling Threshold				0.77		0.84	V
Sync Frequency Duty- Cycle Range					50		%
Sync Frequency Range				400		2200	kHz
MOSFET							
DRAIN MOSFET Rds(on)		I _{DRAIN} = 1A			0.075	0.125	Ω
DRAIN Leakage Current		V _{DRAIN} = 36V, T _A :	= +25°C		0.03	1	μA
CURRENT-SENSE COMP	ARATOR						
Current-Limit Threshold at Low Input Voltage	I _{LIMLV}			8.1	9.1	9.8	A
Current-Limit Threshold	ILIM			4.3	5.3	6	A
ERROR AMPLIFIER							
OUT_ Regulation High Threshold	V _{OUTH}	V _{OUT} _falling		0.825	0.85	0.875	V
OUT_ Regulation Low Threshold	V _{OUTL}	V _{OUT} _rising		0.55	0.58	0.61	v
Transconductance				410	630	890	μS
COMP Sink Current		V _{COMP} = 1V		270	380	500	μA
COMP Source Current		V _{COMP} = 1V		270	380	500	μA
LED CURRENT SINKS							
ISET Output Voltage	VISET				0.75		V
		R _{ISET} = 12.5kΩ	120mA setting	116	120	124	
OUT_ Output Current		R _{ISET} = 15kΩ	100mA setting	97	100	103	mA
		R _{ISET} = 30kΩ	50mA setting	48	50	52	
Channel-to-Channel		I _{OUT} _ = 120mA		-2		2.2	%
Matching		I _{OUT} _ = 50mA		-3.25		3.25	/0
Total OUT_ Leakage Current	IOUTLEAK	V _{OUT} = 36V, DIM shorted together	= 0V, all OUT_ are		0.01	4	μA
OUT_ Minimum Pulse Width					300		ns
OUT_ Minimum Negative Pulse Width					90		ns

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Electrical Characteristics (continued)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
OUT_ Current Rise Time		10% to 90% I _{OUT_} , (Note 2)		150		ns
OUT_ Current Fall Time		90% to 10% I _{OUT_} , (Note 2)		30		ns
OVERVOLTAGE AND UN	DERVOLTAGE	PROTECTION				
BSTMON Overvoltage Trip Threshold	V _{BST_OV}	V _{BSTMON} rising	0.93	0.95	0.97	V
BSTMON Hysteresis				50		mV
BSTMON Input Bias Current		0V < V _{BSTMON} < 1.3V	-1		+1	μΑ
BSTMON Undervoltage	V _{BST_UVR,N}	Normal soft-start	384	400	416	
Detection Threshold, Rising	V _{BST_UVR, F}	Fast soft-start	720	750	780	mV
BSTMON Undervoltage Detection Threshold, Falling	V _{BST_UVF}	BSTMON falling, NGATE latched off	0.335	0.35	0.363	v
Boost Undervoltage Blanking Time, Standard Soft-Start		After EN pin taken high	49	53.25	57.5	ms
Boost Undervoltage Blanking Time, Fast Soft-Start		After EN pin taken high	26.18	28.46	30.74	ms
BSTMON Undervoltage Detection Delay	^t BST_UV_DEL	BSTMON falling	4	10	18	μs
LED FAULT DETECTION		1				
Maximum LED Short- Detection Threshold		V _{RSDT} = 833mV rising	9.7	10	10.3	V
LED Short-Detection Threshold		V _{RSDT} = 0.667V	7.5	8	8.5	V
Minimum LED Short- Detection Threshold		V _{RSDT} = 200mV rising	2.25	2.4	2.5	V
LED Short Disable Threshold		All active OUT_S rising	1.9	2	2.15	V
RSDT Pin Voltage Range			0.2		1	V
RSDT Disable/Switch- to-I2C Threshold			1.45	1.5	1.55	V
RSDT Pin Bias Current			-5		+5	μA
Short-Detection Comparator Delay	tSD_DEL			6.8		μs
OUT_ Check LED Source Current	ICHKLED		50	60	70	μΑ
OUT_ Short to GND Detection Falling Threshold	V _{th_SGND}	Before boost converter start-up	230	250	270	mV

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Electrical Characteristics (continued)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
OUT_ Unused Detection Threshold	V _{th_UNUSED}		0.775	0.85	0.925	V
OUT_ Open-LED Detection Threshold	V _{OOL}	During operation	230	250	270	mV
LOGIC INPUT AND OUT	PUTS	•	·			
DIM, SDA, SCL Input Logic-High			1.6			V
DIM, SDA, SCL Input Logic-Low					0.4	V
DIM, SCL Input Leakage Current			-1		+1	μA
EN Input Logic-High			0.9			V
EN Input Logic-Low					0.6	V
EN Input Current		V _{EN} = 5V		0.01	1	μA
Minimum EN Pulse Width for Device Enable	t _{EN_ON}		5			ms
EN Turn-Off Delay	t _{EN_OFF}	Time between EN going low and complete device shutdown.	11.5	12.8	14.1	ms
DIM Frequency Range			90		50000	Hz
DIM Sampling Frequency				20		MHz
FLTB Output Low Voltage		Sinking 3mA			0.4	V
FLTB Output Leakage Current		V _{FLTB} = 5.5V	-1		1	μA
SDA Output Leakage Current			-1		+1	μA
TEMP Pin						
TEMP Pin Voltage			180	200	220	mV
TEMP to ISET Gain		V _{TEMP} < 250mV	13.7	14.3	14.9	V/mA
TEMP Pin Disable Threshold				0.25		V
TEMP Pin Leakage Current		25°C		0.005	1	μA
ISET Voltage Threshold for LED Current Disable	V _{TEMPD}			150		mV
THERMAL SHUTDOWN						
Thermal-Shutdown Threshold	T _{SHDN}			160		°C
Thermal-Shutdown Hysteresis				17		°C
Thermal Warning Threshold	T _{WARN}	Temperature rising		125		°C

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Electrical Characteristics (continued)

 $(V_{IN} = V_{EN} = 12V, T_A = T_J = -40^{\circ}C$ to +125°C, unless otherwise noted. Typical values are at $T_A = +25^{\circ}C$, unless otherwise noted. (Note 1))

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
I ² C INTERFACE						1
Clock Frequency	f _{SCL}				0.4	MHz
Hold Time (Repeated) START	^t HD:STA		600			ns
SCL Low Time	t _{LOW}		1300			ns
SCL High Time	t _{HIGH}		600			ns
Setup Time (Repeated) START	^t SU:STA		600			ns
Data Hold Time	thd:dat		0			ns
Data Setup Time	t _{SU:DAT}		100			ns
Setup Time for STOP Condition	tsu:sto		600			ns
Spike Suppression				50		ns


Note 1: Limits are 100% tested at $T_A = +25^{\circ}$ C, $T_A = +125^{\circ}$ C and $T_A = -40^{\circ}$ C. Limits over the operating temperature range and relevant supply voltage range are guaranteed by design and characterization.


Note 2: Guaranteed by design.


I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter


Typical Operating Characteristics


(V_{IN} = V_{EN} =12V, 4x9 LED load at 100mA, f_{SW} = 2.2MHz, T_A = +25°C unless otherwise noted.)


























I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter


Typical Operating Characteristics (continued)


(V_{IN} = V_{EN} =12V, 4x9 LED load at 100mA, f_{SW} = 2.2MHz, T_A = +25°C unless otherwise noted.)















EFFICIENCY vs. INPUT VOLTAGE










I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter


Typical Operating Characteristics (continued)

(V_{IN} = V_{EN} =12V, 4x9 LED load at 100mA, f_{SW} = 2.2MHz, T_A = +25°C unless otherwise noted.)



Pin Configuration

MAX25512



I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter


Pin Description

PIN	NAME	FUNCTION
1, 2	DRAIN	Drain connection of internal switching power nMOSFET. Connect to the external inductor and rectifier diode.
3	IN	Input voltage. Connect to protected battery. Bypass IN with a minimum of 2.2μ F in parallel with 0.1μ F placed close to the pin.
4	NGATE	Gate connection for external series nMOSFET driven by the internal charge pump.
5	BSTMON	Boost Voltage Monitoring Input. Connect a resistor divider from the boost converter output to GND with its mid-point connected to the BSTMON pin in order to set the maximum boost output voltage.
6	RT	Oscillator Timing Resistor Connection. Connect a timing resistor (RT) to GND to program the switching frequency. Apply an AC-coupled external clock at RT to synchronize the switching frequency with an external clock.
7	COMP	Switching Converter Compensation Input. Connect the compensation network from COMP to GND for current-mode control (see the <i>Feedback Compensation</i> section).
8	RSDT	LED Short Detection Threshold-Adjust Input. Connect a resistive divider from V18 to RSDT and GND to program the LED short detection threshold. Connect RSDT directly to V18 to disable LED short detection or when programming the threshold using the I ² C interface.
9	V18	Output of internal 1.8V regulator. Connect 1μ F and 0.1μ F capacitors from V18 to GND with the 0.1μ F capacitor placed closest to the pin.
10	GND	Signal GND. GND is the current return path connection for the low-noise analog signals. Connect GND, LEDGND, and PGND at a single point.
11	OUT1	LED String Cathode Connection 1. OUT1 is the open-drain output of the linear current sink that controls the current through the LED string connected to OUT1. OUT1 sinks up to 120mA.
12	OUT2	LED String Cathode Connection 2. OUT2 is the open-drain output of the linear current sink that controls the current through the LED string connected to OUT2. OUT2 sinks up to 120mA. If OUT2 is unused, connect a $10k\Omega$ resistor from OUT2 to LEDGND.
13	ISET	LED Current-Adjust Input. Connect a resistor (R_{ISET}) from ISET to GND to set the current through each LED string (ILED), according to the formula ILED = 1500/ R_{ISET} . Place the resistor close to the pin to avoid parasitic capacitance.
14	TEMP	Temperature sensor input. To implement LED current reduction at high temperatures connect an NTC temperature sensor to GND with resistors from the NTC to TEMP and to V18. If unused, connect TEMP to V18.
15	LEDGND	LED Ground. LEDGND is the return path connection for the linear current sinks. Connect GND, LEDGND, and PGND at a single point.
16	FLTB	Open-Drain Fault Output. FLTB asserts low when a fault is detected. Connect a pullup resistor from FLTB to a logic supply of 5V or lower.
17	DIM	Digital PWM Dimming Input. Apply a PWM signal to DIM for LED dimming control. Connect DIM to a logic supply of 5V or lower if dimming control is not used.
18	SDA	Bidirectional I ² C data pin. Connect a pull-up resistor from this node to the logic supply voltage.
19	SCL	I ² C clock input pin. Connect a pull-up resistor from this node to the logic supply voltage.
20	OUT3	LED String Cathode Connection 3. OUT3 is the open-drain output of the linear current sink that controls the current through the LED string connected to OUT3. OUT3 sinks up to 120mA. If OUT3 is unused connect a $10k\Omega$ resistor from OUT3 to LEDGND.
21	OUT4	LED String Cathode Connection 4. OUT4 is the open-drain output of the linear current sink that controls the current through the LED string connected to OUT4. OUT4 sinks up to 120mA. If OUT4 is unused, connect a $10k\Omega$ resistor from OUT4 to LEDGND.
22, 23	PGND	Power Ground. PGND is the DRAIN current return path connection. Connect GND, LEDGND, and PGND at a single point.
24	EN	Enable Input. Connect EN to logic-high for normal operation. When EN is taken low, the device is disabled after a delay of t_{EN_OFF} . Do not leave the EN input open.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Functional Diagrams

MAX25512



I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Detailed Description

The MAX25512 is a 4-channel backlight driver IC with integrated boost converter for automotive displays. The integrated current outputs can each sink up to 120mA LED current. The device accepts a wide 3V to 36V input voltage range. The IC provides load-dump voltage protection up to 40V in automotive applications and incorporates three major blocks: a DC-DC converter with peak current-mode control to implement a boost or SEPIC-type switched-mode power supply, a 4-channel LED driver with up to 120mA constant-current sink capability per channel, and a logic control block.

The internal current-mode switching DC-DC converter supports boost or SEPIC topologies and operates in the 400kHz to 2.2MHz frequency range. Optional spread spectrum helps reduce EMI. An adaptive output-voltage-control scheme minimizes power dissipation in the LED current-sink paths.

The device tracks the external pulse-width-modulation (PWM) dimming input on DIM. The minimum pulse width is 300ns. Phase-shifted dimming of the strings is selectable for lower EMI.

Comprehensive diagnostic and protection features are implemented. The MAX25512 features an I²C interface for enhanced control and diagnostics.

Enable

The internal regulator is enabled when the EN pin is high. To shut down the device, drive EN low. The current consumption reduces to μ A levels.

The internal low dropout (LDO) regulator converts the input voltage at IN to a 1.8V output voltage at V18. The LDO regulator supplies current to the internal control circuitry and the gate driver.

Undervoltage Lockout

The IC features two undervoltage lockouts (UVLOs) that monitor the input voltage at IN and the output of the internal LDO regulator at V18. The device turns on when EN is taken high, and the boost converter can be enabled if both IN and V18 are higher than their respective UVLO thresholds.

After start-up, the device can operate down to 3V as described below in *Low-Voltage Operation*.

High-Voltage Operation

When the input voltage exceeds V_{LDUMP_TH} the NGATE output follows the IN voltage and the external nMOSFET operates as a source follower. During this time, the power dissipation in the nMOSFET is higher than normal and is approximately Vt x I_{LED(TOTAL)} where Vt is the threshold voltage of the external nMOSFET.

Low-Voltage Operation

After the boost soft-start is complete, the MAX25512 continues to operate with IN voltages as low as 3V.

At very low input voltages, the efficiency of the boost converter reduces, and the input current can reach very high levels as a consequence. When the input voltage falls below V_{LVF} , the boost converter current limit is automatically increased to I_{LIMLV} , and the switching frequency is reduced if it is greater than 1.4MHz. In this mode, if the standard current limit (I_{LIM}) is exceeded on four consecutive cycles, a 100ms timer is started. This returns the current limit to I_{LIM} when it expires. When the input voltage returns above V_{LVR} , operation at the normal switching frequency is resumed.

The external boost converter components must be selected for worst-case operation. An alternative is to reduce the output power at low input voltages.

If the voltage at IN drops below the undervoltage lockout level (V_{INUVF}) at any time, the boost converter is disabled.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Operating Modes




Figure 1. Boost Converter Operating Modes

Disabling Individual Strings

To disable an unused LED string, connect the unused OUT_ to ground through a $10k\Omega$ resistor, or set the corresponding DIS_ bit to 1 in the DISABLE (0x13) register before the ENA bit is set. During startup, the device sources 60μ A (typ) current through the OUT_ pins and measures the corresponding voltage. For the string to be properly disabled, the OUT_ voltage should measure between 270mV and 0.775V during this check. 270mV is the maximum threshold for the OUT_ short-to-ground check, and 0.775V is the minimum unused string-detection threshold.

Note: When disabling unused strings, it is necessary to start by disabling the highest numbered current sinks first (e.g., if two strings need to be disabled, disable OUT4 and OUT3. Do not disable any two strings at random). During normal operation, strings can be selectively turned off by changing the corresponding TON_ setting to 0. This is only possible when internal dimming is used, not when using the DIM input pin.

Current-Mode DC-DC Controller

The IC has a constant-frequency, current-mode controller designed to drive the LEDs in a boost or SEPIC configuration. The IC features multi-loop control to regulate the peak current in the inductor, as well as the voltage across the LED current sinks, to minimize power dissipation.

The internal MOSFET is turned on at the beginning of every switching cycle. The inductor current ramps up linearly until it is turned off at the peak current level set by the feedback loop. The peak inductor current is sensed internally, and slope compensation is added.

The IC features leading-edge blanking to suppress the MOSFET switching noise. A PWM comparator compares the current-sense voltage plus the slope-compensation signal with the output of the transconductance error amplifier. The controller turns off the MOSFET when the total current-sense voltage exceeds the error amplifier's output voltage, which is also the voltage on the COMP pin. This process repeats every switching cycle to achieve peak current-mode control.

In addition to the peak current-mode-control loop, the IC has two other feedback loops for control. The converter output voltage is sensed through the BSTMON input, which goes to the inverting input of the error amplifier. The other feedback comes from the OUT_ current sinks. This loop controls the headroom of the current sinks to minimize total power dissipation while still ensuring accurate LED current matching. Each current sink has a window comparator with a low threshold of V_{OUTL} and a high threshold of V_{OUTH} . The outputs of these comparators control an up/down counter. The up/down counter is updated on every falling edge of the DIM input and drives a 9-bit DAC that sets the reference to the error amplifier. When dimming is set to 100%, the counter is updated at intervals of 10ms.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

9-Bit Digital-to-Analog Converter

The error amplifier's reference input is controlled with an 9-bit digital-to-analog converter (DAC). The DAC output is ramped up slowly during startup to implement a soft-start function (see the *Startup Sequence* section). During normal operation, the DAC output range is limited to 0.48V to 1V. Because the DAC output is limited to no less than 0.48V during normal operation, the overvoltage threshold for the output should be set to a value less than twice the minimum LED forward voltage. The DAC LSB determines the minimum step in output voltage according to the equation:

VSTEP_MIN = VDAC_LSB × AOVP

where,

V_{STEP MIN} = Minimum output-voltage step

V_{DAC LSB} = DAC least significant bit size (1.95mV)

 A_{OVP} = BSTMON resistor-divider gain (1 + R6/R7)

LED Current Control

The full-scale sink current for the outputs (OUT1–OUT4) is set using the resistor on the ISET pin. Use the following equation to calculate the resistor value:

 $R_{\text{ISET}} = \frac{1500}{l_{\text{LED}}}$

where I_{LED} is the individual OUT_ current.

If the R_{ISET} value is less than 11.9k Ω , the device may not operate.

When PWM dimming is used, the current in the OUT_ channels switches between zero and the full-scale sink current at the set duty cycle.

Analog Dimming

By using the ADIM register, the OUT_current set by the resistor on the ISET pin can be reduced in 255 steps. Each step represents 0.4% of the ISET current. When ADIM is set to 0xFF, the full-scale current is provided.

Dimming

Dimming can be performed using an external PWM signal applied to the DIM pin or by writing to the TON_ registers. The signal on the DIM pin is sampled with a 20MHz internal clock except when phase-shifting is disabled, in which case, the DIM signal controls the OUT_ outputs directly.

The device tracks frequency changes in the external pulse-width-modulation (PWM) dimming input on DIM in phase-shift mode.

Low-Dimming Mode

The IC's operation changes at very narrow dimming pulses to ensure a consistent dimming response of the LEDs. If the dimming on-time is lower than $50\mu s$ (typ), the device enters low-dimming mode. In this state, the converter switches continuously, and LED short detection is disabled. When the DIM input is greater than $51\mu s$ (typ), the device goes back into normal operation, enabling the short-LED detection and switching the power FET only when the effective dimming signal is high.

By setting the BSTFORCE bit in the ISET_REG register to 1, it is possible to force the boost converter to run continuously independent of the state of the DIM input.

Phase-Shift Dimming

When the PSEN bit in register 0x02 is set phase shifting of the LED strings is enabled. The device automatically sets the phase shift between strings to 90°, 120°, or 180° depending on the number of strings enabled.

Automatic Fade-In/Fade-Out During Dimming

The device can be configured to perform a smooth change in brightness, even when the DIM input duty cycle or TON_ setting is suddenly changed by setting the FADE_IN_OUT bit in the FADING_REG register to 1.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

When using the fade function, it is important to maintain the DIM frequency constant while entering and leaving 100% duty cycle. This is necessary in order to avoid erroneous frequency measurement that can change the speed of the fade-in/out.

The step size in the dimming transition is either 6.25% or 12.5% depending on the setting of the FADE_GAIN bit. The total transition time can be set by writing the TDIM field to a value between 0 to 5, where the value sets the update speed to once every 2^{TDIM}. The transition time depends on the initial and final dimming values according to:

 $t = \frac{1}{f_{\text{DIM}}} \times 2^{\text{TDIM}} \times \frac{\ln(\text{DIM}_{F}) - \ln(\text{DIM}_{i})}{\text{FADE}_{GAIN}}$

where f_{DIM} is the dimming frequency, TDIM is the TDIM register setting, DIM_F is the final dimming setting, DIM_i is the initial dimming setting, and FADE_GAIN is either 0.0625 or 0.125. For this equation, DIM_F should be larger than DIM_i but, since the fading function is symmetrical, the values can be swapped if the final dimming ratio is lower than the initial one.

When transitioning to 100% dimming with fading enabled, do not change the input dimming from 100% until the complete fading transition to 100% is complete. Use the above equation to determine the transition time.

Hybrid Dimming

In hybrid dimming mode, the external LEDs are dimmed by first reducing their current as the dimming duty-cycle decreases from 100% (see Figure 2). At the crossover level set by the HDIM_THR_1_0[1:0] bits (50%, 25%, 12.5% or 6.25%), dimming transitions to PWM dimming where the LED current is chopped. To select hybrid dimming, set the HDIM bit in the IMODE (0x03) register. Select the desired crossover level between analog and PWM dimming using the HDIM_THR_1_0[1:0] bits in the same register. Depending on the DIM_EXT bit, the device functions in one of the following two ways:

- 1. (DIM_EXT=1) measures the duty cycle on the DIM pin and translates it into a combined LED current value and PWM setting.
- 2. (DIM_EXT=0) takes the 18-bit value from the TON1 register and translates it into a combined LED current value and PWM setting.

When hybrid dimming is used with an internal dimming setting (DIM_EXT=0), only the value TON1[17:0] is used. It is not possible to have individual dimming settings for each channel in this mode.

Note that when hybrid dimming is enabled, the ADIM register has no effect.

Figure 3 illustrates the difference between standard and hybrid dimming with phase-shifting enabled.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Hybrid Dimming Operation






Figure 2. Hybrid Dimming Operation with HDIM[1:0]=10 (25%)

Hybrid Dimming Operation Modes





I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Startup Sequence

When the EN pin is taken high (assuming the IN voltage is above its undervoltage-lockout value), the internal regulator and the I²C interface are turned on. The total duration of this phase of the startup is 2ms (max). After this phase, the I²C interface can be used, and the device registers can be written. The ENA bit should be set to 1 to enable the boost and subsequently the OUT_ current sinks. Before setting the ENA bit to 1 fast soft-start can be chosen by setting the FAST_SS bit to 1. When the ENA bit is set high, the device checks the OUT_ channels for short-circuits to GND. If any of the OUT_ pins are detected as shorted to GND, the boost converter does not start. This avoids possible damage. The corresponding OUT_SG bit(s) are set. The device also detects and disconnects any unused current-sink channels connected to GND by means of a 10k Ω resistor. Alternatively, individual channels can be disabled using the DIS[4:1] bits. The subsequent startup sequence occurs in three stages.

Stage 1

After the ENA bit is set high, the controller turns on the charge-pump for the external nMOSFET. The output current of the charge-pump charges the gate of the external nMOSFET to turn it on. After a 2ms timeout expires, stage 2 of the startup begins.

Stage 2

After the external nMOSFET is turned on, the converter starts switching, and the output begins to ramp. The DAC reference to the error amplifier is stepped up 1 bit at a time until the voltage at BSTMON reaches 480mV or 0.88V when fast soft-start is selected. This stage duration is fixed at approximately 50ms (typ) or 25ms (typ) when fast soft-start is selected. If the BSTMON voltage is greater than 480mV at the end of stage 2, the device transitions directly to stage 3. The BSTMON pin is sampled at the end of this stage. If its voltage is less than 350mV (typ), FLTB is asserted low, the power converter is turned off, the external nMOSFET on NGATE is turned off, and they all remain off until the ENA bit is toggled.

Stage 3

The third stage begins once stage 2 is complete, and the DIM input goes high. During stage 3, the output of the converter is adjusted until the minimum OUT_ voltage falls between the V_{OUTH} and V_{OUTL} comparator limits. The output adjustment is again controlled by the DAC, which provides the reference for the error amplifier. The DAC output is updated on each rising edge of the DIM input pin. If the DIM input is at 100% duty cycle (DIM = high), the DAC output is updated once every 10ms.

The total soft-start time can be calculated using:

$$t_{\rm SS} = 52 \rm{ms} + \frac{(V_{\rm LED} + 0.715) - (0.48 \times A_{\rm OVP})}{f_{\rm DIM} \times 0.078 \times A_{\rm OVP}}$$

where,

t_{SS} = Total soft-start time

52ms = Fixed stage 1 + stage 2 duration

V_{LED} = Total forward voltage of the LED strings

0.715V = Midpoint of the window comparator

f_{DIM} = Dimming frequency (use 100Hz for f_{DIM} when input duty cycle is 100%)

0.078V = 4 times the 1.95mV LSB of the DAC

A_{OVP} = Gain of the BSTMON resistor-divider or 1 + R6/R7, and

0.48V = Voltage on BSTMON after stage 2

If fast soft-start is enabled, the soft-start is accelerated, and the final value of the voltage on the BSTMON pin is 0.88V. The equation for the total soft-start time then becomes:

$$t_{\rm SS} = 27 {\rm ms} + \frac{(V_{\rm LED} + 0.715) + (0.88 \times A_{\rm OVP})}{f_{\rm DIM} \times 0.078 \times A_{\rm OVP}}$$

After the soft-start period, a fault is detected whenever the BSTMON pin falls below VBST_UVF.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Boost Startup




Figure 4. Boost Startup Waveforms

Oscillator Frequency/External Synchronization

The internal oscillator frequency is programmable between 400kHz and 2.2MHz using a timing resistor (R_{RT}) connected from the RT pin to GND. Use the following equation to calculate the value of R_{RT} for the desired switching frequency (f_{SW}).

$$R_{\rm RT} = \frac{26.4 \times 10^6}{f_{\rm SW}} - 0.32$$

where R_{RT} is in k Ω and f_{SW} is in Hz. For example, a 12k Ω resistor on pin RT sets a switching frequency of 2.14MHz.

If the value of the RT resistor is out of range or the pin is shorted to GND, the boost converter cannot start when the ENA bit is set to 1; the RTOOR bit is set, and the FLTB pin goes low.

Synchronize the oscillator with an external clock by AC-coupling the external clock to the RT input. The value of the capacitor used for AC-coupling is C_{SYNC} = 10pF. The duty cycle of the external clock should be 50%. When synchronizing the converter, do not apply the synchronizing signal to the RT pin at start-up as this may cause the RT resistor value check to fail.

At low input voltages, and when the switching frequency is above 1.4MHz, the switching frequency is automatically reduced by 30% to enable high-duty-cycle operation and maintain output voltage regulation. This also applies when the device is synchronized to an external frequency.

Spread Spectrum

The IC includes spread spectrum that reduces peak electromagnetic interference (EMI) at the switching frequency and its harmonics. Spread spectrum can be enabled and disabled using the SS_OFF bit in the register SETTING_REG.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

The spread spectrum uses a pseudorandom dithering technique where the switching frequency is varied in the range 94% to 106% or 96% to 104% of the programmed switching frequency set through the external resistor from RT to GND. Spread spectrum is disabled if external synchronization is used.

Spread spectrum is disabled if external synchronization

Fault Protection

Fault protection in the IC includes cycle-by-cycle current limiting in the PWM controller, DC-DC converter outputundervoltage protection, output-overvoltage protection, open-LED detection, short-LED detection and protection, and overtemperature shutdown. Thermal shutdown and shorted-LED faults are automatically cleared when the fault is removed; however, FLTB stays low until the relevant fault register is read. It is cleared when the fault condition is removed during thermal shutdown and when shorted LEDs are identified. FLTB is latched low for an open-LED and can be reset by cycling power or by toggling the EN pin.

Open-LED Management and Overvoltage Protection

After the soft-start of the boost converter, the IC detects open-LED strings and disconnects any such strings from the internal minimum OUT_ voltage detector. This keeps the DC-DC converter output voltage within safe limits and maintains high efficiency.

During normal operation, the DC-DC converter output-regulation loop uses the minimum OUT_ voltage as the feedback input. If any LED string is open, the voltage at the opened OUT_ goes to V_{LEDGND} . The DC-DC converter output voltage then increases to the overvoltage-protection threshold set by the voltage-divider network connected between the converter output, the BSTMON input, and GND. The overvoltage-protection threshold at the DC-DC converter output is determined using the equation below.

 $V_{\text{OUT}_\text{BSTMON}} = 0.95 \times \left(1 + \frac{R_6}{R_7}\right)$

where 0.95V (typ) is the overvoltage threshold on BSTMON (see the *Functional Diagram*). Select V_{OUT_BSTMON} according to the following formula.

 $1.1x(V_{LED MAX} + 0.875) < V_{OUT BSTMON} < 2x(V_{LED MIN} + 0.55)$

where,

 $V_{LED MAX}$ = Maximum expected LED string voltage

V_{LED MIN} = Minimum expected LED string voltage

Select R6 and R7 so that the voltage at OUT_ does not exceed the absolute maximum rating. As soon as the DC-DC converter output reaches the overvoltage-protection threshold, the internal MOSFET is switched off.

The overvoltage threshold should be set to less than twice the minimum LED voltage to ensure proper operation and so that the BSTMON minimum regulation point of 0.48V (typ) is not breached. When an open-LED overvoltage condition occurs, FLTB is latched low. Any current-sink output with V_{OUT} < V_{OOL} is permanently disconnected from the minimum voltage detector.

OUT_ Short-to-GND Detection

During device start-up the OUT_ pins are checked for short-circuits to ground by sourcing a current I_{CHKLED} into the OUT_ pin and measuring the resultant voltage. If the voltage is below V_{th_SGND} , the OUT_ is considered shorted to ground and the boost converter does not start.

Shorted-LED Detection

The IC checks for shorted LEDs after the current in any channel is turned on. A shorted-LED is detected at OUT_ if the condition below is met.

$V_{OUT} > V_{SLDET}$

where V_{SLDET} = 12x the voltage set on the RSDT pin or when the RSDT pin is connected to V18, the value set by the SLDET[1:0] bits in the SETTING (0x12) register.

If a short is detected on any of the strings, the affected LED strings are disconnected, and the FLTB output flag asserts low until the device detects that the shorts are removed. Disable short-LED detection by connecting RSDT to V18 with

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

SLDET[1:0] set to 0x0. Short-LED detection is disabled in low-dimming mode.

In external dimming mode with the DIM input connected continuously high, the OUT_ pins are periodically scanned to detect shorted LEDs. The scan frequency is 100Hz. Similarly, when DIM_EXT=0 and internal dimming is used, shorted LEDs are still detected by periodically scanning the OUT_ states at 100Hz.

Thermal Warning

If the junction temperature of the device reaches T_{WARN} or if the TEMP pin reaches the voltage representing the temperature T1, the over-temperature warning (OTW) bit in the DIAG_REG register is set. In addition, if the OTWMASK bit is 0 the FLTB pin is asserted low.

Thermal Shutdown

The IC includes thermal protection that operates at a temperature of T_{SHDN} . When the thermal-shutdown temperature is reached, the device is immediately disabled so it can cool. When the junction temperature falls by 17°C, the device is re-enabled and the boost converter performs a soft-start. When a thermal shutdown occurs, the FLTB pin goes low.

Temperature Foldback

When an NTC temperature sensor is connected between GND and a resistor (RT1) connected to the V18 supply, with a further resistor (RT2) connected from the junction of the NTC and RT1 to the TEMP pin, temperature foldback is implemented. When the temperature reaches the temperature T1 (set by RT1), the current in the LEDs is reduced according to the linear scheme shown in figure 5 (Temperature Foldback Curve). The slope of the current reduction is set nominally by RT2. The MAX25512 is specifically designed to be used with the NTCLE100E3 or a similar NTC device. The following table illustrates some examples of values of RT1 and RT2 to obtain certain values of T1 and T_{DELTA}.

RT1	RT2	T1	T _{DELTA}
20kΩ	1.9kΩ	+60°C	+40°C
14kΩ	2kΩ	+70°C	+30°C
10kΩ	1.5kΩ	+80°C	+25°C

Above Temperature T1

When the temperature reaches T1, the OTW bit in register DIAG_REG is asserted. When the temperature reaches T_{OFF}, the LED current is turned off and the FLTB pin asserts low.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Temperature Foldback Curve




Figure 5. Temperature Foldback Curve

TEMP External Circuit




Figure 6. TEMP External Circuit

I2C Interface

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Slave Address

Table 1. I²C Slave Address

	DEVICE ADDRESS							WRITE	READ
	A6	A5	A4	A3	A2	A1	A0	ADDRESS	ADDRESS
MAX25512ATG	0	0 1 0 0 0 1 0					0x44	0x45	

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Register Map

MAX25512

ADDRESS	NAME	MSB							LSB	
USER_REG	ISTERS					I				
0x00	DEV_ID_REG[7:0]				DEV_	ID[7:0]				
0x01	REV_ID_REG[7:0]	_	_	_	_		REV_	ID[3:0]		
0x02	ISET_REG[7:0]	-	_	-	_	BSTFOR CE	FAST_S S ENA PS			
0x03	IMODE_REG[7:0]	LO_DIM 4	LO_DIM 3	LO_DIM 2	LO_DIM 1	DIM_EX T	HDIM	HDIM_TH	R_1_0[1:0]	
0x04	ADIM_REG[7:0]				ADIN	/[7:0]				
0x05	TON1H_REG[7:0]				TON1	H[7:0]				
0x06	TON1L_REG[7:0]				TON1	L[7:0]				
0x07	TON2H_REG[7:0]				TON2	:H[7:0]				
0x08	TON2L_REG[7:0]				TON2	2L[7:0]				
0x09	TON3H_REG[7:0]				TON3	H[7:0]				
0x0A	TON3L_REG[7:0]				TONS	BL[7:0]				
0x0B	TON4H_REG[7:0]				TON4	H[7:0]				
0x0C	TON4L_REG[7:0]				TON4	L[7:0]				
0x0D	TON1_4LSB_REG[7:0]	TON4L	SB[1:0]	TON3L	SB[1:0]	TON2L	SB[1:0]	TON1L	SB[1:0]	
0x0E	SETTING_REG[7:0]	-		FPWM[2:0]		SS_OFF	SSL	SLDE	T[1:0]	
0x0F	DISABLE_REG[7:0]	-	-	CP_DIS	-	DIS4	DIS3	DIS2	DIS1	
0x10	FADING_REG[7:0]	-	-	-	FADE_G AIN	FADE_I N_OUT		TDIM[2:0]		
0x11	OPEN_REG[7:0]	-	_	-	_	OUT4O	OUT3O	OUT2O	OUT10	
0x12	SHORTGND_REG[7:0]	_	_	_	_	OUT4SG	OUT3SG	OUT2SG	OUT1SG	
0x13	SHORTED_LED_REG[7:0]	-	_	_	_	OUT4SL	OUT3SL	OUT2SL	OUT1SL	
0x14	MASK_REG[7:0]	-	-	-	BSTUVM ASK	OMASK	SGMAS K	OTWMA SK	SLMASK	
0x15	DIAG_REG[7:0]	RTOOR	_	ISETOO R	BSTUV	BSTOV	HW_RS T	OTW	ОТ	

Register Details

DEV_ID_REG (0x00)

BIT	7	6	5	4	3	2	1	0				
Field		DEV_ID[7:0]										
Reset				0x	:28							
Access Type				Read	I Only							
BITFIEI	D	BITS DESCRIPTION										
DEV_ID		7:0	Devid	Device ID 0x28.								

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

REV_ID_REG (0x01)

BIT	7	6	5	4	3	2	1	0	
Field	-	-	-	-	REV_ID[3:0]				
Reset	-	-	-	-	0x02				
Access Type	_	-	_	-	Read Only				
BITFIEI	LD	BITS		DESCRIPTION					
REV_ID		3:0	Dev	Device revision ID.					

ISET_REG (0x02)

BIT	7	6	5		4	3	2	1	0
Field	-	-	_		-	BSTFORCE	FAST_SS	ENA	PSEN
Reset	-	-	-		_	0x0	0x0	0b0	0b1
Access Type	_	-	-		-	Write, Read	Write, Read	Write, Read	Write, Read
BITFIEL	D	BITS				DE	SCRIPTION		
BSTFORCE		3			n 1, this bit force endent of the c			continuously ar	nd
FAST_SS		2		Selec	ts slow or fast	boost soft-start	. Set to 1 for fa	ist soft-start.	
ENA		1		Boost converter and LED outputs enable bit. Set to 1 to enable the device				ne device.	
PSEN		0		Wher	n 0, phase shift	ing is disabled.	When 1, phas	e shifting is ena	abled.

IMODE_REG (0x03)

BIT	7	6	5		4	3 2 1				
Field	LO_DIM4	LO_DIM3	LO_D	0IM2	LO_DIM1	DIM_EXT	HDIM	HDIM_TH	R_1_0[1:0]	
Reset	0x0	0x0	0x	0	0x0	0b1	0b0	0b	00	
Access Type	Read Only	Read Only	Read	Only	Read Only	Write, Read	Write, Read	ead Write, Read		
BITFIEI	LD	BITS		DESCRIPTION						
LO_DIM4		7		Wher	n 1, indicates cl	nannel 4 is in le	ow-dim mode.			
LO_DIM3		6			n 1, indicates cl	nannel 3 is in le	ow-dim mode.			
LO_DIM2		5		Wher	n 1, indicates cl	nannel 2 is in le	ow-dim mode.			
LO_DIM1		4		Wher	n 1, indicates cl	nannel 1 is in le	ow-dim mode.			
DIM_EXT		3			n 1, dimming th olled using the		pin is enabled. ers.	When 0, dimm	iing is	
HDIM		2		Wher	n 1, hybrid dimr	ning is enable	d. Default value	is 0.		
				Set h	ybrid dimming	threshold.				
				00		6.25%	0			
HDIM THR 1	0	1:0		10 12.5%						
	10 25%									
				11		50%				

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

ADIM_REG (0x04)

BIT	7	6	5	4	3	2	1	0		
Field		ADIM[7:0]								
Reset				0x	FF					
Access Type		Write, Read								
BITFIE	LD	D BITS DESCRIPTION								
ADIM		7:0 8-bit linear analog dimming value. 0xFF is full-scale current, and each bit represents a current step of 0.4%.								

TON1H_REG (0x05)

On-time setting for channel 1 with 50ns resolution, high byte.

BIT	7	6	5	4	3	2	1	0			
Field		TON1H[7:0]									
Reset				0x	FF						
Access Type				Write,	Read						
BITFIEL	D	D BITS DESCRIPTION									
TON1H	7:0 High byte of 18-bit TON setting for channel 1.										

TON1L_REG (0x06)

On-time setting for channel 1 with 50ns resolution, middle byte.

BIT	7	6	5	4	3	2	1	0			
Field		TON1L[7:0]									
Reset		0xFF									
Access Type		Write, Read									
BITFIEL	D	D BITS DESCRIPTION									
TON1L	7:0 Middle byte of 18-bit TON setting for channel 1.										

TON2H_REG (0x07)

On-time setting for channel 2 with 50ns resolution2, high byte.

BIT	7	6	5	4	3	2	1	0			
Field		TON2H[7:0]									
Reset		0xFF									
Access Type		Write, Read									
BITFIEI	D	D BITS DESCRIPTION									
TON2H		7:0 High byte of 18-bit TON setting for channel 2.									

TON2L_REG (0x08)

On-time setting for channel 2 with 50ns resolution, middle byte.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

BIT	7	6	5	4	3	2	1	0			
Field		TON2L[7:0]									
Reset		0xFF									
Access Type		Write, Read									
BITFIEI	D	BITS DESCRIPTION									
TON2L		7:0	0 Middle byte of 18-bit TON setting for channel 2.								

TON3H_REG (0x09)

On-time setting for channel 3 with 50ns resolution, high byte.

BIT	7	6	5	4	3	2	1	0			
Field		TON3H[7:0]									
Reset		0xFF									
Access Type		Write, Read									
BITFIEL	D	BITS DESCRIPTION									
ТОМЗН		7:0 High byte of 18-bit TON setting for channel 3.									

TON3L_REG (0x0A)

BIT	7	6	5	4	3	2	1	0		
Field		TON3L[7:0]								
Reset				0x	FF					
Access Type		Write, Read								
BITFIEI	D	BITS DESCRIPTION								
TON3L		7:0 Middle byte of 18-bit TON setting for channel 3.								

TON4H_REG (0x0B)

On-time setting for channel 4 with 50ns resolution, high byte.

BIT	7	6	5	4	3	2	1	0			
Field		TON4H[7:0]									
Reset		0xFF									
Access Type		Write, Read									
BITFIEI	LD	BITS DESCRIPTION									
TON4H		7:0 High byte of 18-bit TON setting for channel 4.									

TON4L_REG (0x0C)

On-time setting for channel 4 with 50ns resolution, middle byte.

On-time setting for channel 3 with 50ns resolution, middle byte.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

BIT	7	6	5	4	3	2	1	0			
Field		TON4L[7:0]									
Reset		0xFF									
Access Type		Write, Read									
BITFIEI	D	BITS DESCRIPTION									
TON4L		7:0	7:0 Middle byte of 18-bit TON setting for channel 4.								

TON1_4LSB_REG (0x0D)

LSBs of on-time setting for all channels with 50ns resolution.

BIT	7	6	5 4		3	2	1	0			
Field	TON4	TON4LSB[1:0] T		SB[1:0]	TON2LSB[1:0]		TON1L	SB[1:0]			
Reset	0	0b11		0b11		11	0b	11			
Access Type	Write, Read		Write,	Read	Write, Read		Write, Read				
BITFIEI	D	BITS		DESCRIPTION							
TON4LSB		7:6	2 leas	2 least significant bits of 18-bit TON setting for channel 4.							
TON3LSB		5:4	2 leas	2 least significant bits of 18-bit TON setting for channel 3.							
TON2LSB		3:2	2 leas	2 least significant bits of 18-bit TON setting for channel 2.							
TON1LSB		1:0	2 least significant bits of 18-bit TON setting for channel 1.								

<u>SETTING_REG (0x0E)</u>

BIT	7	6	5		4		3	3	2		1	0
Field	_		FPWN	I[2:0]			SS_	OFF	FF SSL		SLDE	T[1:0]
Reset	_		0b0	01		Ob	0	0b0		0b	00	
Access Type	-		Write,			Read			Write, Read		Write,	Read
BITFIEI	D	BITS			DESCRIPTION							
			These bits set the PWM frequency in internal PWM mode.									
				FP	WM2	FPWM1		FPW	WM0 PV		/M FREQUEN	CY (Hz)
					0		0 0)		153	
					0 0		0	1			203	
					0		1	0)		305	
FPWM		6:4		0			1 1			610		
					1		0 0		0 980		980	
					1		0	1			1220	
					1		1	0)		1401	
					1		1		1 1634			
SS_OFF		3		When 1, spread-spectrum switching is disabled. Default value is 0.					0.			

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

BITFIELD	BITS		DESCRIPTION				
SSL	2	When spread spectrum is enabled, the SSL bit chooses the amount of spread. When 0, the spread is nominally ±6%. When 1, the spread is ±4%. When changing the percentage, disable spread-spectrum using the SS_OFI bit first. Then, change the value of SSL. Finally, re-enable spread spectrum using SS_OFF.					
		Shorted-LED-Threshold Settings.					
		00	Disabled				
SLDET	1:0	01	3V				
	-	10	6V				
		11 8V					

DISABLE_REG (0x0F)

Channel-disable bits.

BIT	7	6	5	4	3	2	1	0	
Field	_	-	CP_DI	S –	DIS4	DIS3	DIS2	DIS1	
Reset	_	– 0b0		-	0b0	0b0	0b0	0b0	
Access Type	_	– Write, F		ead –	Write, Read	Write, Read	Write, Read	Write, Read	
BITFIE	LD	BITS		DESCRIPTION					
CP_DIS		5	p z	When 1, this bit disables the internal charge pump, which drives the pin. Set to 1 when an external series switch is not used. Setting CP_zero during operation will cause complete shutdown of the device an recommended.					
DIS4		3	S	Set bit to 1 to disat	le OUT4. This n	nust be done b	efore ENA is w	ritten to 1.	
DIS3		2	S	Set bit to 1 to disable OUT3. This must be done before ENA is written to 1.					
DIS2		1	S	Set bit to 1 to disable OUT2. This must be done before ENA is written to 1.					
DIS1		0	S	Set bit to 1 to disable OUT1. This must be done before ENA is written to 1.					

FADING_REG (0x10)

BIT	7	6	5	4	3	2	1	0	
Field	-	-	-	FADE_GAI N	FADE_IN_ OUT	TDIM[2:0]			
Reset	_	_	_	0b0	0b0		0b000		
Access Type	-	-	-	Write, Read	Write, Read	d Write, Read			
BITFIELD	BITS		DESCRIPT	ION		D	ECODE		
FADE_GAIN	4		it is set to 1, the a gain of 12.5						
FADE_IN_O UT	3		it is set to 1, the						

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

BITFIELD	BITS	DESCRIPTION	DECODE
TDIM	2:0	Sets the fading update time interval according to 2 ^{TDIM} . TDIM can be between 0 and 5. When set to 0, fading is updated on every dimming cycle.	0x0: 1 0x1: 2 0x2: 4 0x3: 8 0x4: 16 0x5: 32 0x6: NA 0x7: NA

OPEN_REG (0x11)

Open-string diagnostics.

BIT	7	6	5		4	3	2	1	0
Field	-				-	OUT4O	OUT3O	OUT2O	OUT1O
Reset	-				—	0b0	0b0	0b0	0b0
Access Type			_		_	Read Only	Read Only	Read Only	Read Only
BITFIEI	LD	BITS				DE	SCRIPTION		
OUT4O		3		lf 1, a	in open is deteo	cted on channe	el 4.		
OUT3O		2	2 If 1, an open is detected on channel 3.						
OUT2O		1	If 1, an open is detected on channel 2.						
OUT1O	0 If 1, an open is detected on channel 1.								

SHORTGND_REG (0x12)

Short-to-ground diagnostics.

BIT	7	6	5	4	3	2	1	0	
Field	_	-	_	-	OUT4SG	OUT3SG	OUT2SG	OUT1SG	
Reset	-	-	-	-	0b0	0b0	0b0	0b0	
Access Type	-	_	-	-	Read Only	Read Only	Read Only	Read Only	
BITFIELD BITS DESCRIPTION									
OUT4SG		3	lf 1, a	a short-to-grour	d is detected c	on channel 4 at	startup.		
OUT3SG	T3SG 2		lf 1, a	If 1, a short-to-ground is detected on channel 3 at startup.					
OUT2SG 1		lf 1, a	If 1, a short-to-ground is detected on channel 2 at startup.						
OUT1SG 0			lf 1, a	If 1, a short-to-ground is detected on channel 1 at startup.					

SHORTED_LED_REG (0x13)

Shorted-LED diagnostics,

BIT	7	6	5	4	3	2	1	0	
Field	-	-	-	-	OUT4SL	OUT3SL	OUT2SL	OUT1SL	
Reset	-	-	-	-	0b0	0b0	0b0	0b0	
Access Type	_	-	_	-	Read Only	Read Only	Read Only	Read Only	
BITFIEI	LD	BITS		DESCRIPTION					
OUT4SL		3	lf 1,	If 1, a shorted-LED condition is detected on channel 4.					

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

BITFIELD	BITS	DESCRIPTION
OUT3SL	2	If 1, a shorted-LED condition is detected on channel 3.
OUT2SL	1	If 1, a shorted-LED condition is detected on channel 2.
OUT1SL	0	If 1, a shorted-LED condition is detected on channel 1.

MASK_REG (0x14)

Mask register for the FLTB pin.

BIT	7	6	5		4	3	2	1	0
Field	-	-	_		BSTUVMAS K	OMASK	SGMASK	OTWMASK	SLMASK
Reset	_	-			0b0	0b0	0b0	0b1	0b0
Access Type	_	-			Write, Read	Write, Read	Write, Read	Write, Read	Write, Read
BITFIEI	LD BITS DESCRIPTION								
BSTUVMASK		4	4 When 1, a boost undervoltage fault does not cause the FLTB pin to assert low.					to assert	
OMASK		3		Wher	n 1, an open-LE	D fault does n	ot cause the Fl	TB pin to asse	ert low.
SGMASK		2		When 1, a short-to-ground LED fault does not cause the FLTB pin to assert low.					
OTWMASK		1	When 1, an overtemperature warning does not cause the FLTB pin to ass low.					oin to assert	
SLMASK		0		Wher	n 1, a shorted-L	ED fault does	not cause the F	LTB pin to ass	ert low.

DIAG_REG (0x15)

Boost state, overtemperature-warning/shutdown diagnostics.

boost state, overtemperature-warning/shutdown diagnostics.									
BIT	7	6	5	5	4	3	2	1	0
Field	RTOOR	-	– ISETC		BSTUV	BSTOV	HW_RST	OTW	ОТ
Reset	0b0	-	0b0		0b0	0b0	0b1	0b0	0b0
Access Type	Read Onl	у –	Read	Only	Read Only	Read Only	Read Only	Read Only	Read Only
BITFI	ELD	BITS		DESCRIPTION					
RTOOR		7		This bit is set to 1 if the resistor on the RT pin is out of the expected range. When this happens, the device cannot operate.					
ISETOOR		5		When 1, this bit indicates that the ISET current is out of range. This is more than likely due to an incorrect resistor value on ISET. In this condition, the IC stops operation.					
BSTUV		4	If 1, an undervoltage is detected on the boost output, and the boost is disabled						ost is

		disabled.
BSTOV	3	If 1, the boost converter is at its overvoltage limit.
HW_RST	2	If 1, the device has just emerged from a hardware reset (power-up). This bit is reset after the first read from this register.
отw	1	If 1, the junction temperature of the device is over $T_{WARN},$ or the temperature foldback circuit has reached the temperature T1.
от	0	If 1, the junction temperature of the device exceeds T _{SHDN} , and the device is shut down.

Applications Information

DC-DC Converter

The MAX25512 DC-DC converter offers the capability to work with two different converter topologies that have the ground-referenced outputs necessary to use the constant-current sink drivers. If the LED string forward voltage is always greater than the input supply voltage range, use the boost-converter topology. If the LED string forward voltage falls within the supply voltage range, use the SEPIC topology.

The boost-converter topology provides the highest efficiency of these topologies. The SEPIC configuration requires either two inductors or a coupled inductor and a coupling capacitor.

Power-Circuit Design

First, select a converter topology based on the factors listed above. Determine the required input supply voltage range, the maximum voltage needed to drive the LED strings, including the minimum 0.875V across the constant LED current sink (V_{LED}), and the total output current needed to drive the LED strings (I_{LED}), as shown in the equation below.

$$I_{\text{LED}} = I_{\text{STRING}} \times N_{\text{STRING}}$$

where I_{STRING} is the current per string, and N_{STRING} is the number of strings used.

Next, calculate the maximum duty cycle (D_{MAX}) using one of the equations below, depending on the configuration.

(for boost configuration):

$$D_{\text{MAX}} = \frac{\left(V_{\text{LED}} + V_{D1} - V_{\text{IN}}_{\text{MIN}}\right)}{\left(V_{\text{LED}} + V_{D1} - V_{\text{DS}} - 0.3\right)}$$

(for SEPIC configuration):

$$D_{\text{MAX}} = \frac{V_{\text{LED}} + V_{D1}}{\left(V_{\text{IN}_{\text{MIN}}} - V_{\text{DS}} - 0.3 + V_{\text{LED}} + V_{D1}\right)}$$

where,

- V_{D1} = Forward drop of the rectifier diode in volts (approximately 0.6V)
- V_{IN MIN} = Minimum input supply voltage
- V_{DS} = Drain-to-source voltage of the internal MOSFET when it is on, given by ILAVG x RDS(ON) where RDS(ON) = 125mohm

Select the switching frequency (f_{SW}) depending on space, noise, and efficiency constraints.

Boost Configuration

In the converter configurations, the average inductor current varies with the input voltage; the maximum average current occurs at the lowest input voltage. For the boost converter, the average inductor current is equal to the input current. Select the maximum peak-to-peak ripple on the inductor current (Δ IL). The recommended maximum peak-to-peak ripple is 60% of the average inductor current, but lower and higher values of ripple are also acceptable.

Use the following equations to calculate the maximum average inductor current (I_{LAVG}) and peak inductor current (I_{LP}) in amperes.

$$IL_{AVG} = \frac{I_{LED}}{(1 - D_{MAX})}$$

Allowing the peak-to-peak inductor ripple (Δ IL) to be ±30% of the average inductor current:

$$\Delta IL = IL_{AVG} \times 0.3 \times 2$$

and:
$$IL_P = IL_{AVG} + \frac{\Delta IL}{2}$$

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Calculate the minimum inductance value (L_{MIN}) in henries (H) with the inductor current ripple set to the maximum value:

$$L_{\text{MIN}} = \frac{\left(V_{\text{IN}} - V_{\text{DS}} - 0.3\right) \times D_{\text{MAX}}}{f_{\text{SW}} \times \Delta IL}$$

where V_{DS} is IL_{AVG} x 0.125. Choose an inductor with a minimum inductance greater than the calculated L_{MIN} and current rating greater than IL_P. The recommended saturation current limit of the selected inductor is 10% higher than the inductor peak current.

SEPIC Configuration

Power-circuit design for the SEPIC configuration is very similar to a conventional design with the output voltage referenced to the input supply voltage. For SEPIC, the output is referenced to ground and the inductor is split into two parts. One of the inductors (L2) takes LED current as the average current, and the other (L1) takes input current as the average current.

Use the following equations to calculate the average inductor currents ($IL1_{AVG}$, $IL2_{AVG}$) and peak inductor currents ($IL1_P$, $IL2_P$) in amperes.

$$I_{L1AVG} = \frac{I_{LED} \times D_{MAX} \times 1.1}{1 - D_{MAX}}$$

The factor 1.1 provides a margin of 10% to account for the converter losses.

$$IL2_{AVG} = I_{LED}$$

Assuming the peak-to-peak inductor ripple ΔIL is ±30% of the average inductor current.

$$\Delta IL1 = IL1_{AVG} \times 0.3 \times 2$$

and:
$$IL1_P = IL1_{AVG} + \frac{\Delta IL1}{2}$$

and:
$$\Delta IL2 = IL2_{AVG} \times 0.3 \times 2$$

and:
$$IL2_P = IL2_{AVG} + \frac{\Delta IL2}{2}$$

Calculate the minimum inductance values (L1_{MIN} and L2_{MIN}) in henries with the inductor current ripple set to the values previously calculated.

$$L1_{\text{MIN}} = \frac{\left(V_{\text{IN}_\text{MIN}} - V_{\text{DS}} - 0.3\right) \times D_{\text{MAX}}}{f_{\text{SW}} \times \Delta \text{IL1}}$$
$$L2_{\text{MIN}} = \frac{\left(V_{\text{IN}_\text{MIN}} - V_{\text{DS}} - 0.3\right) \times D_{\text{MAX}}}{f_{\text{SW}} \times \Delta \text{IL2}}$$

Choose inductors with a minimum inductance greater than the calculated $L1_{MIN}$ and $L2_{MIN}$ and current rating greater than IL1_P and IL2_P, respectively. The recommended saturation current limit of the selected inductor is 10% higher than the inductor peak current.

To simplify further calculations, consider a single inductor equivalent to L1 and L2 connected in parallel. The combined inductance value and current is calculated as shown below.

$$L = \frac{L1 \times L2}{L1 + L2}$$

and:
$$IL_{AVG} = IL1_{AVG} + IL2_{AVG}$$

where ILAVG represents the total average current through both the inductors in the SEPIC configuration. Use these

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

values in the calculations in the following sections.

Select coupling-capacitor C_S so peak-to-peak ripple on it is less than 2% of the minimum input supply voltage. This ensures that the second-order effects created by the series-resonant circuit comprising L1, C_S , and L2 do not affect the normal operation of the converter. Use the following equation to calculate the minimum value of C_S .

$$C_{\rm S} = \frac{l_{\rm LED} \times D_{\rm MAX}}{V_{\rm IN MIN} \times 0.02 \times f_{\rm SW}}$$

where,

- C_S = Minimum value of the coupling capacitor in farads
- 0.02 = 2% ripple factor

Output Capacitor Selection

The output capacitor supplies the load current when the main switch is on. The function of the output capacitor is to reduce the converter output ripple to acceptable levels. The entire output-voltage ripple appears across the constantcurrent sink outputs because the LED-string voltages are stable due to the constant current. For the MAX25512, limit peak-to-peak output-voltage ripple to 250mV to get stable output current.

The equivalent series resistance (ESR), equivalent series inductance (ESL), and bulk capacitance of the output capacitor contribute to the output ripple. In most applications, using low-ESR ceramic capacitors can dramatically reduce the output ESR and ESL effects. To reduce this, connect multiple ceramic capacitors in parallel to achieve the required bulk capacitance. To minimize audible noise during PWM dimming, the amount of ceramic capacitors on the output is usually minimized. In this case, an additional electrolytic or aluminum organic polymer capacitor can provide most of the bulk capacitance.

Rectifier Diode Selection

Using a Schottky rectifier diode produces less forward drop and puts the least burden on the MOSFET during reverse recovery. Select a diode with low reverse-recovery losses to reduce the MOSFET switching losses and avoid increased EMI. The voltage rating of the diode should be 20% higher than the maximum boost-converter output voltage and its current rating greater than that shown below.

$$IL_{AVG} \times (1 - D_{MAX}) \times 1.2$$

Feedback Compensation

During normal operation, the feedback control loop regulates the minimum OUT_ voltage to fall within the window comparator limits of V_{OUTL} and V_{OUTH} when LED string currents are enabled during PWM dimming. When LED currents are off during PWM dimming, the control loop turns off the converter (when BSTFORCE=0) and stores the previous boost output-voltage value for use during the next on cycle.

The switching converter small-signal-transfer function has a right-half plane (RHP) zero in the boost configuration if the inductor current is in continuous-conduction mode. The RHP zero adds a 20dB/decade gain together with a 90° phase lag, which is difficult to compensate.

(worst-case RHP zero frequency (f_{ZRHP}) is calculated using):

$$f_{ZRHP} = \frac{V_{LED} \times (1 - D_{MAX})^2}{2 \times \pi \times L \times I_{LED}}$$

2

(for the SEPIC configuration):

$$f_{ZRHP} = \frac{V_{LED} \times (1 - D_{MAX})^2}{2 \times \pi \times L \times I_{LED} \times D_{MAX}}$$

The standard way to avoid this zero is to roll off the loop gain to 0dB at a frequency of less than 1/5 of the RHP zero frequency with a -20dB/decade slope.

The switching converter small-signal transfer function also has an output pole. The effective output impedance, together with the output filter capacitance, determines the output pole frequency (f_{P1}) that is calculated for the boost configuration,

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

as shown in the following equation.

$$f_{P1} = \frac{I_{LED}}{\pi \times V_{LED} \times C_{OUT}}$$

(for SEPIC):

$$f_{P1} = \frac{I_{\text{LED}} \times D_{\text{MAX}}}{\pi \times V_{\text{LED}} \times C_{\text{OUT}}}$$

Compensation components R_{COMP} and C_{COMP} perform two functions. C_{COMP} introduces a low-frequency pole that presents a -20dB/decade slope to the loop gain. R_{COMP} flattens the gain of the error amplifier for frequencies above the zero formed by R_{COMP} and C_{COMP} . For compensation, this zero is placed at f_{P1} to provide a -20dB/decade slope for frequencies above f_{P1} to the combined modulator and compensator response.

The value of R_{COMP} needed to fix the total loop gain at f_{P1} so the total loop gain crosses 0dB with -20dB/decade slope at 1/5 the RHP zero frequency, is calculated for the boost configuration below.

$$R_{\text{COMP}} = \frac{f_{\text{ZRHP}} \times R_{\text{CS}} \times I_{\text{LED}} \times A_{\text{OVP}}}{5 \times f_{P1} \times GM_{\text{COMP}} \times V_{\text{LED}} \times (1 - D_{\text{MAX}})}$$

(for the SEPIC configuration):

$$R_{\text{COMP}} = \frac{f_{\text{ZRHP}} \times R_{\text{CS}} \times I_{\text{LED}} \times A_{\text{OVP}} \times D_{\text{MAX}}}{5 \times f_{P1} \times GM_{\text{COMP}} \times V_{\text{LED}} \times (1 - D_{\text{MAX}})}$$

where,

- R_{COMP} = Compensation resistor in Ω
- A_{OVP} = BSTMON resistor-divider gain (a value >> 1)
- R_{CS} = Current-sense resistor of value 0.066 Ω
- GM_{COMP} = Transconductance of the error amplifier (600µS)

The value of C_{COMP} is calculated as shown below.

$$C_{\text{COMP}} = \frac{1}{2 \times \pi \times f_{Z1} \times R_{\text{COMP}}}$$

where f_{Z1} is the compensation zero placed at 1/5 the crossover frequency; in turn, it is set at 1/5 the f_{ZRHP} . If the output capacitors do not have low ESR, the ESR zero frequency can fall below the 0dB crossover frequency. An additional pole may be required to cancel out this zero placed at the same frequency. This can be added by connecting a capacitor from the COMP pin directly to GND with a value shown below.

where R_{ESR} is the capacitor ESR value and C_{OUT} is the output-capacitor value.

External Disconnect MOSFET Selection

An external nMOSFET can be used to disconnect the boost output from the battery in the event of an output overload or short condition. There is no need for the nMOSFET in the case of the SEPIC or buck-boost, since this protection is not necessary. Leave the NGATE pin disconnected when an external nMOSFET is not used and set the CP_DIS bit to 1. If it is necessary to have output-short protection for the boost even at power-up, then the current through the nMOSFET must be sensed (refer to the MAX25512 EV kit for a reference circuit). Once the current-sense voltage exceeds a certain threshold, it should limit the input current to the programmed threshold. This threshold should be set at a sufficiently high level so it never trips at startup or under normal operating conditions. Check the safe operating area (SOA) of the nMOSFET to confirm the current-limit-trip threshold and voltage on the MOSFET do not exceed the limits of the SOA curve of the nMOSFET at the highest operating temperature.

Ensure that the maximum value of the nMOSFET gate threshold voltage is lower than 4V for reliable operation.

V_{OUT} to OUT_ Bleed Resistors

The OUT_ pins have a leakage specification of 4µA (max) in cases where all OUT_ pins are shorted to 36V (see

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

 $I_{OUTLEAK}$ in the *Electrical Characteristics* table). This leakage current is dependent on the OUT_voltage and is higher at higher voltages. Therefore, in cases where large numbers of LEDs are connected in series, a 100k Ω (or larger) bleed resistor can be placed in parallel with the LED string to prevent the OUT_leakage current from turning on the LEDs dimly, even when the DIM signal is low (see resistors R8–R11 in the *Typical Application Circuit*).

Thermal Considerations

The on-chip power dissipation of the MAX25512 comprises four main factors:

- 1. Current-sink power loss = $0.875V \times I_{LED}$
- 2. Device operating current power loss = $V_{IN} \times 1.3$ mA
- 3. Power due to $R_{DS(ON)}$ of internal MOSFET = DC × I_{LAVG}^2 × 0.125
- Power due to switching losses in the internal MOSFET = 0.5 × VLED × ILED × t_{R/F} × f_{SW} where t_{R/F} is the rise/fall time of the boost converter switching node approximated to 6ns.

Calculate the total power dissipation by adding the values calculated above. The junction temperature at the maximum ambient temperature can then be calculated as follows.

$$T_J = T_A + P_{TOT} \times \theta_{JA}$$

where T_A is the ambient temperature and θ_{JA} is the junction-to-ambient thermal resistance of the package (36°C/W on a four-layer board). Ensure that the junction temperature does not exceed 150°C.

As an example, consider an application with a minimum operating voltage of 9V, a total output current of 400mA at 28.7V and an average 1.5A inductor current. With a switching frequency of 400kHz, the total power dissipation is calculated in the following equation.

$$P_{\mathsf{TOT}} = (0.875 \times 0.4) + (9 \times 0.0013) + (\frac{28.7}{28.7 + 9} \times 1.5^2 \times 0.125) + (0.5 \times 28.7 \times 0.4 \times 6E - 9 \times 400000) = 0.59W$$

The maximum junction temperature at an ambient temperature of +85°C is shown in the following equation.

$$T_J = 85 + 0.59 \times 36 = +106 \circ C$$

PCB Layout Considerations

Based on the MAX25512, LED driver circuits use a high-frequency switching converter to generate the voltage for LED strings. Take proper care while laying out the circuit to ensure correct circuit operation. The switching-converter part of the circuit has nodes with fast voltage changes that can lead to undesirable effects on the sensitive parts of the circuit. Follow the guidelines below to reduce noise as much as possible:

- Connect the bypass capacitors on V18 as close as possible to the device. Make the connections directly to the device V18 and GND pins. Connect the GND pin of the device to the analog ground plane and to the exposed pad of the device. Place the analog ground plane on an inner layer.
- Place a power ground plane for the switching-converter power circuit under the power components (input filter capacitor, output filter capacitor, inductor and rectifier diode). Connect the PGND pins to the power ground plane and to the exposed pad of the device. Connect all other ground connections to the power ground plane using vias close to the terminals.
- There are two loops in the power circuit that carry high-frequency switching currents. One loop exists when the internal MOSFET is on (from the input filter capacitor positive terminal, through the inductor and internal MOSFET, to the input capacitor negative terminal). The other loop exists when the MOSFET is off (from the input capacitor positive terminal, through the inductor, the rectifier diode, output filter capacitor, to the input capacitor negative terminal). Analyze these two loops in order to make the loop areas as small as possible. Wherever possible, have a return path on the power ground plane for the switching currents on the top layer copper traces or through power components. This reduces the loop area considerably and provides a low-inductance path for the switching currents. Reducing the loop area also decreases radiation during switching.
- Connect the power ground plane for the constant-current LED driver part of the circuit to the LEDGND pin. Also connect the LEDGND pin to the device exposed pad.
- Add a small bypass capacitor (22pF to 47pF) to the BSTMON input. Place the capacitor as close as possible to the pin to suppress high-frequency noise.
- Boost output voltage for the LED strings must be taken directly from the output capacitors and not from the boost diode anode.


I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

- Input and output capacitors need good grounding with wide traces and multiple vias to the ground plane.
- To enhance device power dissipation, add multiple vias under the device exposed pad connected to an area of copper on the backside of the PCB. This is important for maintaining device efficiency and reducing junction temperature during operation.

Refer to the EV kit for a reference layout.

Typical Application Circuits


MAX25512 Application Circuit



I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Typical Application Circuits (continued)

MAX25512 Application Circuit - SEPIC



Ordering Information

PART NUMBER	TEMPERATURE RANGE	PIN-PACKAGE
MAX25512ATG/V+	-40°C to +125°C	24 TQFN-EP*

N Denotes an automotive-qualified part.

+ Denotes a lead(Pb)-free/RoHS-compliant package.

T = Tape and reel.

*EP = Exposed pad.

Y = Side-wettable (SW) package.

I²C-Controlled 4-Channel Low-Voltage 120mA LED Backlight Driver with Integrated Boost Converter

Revision History

REVISION	REVISION	DESCRIPTION	PAGES
NUMBER	DATE		CHANGED
0	5/21	Initial release	—

For pricing, delivery, and ordering information, please visit Maxim Integrated's online storefront at https://www.maximintegrated.com/en/storefront/storefront.html.

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the Electrical Characteristics table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.

Maxim Integrated and the Maxim Integrated logo are trademarks of Maxim Integrated Products, Inc.