1575.42 MHz GNSS Chip Antenna








Features

- Stable and reliable performance
- · Low Profile, Compact Size
- RoHs Complaint

Applications

- GNSS (Global Navigation Satellite System)
- Hand-held devices when GPS & BDS & GLONASS & GALILEO functions are needed, e.g, PDA, Smart Phone, PND








1575.42 MHz GNSS Chip Antenna







Part Number Breakdown



Pin Definition



PIN	1	2
Soldering PAD	Signal	Tuning / Ground


1575.42 MHz GNSS Chip Antenna







Dimension Drawing



Dimensions (mm) & Mechanical

Body Length (A)	3.2 ± 0.15
Width (B)	1.6 ± 0.15
Thickness (C)	0.5 ± 0.15
Connection Type	SMT
Ground Plane	49.5 mm x 20 mm
Material	Ceramic


1575.42 MHz GNSS Chip Antenna







Evaluation Board



Unit: mm

1575.42 MHz GNSS Chip Antenna









Solder Land Pattern

The gray areas represent the solder land pattern. Any recommendations on the matching circuit will be provided according to the customer's installation conditions.



Transmission Line with 50Ω Impedance Characteristic

Top View



Bottom View


1575.42 MHz GNSS Chip Antenna







Soldering Conditions



^{*}Recommended solder paste alloy: SAC305 (Sn96.5 /Ag3 /Cu0.5) Lead Free solder paste


1575.42 MHz GNSS Chip Antenna







Frequency vs. V.S.W.R. and Total Radiation Gain



1575.42 MHz GNSS Chip Antenna









Radiation Patterns

3D Radiation Gain Pattern @ 1561 MHz


















1575.42 MHz GNSS Chip Antenna








3D Radiation Gain Pattern @ 1575.42 MHz


















1575.42 MHz GNSS Chip Antenna








3D Radiation Gain Pattern @ 1590 MHz


















1575.42 MHz GNSS Chip Antenna








3D Radiation Gain Pattern @ 1602 MHz


















1575.42 MHz GNSS Chip Antenna








Frequency Tuning & Matching Circuit














System Matching Circuit Component				
Location	Description	Tolerance	NIC Part Number	
1	1.5pF, (0402)	±0.05pF	NMC-Q0402NPO1R5A50TRPF	
2	0Ω, (0402)	-	NRC04Z0TRF	
3	3.3pF, (0402)	±0.05pF	NMC-Q0402NPO3R3A50TRPF	
4 Fine Tuning Element	1.0pF, (0402)	±0.05pF	NMC-Q0402NPO1R0A50TRPF	
5 Fine Tuning Element	2.7pF, (0402)	±0.05pF	NMC-Q0402NPO2R7A50TRPF	

Frequency Tuning Element 5




1575.42 MHz GNSS Chip Antenna







Frequencies vs. Capacitance of Tuning Element 5



2.4 GHz WiFi / Bluetooth Chip Antenna








Packing

(1) Unit Weight: 0.042±0.005(g)/pcs

(2) Quantity/Reel: 3000 pcs/Reel

(3) Plastic tape: Black Conductive Polystyrene.

a. Tape Drawing




b. Tape Dimensions (unit: mm)

Feature	Specifications	Tolerances
W	12.00	±0.30
Р	4.00	±0.10
E	1.75	±0.10
F	5.50	±0.10
P2	2.00	±0.10
D	1.50	+0.10
	1.50	-0.00
Po	4.00	±0.10
10Po	40.00	±0.20

c. Reel Drawing

В



Performance Passives By Design

Ρ