Final datasheet

EconoDUAL™3 module with CoolSiC™ Trench MOSFET and PressFIT / pre-applied thermal interface material / NTC



Features

- Electrical features
  - V_{DSS} = 1200 V
  - I_{DN} = 500 A / I_{DRM} = 1000 A
  - Integrated temperature sensor
  - Suitable Infineon gate drivers can be found under https://www.infineon.com/gdfinder
- Mechanical features
  - Standard housing
  - PressFIT contact technology
  - Isolated base plate
  - High power density
  - Pre-applied thermal interface material

Potential applications

- Construction, commercial, and agriculture vehicles
- Wind turbines
- Motor drives
- UPS systems
- Solar applications

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description



Table of contents

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, f = 50 Hz, *t* = 1 min	3.4	kV
Isolation test voltage NTC	$V_{ISOL(NTC)}$	RMS, f = 50 Hz, *t* = 1 min	3.4	kV
Material of module baseplate			Cu	
Internal isolation		basic insulation (class 1, IEC 61140)	Al_2O_3	
Creepage distance	$d_{Creep\ nom}$	terminal to baseplate, nom., (PD2, IEC 60664-1, Ed. 3.0)	> 15	mm
Creepage distance	$d_{Creep\ min}$	terminal to baseplate, min., (PD2, IEC 60664-1, Ed. 3.0)	14.7	mm
Creepage distance	$d_{Creep\ nom}$	terminal to terminal, nom., (PD2, IEC 60664-1, Ed. 3.0)	12.1	mm
Creepage distance	$d_{Creep\ min}$	terminal to terminal, min., (PD2, IEC 60664-1, Ed. 3.0)	11.5	mm
Clearance	$d_{Clear\ nom}$	terminal to baseplate, nom.	> 12.5	mm
Clearance	$d_{Clear\ min}$	terminal to baseplate, min.	12.5	mm
Clearance	$d_{Clear\ nom}$	terminal to terminal, nom.	10.0	mm
Clearance	$d_{Clear\ min}$	terminal to terminal, min.	9.6	mm
Comparative tracking index	*CTI*		> 200	
Relative thermal index (electrical)	*RTI*	housing	140	°C

Table 2 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Stray inductance module	L_{sCE}				20		nH
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	T_H = 25 °C, per switch			0.8		mΩ
Storage temperature	T_{stg}			-40		125	°C
Maximum baseplate operation temperature	T_{BPmax}					150	°C
Mounting torque for module mounting	*M*	- Mounting according to valid application note	M5, Screw	3		6	Nm
Terminal connection torque	*M*	- Mounting according to valid application note	M6, Screw	3		6	Nm
Weight	*G*				345		g

Note: *Storage and shipment of modules with TIM => see AN2012-07*

2 MOSFET, T1 / T2

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Drain-source voltage	V_{DSS}		T_{vj} = 25 °C	1200	V
Implemented drain current	I_{DN}			500	A
Continuous DC drain current	I_{DDC}	T_{vj} = 175 °C, V_{GS} = 18 V	T_H = 65 °C	470	A
Repetitive peak drain current	I_{DRM}	verified by design, t_p limited by T_{vjmax}		1000	A
Gate-source voltage, max. transient voltage	V_{GS}	D < 0.01		-10/23	V
Gate-source voltage, max. static voltage	V_{GS}			-7/20	V

Table 4 Recommended values

Parameter	Symbol	Note or test condition	Values	Unit
On-state gate voltage	$V_{GS(on)}$		15...18	V
Off-state gate voltage	$V_{GS(off)}$		-5...0	V

Table 5 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source on-resistance	$R_{DS(on)}$	I_D = 500 A	V_{GS} = 15 V, T_{vj} = 25 °C		1.75		mΩ
			V_{GS} = 18 V, T_{vj} = 25 °C		1.46	1.91	
			V_{GS} = 18 V, T_{vj} = 125 °C		2.36		
			V_{GS} = 18 V, T_{vj} = 175 °C		3.13		
Gate threshold voltage	$V_{GS(th)}$	I_D = 224 mA, V_{DS} = V_{GS}, T_{vj} = 25 °C, (tested after 1ms pulse at V_{GS} = +20 V)		3.45	4.3	5.15	V
Total gate charge	Q_G	V_{DD} = 800 V, V_{GS} = -3/18 V, T_{vj} = 25 °C			1.6		µC
Internal gate resistor	R_{Gint}	T_{vj} = 25 °C			0.9		Ω
Input capacitance	C_{ISS}	f = 100 kHz, V_{DS} = 800 V, V_{GS} = 0 V	T_{vj} = 25 °C		48.4		nF
Output capacitance	C_{OSS}	f = 100 kHz, V_{DS} = 800 V, V_{GS} = 0 V	T_{vj} = 25 °C		2.4		nF

(table continues...)

Table 5 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Reverse transfer capacitance	C_{rss}	f = 100 kHz, V_{DS} = 800 V, V_{GS} = 0 V	T_{vj} = 25 °C		0.158		nF
C_{OSS} stored energy	E_{OSS}	V_{DS} = 800 V, V_{GS} = -3/18 V, T_{vj} = 25 °C			945		µJ
Drain-source leakage current	I_{DSS}	V_{DS} = 1200 V, V_{GS} = -3 V	T_{vj} = 25 °C		0.32	660	µA
Gate-source leakage current	I_{GSS}	V_{DS} = 0 V, T_{vj} = 25 °C	V_{GS} = 20 V			400	nA
Turn-on delay time (inductive load)	$t_{d\,on}$	I_D = 500 A, R_{Gon} = 6.8 Ω, V_{DD} = 600 V, V_{GS} = -3/18 V, t_{dead} = 1000 ns	T_{vj} = 25 °C		156		ns
			T_{vj} = 125 °C		172		
			T_{vj} = 175 °C		182		
Rise time (inductive load)	t_r	I_D = 500 A, R_{Gon} = 6.8 Ω, V_{DD} = 600 V, V_{GS} = -3/18 V, t_{dead} = 1000 ns	T_{vj} = 25 °C		261		ns
			T_{vj} = 125 °C		243		
			T_{vj} = 175 °C		238		
Turn-off delay time (inductive load)	$t_{d\,off}$	I_D = 500 A, R_{Goff} = 3.9 Ω, V_{DD} = 600 V, V_{GS} = -3/18 V	T_{vj} = 25 °C		276		ns
			T_{vj} = 125 °C		305		
			T_{vj} = 175 °C		319		
Fall time (inductive load)	t_f	I_D = 500 A, R_{Goff} = 3.9 Ω, V_{DD} = 600 V, V_{GS} = -3/18 V	T_{vj} = 25 °C		74		ns
			T_{vj} = 125 °C		76		
			T_{vj} = 175 °C		77		
Turn-on energy loss per pulse	E_{on}	I_D = 500 A, V_{DD} = 600 V, L_σ = 8 nH, V_{GS} = -3/18 V, R_{Gon} = 6.8 Ω, di/dt = 4.7 kA/µs (T_{vj} = 175 °C), t_{dead} = 1000 ns	T_{vj} = 25 °C		40.2		mJ
			T_{vj} = 125 °C		38.3		
			T_{vj} = 175 °C		39		
Turn-on energy loss per pulse, optimized	$E_{on,o}$	I_D = 500 A, V_{DD} = 600 V, L_σ = 8 nH, V_{GS} = -3/18 V, $R_{Gon,o}$ = 2.4 Ω, di/dt = 9.3 kA/µs (T_{vj} = 175 °C), t_{dead} = 200 ns	T_{vj} = 25 °C		16.8		mJ
			T_{vj} = 125 °C		17.1		
			T_{vj} = 175 °C		18.1		
Turn-off energy loss per pulse	E_{off}	I_D = 500 A, V_{DD} = 600 V, L_σ = 8 nH, V_{GS} = -3/18 V, R_{Goff} = 3.9 Ω, dv/dt = 6.2 kV/µs (T_{vj} = 175 °C)	T_{vj} = 25 °C		20.4		mJ
			T_{vj} = 125 °C		21.6		
			T_{vj} = 175 °C		22.2		
Thermal resistance, junction to heat sink	R_{thJH}	per MOSFET, Valid with IFX pre-applied Thermal Interface Material			0.12		K/W
Temperature under switching conditions	$T_{vj\,op}$			-40		175	°C

***Note**: The selection of positive and negative gate-source voltages impacts losses and the long-term behavior of the MOSFET and body diode. The design guidelines described in Application Notes AN 2018-09 and AN 2021-13 must be considered to ensure sound operation of the device over the planned lifetime.*

Tvj op > 150°C is allowed for operation at overload conditions for MOSFET and body diode. For detailed specifications, please refer to AN 2021-13.

3 Body diode (MOSFET, T1 / T2)

Table 6 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
DC body diode forward current	I_{SD}	T_{vj} = 175 °C, V_{GS} = -3 V	T_H = 65 °C	240	A

Table 7 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Forward voltage	V_{SD}	I_{SD} = 500 A, V_{GS} = -3 V	T_{vj} = 25 °C		4.14	5.2	V
			T_{vj} = 125 °C		3.88		
			T_{vj} = 175 °C		3.78		
Peak reverse recovery current	I_{rrm}	I_{SD} = 500 A, di_s/dt = 4.7 kA/µs, V_{DD} = 600 V, V_{GS}=-3 V, t_{dead} = 1000 ns	T_{vj} = 25 °C		76		A
			T_{vj} = 125 °C		114		
			T_{vj} = 175 °C		148		
Recovered charge	Q_{rr}	I_{SD} = 500 A, di_s/dt = 4.7 kA/µs, V_{DD} = 600 V, V_{GS}=-3 V, t_{dead} = 1000 ns	T_{vj} = 25 °C		3.7		µC
			T_{vj} = 125 °C		4.9		
			T_{vj} = 175 °C		7		
Reverse recovery energy	E_{rec}	I_{SD} = 500 A, di_s/dt = 4.7 kA/µs (T_{vj} = 175 °C), V_{DD} = 600 V, V_{GS}=-3 V, t_{dead} = 1000 ns	T_{vj} = 25 °C		0.12		mJ
			T_{vj} = 125 °C		0.37		
			T_{vj} = 175 °C		0.67		
Reverse recovery energy, optimized	$E_{rec,o}$	I_{SD} = 500 A, di_s/dt = 9.3 kA/µs (T_{vj} = 175 °C), V_{DD} = 600 V, V_{GS} = -3 V, t_{dead} = 200 ns	T_{vj} = 25 °C		1.3		mJ
			T_{vj} = 125 °C		3.8		
			T_{vj} = 175 °C		5.3		

4 NTC-Thermistor

Table 8 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	R_{25}	T_{NTC} = 25 °C		5		kΩ
Deviation of R_{100}	$\Delta R/R$	T_{NTC} = 100 °C, R_{100} = 493 Ω	-5		5	%

(table continues...)

Table 8 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Power dissipation	P_{25}	T_{NTC} = 25 °C			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2\text{-}1/(298{,}15\ K))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2\text{-}1/(298{,}15\ K))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2\text{-}1/(298{,}15\ K))]$		3433		K

***Note**: For an analytical description of the NTC characteristics please refer to AN2009-10, chapter 4.*

5 Characteristics diagrams

Output characteristic (typical), MOSFET, T1 / T2
$I_D = f(V_{DS})$
V_{GS} = 18 V



Output characteristic (typical), MOSFET, T1 / T2
$I_D = f(V_{DS})$
V_{GS} = 15 V



Output characteristic field (typical), MOSFET, T1 / T2
$I_D = f(V_{DS})$
T_{vj} = 175 °C



Drain source on-resistance (typical), MOSFET, T1 / T2
$R_{DS(on)} = f(I_D)$
V_{GS} = 18 V



Drain source on-resistance (typical), MOSFET, T1 / T2

$R_{DS(on)} = f(T_{vj})$
$I_D = 500$ A



Transfer characteristic (typical), MOSFET, T1 / T2

$I_D = f(V_{GS})$
$V_{DS} = 20$ V



Gate-source threshold voltage (typical), MOSFET, T1 / T2

$V_{GS(th)} = f(T_{vj})$
$V_{GS} = V_{DS}$



Gate charge characteristic (typical), MOSFET, T1 / T2

$V_{GS} = f(Q_G)$
$I_D = 500$ A, $T_{vj} = 25$ °C



Capacity characteristic (typical), MOSFET, T1 / T2

$C = f(V_{DS})$

T_{vj} = 25 °C, V_{GS} = 0 V, f = 100 kHz



Switching times (typical), MOSFET, T1 / T2

$t = f(I_D)$

R_{Goff} = 3.9 Ω, V_{DD} = 600 V, T_{vj} = 175 °C, V_{GS} = -3/18 V



Switching times (typical), MOSFET, T1 / T2

$t = f(I_D)$

V_{DD} = 600 V, R_{Gon} = 6.8 Ω, $R_{Gon,o}$ = 2.4 Ω, T_{vj} = 175 °C, V_{GS} = -3/18 V



Switching times (typical), MOSFET, T1 / T2

$t = f(R_G)$

V_{DD} = 600 V, t_{dead} = 1000 ns, I_D = 500 A, T_{vj} = 175 °C, V_{GS} = -3/18 V



Current slope (typical), MOSFET, T1 / T2

$di/dt = f(R_G)$

V_{DD} = 600 V, I_D = 500 A, V_{GS} = -3/18 V



Voltage slope (typical), MOSFET, T1 / T2

$dv/dt = f(R_G)$

V_{DD} = 600 V, I_D = 500 A, V_{GS} = -3/18 V



Switching losses (typical), MOSFET, T1 / T2

$E_{on} = f(I_D)$

V_{DD} = 600 V, R_{Gon} = 6.8 Ω, $R_{Gon,o}$ = 2.4 Ω, V_{GS} = -3/18 V



Switching losses (typical), MOSFET, T1 / T2

$E_{off} = f(I_D)$

R_{Goff} = 3.9 Ω, V_{DD} = 600 V, V_{GS} = -3/18 V



Switching losses (typical), MOSFET, T1 / T2

$E = f(R_G)$

V_{DD} = 600 V, t_{dead} = 1000 ns, I_D = 500 A, V_{GS} = -3/18 V



Switching losses (typical), MOSFET, T1 / T2

$E_{on} = f(V_{GS(off)})$

R_{Goff} = 3.9 Ω, V_{DD} = 600 V, R_{Gon} = 6.8 Ω, $V_{GS(on)}$ = 18 V, I_D = 500 A, $R_{Gon,o}$ = 2.4 Ω, T_{vj} = 175 °C



Switching losses (typical), MOSFET, T1 / T2

$E_{on} = f(t_{dead})$

R_{Gon} = 6.8 Ω, I_D = 500 A, V_{DD} = 600 V, V_{GS} = -3/18 V



Transient thermal impedance, MOSFET, T1 / T2

$Z_{th} = f(t)$



Forward characteristic body diode (typical), MOSFET, T1 / T2

$I_{SD} = f(V_{SD})$
$T_{vj} = 25\ °C$



Forward voltage of body diode (typical), MOSFET, T1 / T2

$V_{SD} = f(T_{vj})$
$I_{SD} = 500\ A$



Switching losses body diode (typical), MOSFET, T1 / T2

$E_{rec} = f(I_{SD})$
$R_{Gon} = 6.8\ \Omega$, $R_{Gon,o} = 2.4\ \Omega$, $V_{DD} = 600\ V$



Switching losses body diode (typical), MOSFET, T1 / T2

$E_{rec} = f(R_G)$
$t_{dead} = 1000\ ns$, $I_{SD} = 500\ A$, $V_{DD} = 600\ V$



Switching losses body diode (typical), MOSFET, T1 / T2

$E_{rec} = f(V_{GS(off)})$

R_{Goff} = 3.9 Ω, R_{Gon} = 6.8 Ω, $V_{GS(on)}$ = 18 V, I_{SD} = 500 A, $R_{Gon,o}$ = 2.4 Ω, V_{DD} = 600 V, T_{vj} = 175 °C



Switching losses body diode (typical), MOSFET, T1 / T2

$E_{rec} = f(t_{dead})$

R_{Gon} = 6.8 Ω, I_D = 500 A, V_{DD} = 600 V, V_{GS} = -3/18 V



Temperature characteristic (typical), NTC-Thermistor

$R = f(T_{NTC})$



6 Circuit diagram



Figure 1

7 Package outlines



Figure 2

8 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	*Content* Module serial number Module material number Production order number Date code (production year) Date code (production week)	*Digit* 1 – 5 6 - 11 12 - 19 20 – 21 22 – 23	*Example* 71549 142846 55054991 15 30
Example	7154914284655054991530		7154914284655054991530

Figure 3

Revision history

Document revision	Date of release	Description of changes
1.00	2024-12-02	Final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2024-12-02

Published by

Infineon Technologies AG

81726 Munich, Germany

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABM269-001

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.