
IC-3173

Specifications

2022-06-30



Contents

Introduction..... 3

Introduction

This document provides the specifications for the IC-3173. Specifications are subject to change without notice. Refer to the National Instruments Product Manuals Library at ni.com/manuals for the most recent versions of product documentation.

Characteristics/Nominal Specifications describe basic functions and attributes of the device established by design.

Physical Characteristics



Caution You can impair the protection provided by the IC-3173 if you use it in a manner not described in this document.

To clean the IC-3173, wipe it with a dry towel.

Dimensions	17.4 cm × 9.3 cm × 16.8 cm (6.9 in × 3.7 in × 6.6 in)
Weight	3.039 kg (6 lbs, 11 oz)

Processor

Type	Intel Core i7-5650U
Base frequency	2.2 GHz
Maximum frequency	3.1 GHz
On-die cache	4 MB

Operating System

Supported Operating Systems	NI Linux Real-Time 64-bit, Windows Embedded Standard 7 64-bit
-----------------------------	--

Memory

System RAM	
Capacity	8 GB
Type	DDR3L
Speed	1600 MT/s
Nonvolatile storage	
Capacity	4 GB, 32 GB, or 64 GB

Power Requirements



Note Supply voltages are measured at the IC-3173 power connectors.

System power (V_1, V_2)	
Supply voltage	9 to 30 VDC, 21.6 to 30 VDC when using Power over Ethernet (PoE)
Maximum power input	150 W
Isolated-output power (V_{ISO})	

Supply voltage	4.5 to 30 VDC
User-replaceable battery	3V BR2032 lithium-carbon monofluoride coin cell, rated to 85 °C

Reconfigurable FPGA

Type	Xilinx Kintex-7 XC7K160T
Number of flip-flops	202,800
Number of 6-input LUTs	101,400
Number of DSP48E1 slices (18 × 25 multipliers)	600
Embedded block RAM	11,700 kbits
Number of DMA channels	32
Number of logical interrupts	32

FPGA External Memory

DRAM	
Density	2 GB
Type	DDR3L
Maximum theoretical data rate	5.33 GB/s
SRAM	

Density	4.5 MB
Type	QDR-II+
Maximum sustainable data rate	
Read	3.15 GB/s
Write	3.15 GB/s
Combined	6.3 GB/s

Network Port

Standard	IEEE 802.3 Ethernet, 10BASE-T, 100BASE-TX, 1000BASE-T
Interface	RJ45
Speed	10, 100, 1000 Mbps

PoE-Capable Network Ports

Number of ports	4
Standards	IEEE 802.3 Ethernet, 10BASE-T, 100BASE-TX, 100BASE-T, IEEE 802.3af (PoE) compatible
Interface	RJ45
Speed	10, 100, 1000 Mbps

Supported PoE power classes	0, 1, 2, 3
PoE power output (per port)	15.4 W
Recommended port for IEEE 1588 grandmaster connection	PoE1

USB 3.0 Ports

Number of ports	2
Type	USB 3.0, SuperSpeed
Speed	5 GB/s
Maximum current	900 mA, per port

USB 2.0 Ports

Number of ports	4
Type	USB 2.0, Hi-Speed
Speed	480 Mbit/s
Maximum current	1 A, shared across each pair of ports

DisplayPort

Number of ports	2
-----------------	---

Maximum resolution	3840 × 2160 at 60 Hz
--------------------	----------------------

RS-485/422/232 Serial Port

Interface	RJ50
Maximum baud rate	115,200 bps
Data bits	5, 6, 7, 8
Stop bits	1, 1.5, 2
Parity	Odd, Even, Mark, Space
Flow control	None
Wire mode	4-wire, 2-wire, 2-wire auto

TTL Inputs/Outputs

Number of channels	8
Type	Bidirectional
Output voltage range	0 V to 5 V
Maximum pulse rate	2 MHz
Minimum pulse detected	500 ns
Power-on state	Input (high-impedance), 10 k Ω pull-up to 5 V

Logic levels

Input low voltage	0.59 V maximum
Input high voltage	2.57 V minimum
Output low voltage	0.38 V maximum at 1.5 mA
Output high voltage	4.12 V minimum at 1.5 mA

Differential Inputs/Outputs

Number of channels	2
Types	Bidirectional RS-422/RS-485 or single-ended input
Maximum pulse rate	5 MHz, differential
Differential input threshold	± 200 mV
Differential output voltage	2.0 V min ($R_{LOAD} = 100 \Omega$, RS-422)
Input voltage range	0 V to 5.5 V

TTL-compatible single-ended logic levels

Input low voltage	0.8 V
Input high voltage	2.0 V

Isolated Inputs

Type	Current sinking
Number of channels	8
Input voltage	
Input voltage range	0 V to 24 V
Input OFF voltage	0 V to 2.0 V
Input ON voltage	3.3 V to 24 V
Turn-on current	2.5 mA
Maximum pulse rate	100 kHz
Minimum pulse detected	10 μ s
Input protection	
Reverse polarity protection	Yes, -30 V
Input voltage (channel to C _{ISO})	30 V maximum
Input current	3.3 mA, internally limited

Isolated Outputs

Type	Current sourcing
------	------------------

Number of channels	8
Supply voltage (V_{ISO})	
Supply voltage range (V_{ISO})	4.5 to 30 VDC
Reverse polarity protection	Yes, -30 V
Maximum output voltage drop	
$V_{ISO} = 5\text{ V}$	1.08 V at 35 mA
$V_{ISO} = 24\text{ V}$	1.18 V at 80 mA
Maximum output current	
$V_{ISO} = 5\text{ V}$	35 mA
$V_{ISO} = 24\text{ V}$	80 mA
Maximum current limit	345 mA
Minimum pulse rate	2.5 kHz (load of 100 k Ω , 300 pF)
Maximum pulse rate	20 kHz (load of 10 k Ω , 300 pF)
Minimum pulse generated	400 μs



Note The isolated outputs have a current limit which will turn off the outputs in case the limit is exceeded. The circuit resets when the output is turned off. Do not draw more than 100 mA from any 24 V isolated output. Do not draw more than 50 mA from any 5 V isolated output. Do not draw

more than 640 mA combined from the V_{ISO} pins on the 44-pin D-SUB connector.

Environmental

Indoor use only.

Ingress protection (IEC 60529)	IP20
Temperature (IEC 60068-2-1 and IEC 60068-2-2) Operating 0 °C to 55 °C, 0 °C to 50 °C when Power over Ethernet (PoE) exceeds 30 W Storage -20 °C to 85 °C	
Operating humidity (IEC 60068-2-56)	10% RH to 90% RH, noncondensing
Storage humidity (IEC 60068-2-56)	5% RH to 95% RH, noncondensing
Pollution degree (IEC 60664)	2
Maximum Altitude	2,000 m
Operating shock (IEC 60068-2-27)	50 g, 3 ms half sine, 3 shocks per side 30 g, 11 ms half sine, 3 shocks per side
Operating vibration Random (IEC 60068-2-64) 10 to 500 Hz, 5 grms Swept Sine (IEC 60068-2-6) 10 to 500 Hz, 5 g	

Safety

This product is designed to meet the requirements of the following electrical equipment safety standards for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1



Note For UL and other safety certifications, refer to the product label or the [Online Product Certification](#) section.

Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326-1 (IEC 61326-1): Class A emissions; Industrial immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- EN 55022 (CISPR 22): Class A emissions
- EN 55024 (CISPR 24): Immunity
- AS/NZS CISPR 11: Group 1, Class A emissions
- AS/NZS CISPR 22: Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



Note In the United States (per FCC 47 CFR), Class A equipment is intended for use in commercial, light-industrial, and heavy-industrial locations. In Europe, Canada, Australia and New Zealand (per CISPR 11) Class A equipment is intended for use only in heavy-industrial locations.



Note Group 1 equipment (per CISPR 11) is any industrial, scientific, or medical equipment that does not intentionally generate radio frequency energy for the treatment of material or inspection/analysis purposes.



Note For EMC declarations and certifications, and additional information, refer to the [Online Product Certification](#) section.

CE Compliance

This product meets the essential requirements of applicable European Directives, as follows:

- 2014/35/EU; Low-Voltage Directive (safety)
- 2014/30/EU; Electromagnetic Compatibility Directive (EMC)

Product Certifications and Declarations


Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for NI products, visit ni.com/product-certifications, search by model number, and click the appropriate link.

Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the **Engineering a Healthy Planet** web page at ni.com/environment. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

EU and UK Customers

-  Waste Electrical and Electronic Equipment (WEEE)—At the end of the product life cycle, all NI products must be disposed of according to local laws and regulations. For more information about how to recycle NI products in your region, visit ni.com/environment/weee.

Battery Replacement and Disposal

Battery Directive This device contains a long-life coin cell battery. Refer to the device user manual for instructions on changing the battery. Dispose of this battery separately from municipal waste. For more information about compliance with the EU Battery Directive 2006/66/EC about Batteries and Accumulators and Waste Batteries and Accumulators, visit ni.com/environment/batterydirective.

电子信息产品污染控制管理办法 (中国 RoHS)

-  中国 RoHS— NI 符合中国电子信息产品中限制使用某些有害物质指令(RoHS)。关于 NI 中国 RoHS 合规性信息，请登录 ni.com/environment/rohs_china。(For information about China RoHS compliance, go to ni.com/environment/rohs_china.)

Where to Go Next

The following documents and resources contain information you may find helpful as you use the IC-3173 in an application. Refer to the National Instruments Product Manuals Library at <http://www.ni.com/manuals> for the most recent versions of product documentation.

- **IC-317x Getting Started Guide** —Explains how to install and configure the device.

- **IC-317x User Manual** —Contains connector pinouts, configuration information, mounting information, and answers to common troubleshooting questions.
- **NI CVS I/O Accessory User Manual** —Contains installation and operation instructions for the CVS I/O Accessory.

NI Services

Visit ni.com/support to find support resources including documentation, downloads, and troubleshooting and application development self-help such as tutorials and examples.

Visit ni.com/services to learn about NI service offerings such as calibration options, repair, and replacement.

Visit ni.com/register to register your NI product. Product registration facilitates technical support and ensures that you receive important information updates from NI.

NI corporate headquarters is located at 11500 N Mopac Expwy, Austin, TX, 78759-3504, USA.