



Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 22

LOCTITE SI 5368 BK CR310ML EGFD

SDS No. : 164824

V011.0

Revision: 20.10.2026

printing date: 21.10.2026

Replaces version from: 01.07.2026

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE SI 5368 BK CR310ML EGFD

UFI: RPST-AXUA-320W-3H6V

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Silicone sealant

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

SDSinfo.Adhesive@henkel.com

For Safety Data Sheet updates please visit our website www.mysds.henkel.com or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation

Category 2

H315 Causes skin irritation.

Serious eye irritation

Category 2

H319 Causes serious eye irritation.

Very persistent and very bioaccumulative

EUH441 Strongly accumulates in the environment and living organisms including in humans.

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Contains

Octamethylcyclotetrasiloxane

Decamethylcyclopentasiloxane

Dodecamethylcyclohexasiloxane

Signal word: Danger

Hazard statement: H315 Causes skin irritation.
H319 Causes serious eye irritation.
EUH441 Strongly accumulates in the environment and living organisms including in humans.

Precautionary statement: P201 Obtain special instructions before use.
Prevention P273 Avoid release to the environment.

Precautionary statement: P302+P352 IF ON SKIN: Wash with plenty of soap and water.
Response P337+P313 If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

None if used properly.
Self-classification according to Article 12(b) of (EU) 1272/2008.

Following substances are present in a concentration $\geq 0,1\%$ and are identified as ED or PBT/vPvB on the REACH Candidate list or according to BPR or PPP:

Octamethylcyclotetrasiloxane 556-67-2	PBT vPvB
Decamethylcyclopentasiloxane 541-02-6	PBT vPvB
Dodecamethylcyclohexasiloxane 540-97-6	PBT vPvB

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS No. EC No UK-REACH-Reg. No.	Concentration	Classification	Specific Conc. Limits, M-factors and ATEs	Add. Information
Methyltriacetoxysilane 4253-34-3 224-221-9	1- < 3 %	Skin Corr. 1C, H314 Eye Dam. 1, H318 Acute Tox. 4, H302		
Octamethylcyclotetrasiloxane 556-67-2 209-136-7 UK-01-7989296603-1-0015	0,25- < 1 %	Aquatic Chronic 1, H410 Repr. 2, H361f Flam. Liq. 3, H226 PBT EUH440 vPvB EUH441	M chronic = 10	SVHC
Decamethylcyclopentasiloxane 541-02-6 208-764-9	0,1- < 1 %	PBT EUH440 vPvB EUH441		SVHC
Dodecamethylcyclohexasiloxane 540-97-6 208-762-8	0,1- < 1 %	PBT EUH440 vPvB EUH441		SVHC

If no ATE values are displayed, please refer to LD/LC50 values in Section 11.
For full text of the H - statements and other abbreviations see section 16 "Other information".

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

EYE: Irritation, conjunctivitis.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

water, carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.
Silicon dioxide

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes.
Ensure adequate ventilation.
Wear protective equipment.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.
For large spills absorb onto inert absorbent material and place in sealed container for disposal.
Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid skin and eye contact.
See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.
Do not eat, drink or smoke while working.
Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.
Refer to Technical Data Sheet.
Never allow product to get in contact with water during storage

7.3. Specific end use(s)

Silicone sealant

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**Valid for
Great Britain

None

Occupational Exposure LimitsValid for
Ireland

None

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Methylsilanetriyl triacetate 4253-34-3	sediment (freshwater)				0,75 mg/kg		
Methylsilanetriyl triacetate 4253-34-3	sediment (marine water)				0,075 mg/kg		
Methylsilanetriyl triacetate 4253-34-3	Soil				7,1 mg/kg		
Methylsilanetriyl triacetate 4253-34-3	Predator						no potential for bioaccumulation
Octamethylcyclotetrasiloxane 556-67-2	aqua (freshwater)		0,0015 mg/l				
Octamethylcyclotetrasiloxane 556-67-2	aqua (marine water)		0,00015 mg/l				
Octamethylcyclotetrasiloxane 556-67-2	sewage treatment plant (STP)		10 mg/l				
Octamethylcyclotetrasiloxane 556-67-2	sediment (freshwater)				3 mg/kg		
Octamethylcyclotetrasiloxane 556-67-2	sediment (marine water)				0,3 mg/kg		
Octamethylcyclotetrasiloxane 556-67-2	oral				41 mg/kg		
Octamethylcyclotetrasiloxane 556-67-2	Soil				4,2 mg/kg		
Decamethylcyclopentasiloxane 541-02-6	aqua (freshwater)		0,0012 mg/l				
Decamethylcyclopentasiloxane 541-02-6	aqua (marine water)		0,00012 mg/l				
Decamethylcyclopentasiloxane 541-02-6	sewage treatment plant (STP)		10 mg/l				
Decamethylcyclopentasiloxane 541-02-6	sediment (freshwater)				11 mg/kg		
Decamethylcyclopentasiloxane 541-02-6	sediment (marine water)				1,1 mg/kg		
Decamethylcyclopentasiloxane 541-02-6	Soil				2,54 mg/kg		
Decamethylcyclopentasiloxane 541-02-6	oral				16 mg/kg		
Dodecamethylcyclohexasiloxane 540-97-6	sediment (freshwater)				13,5 mg/kg		
Dodecamethylcyclohexasiloxane 540-97-6	oral				66,7 mg/kg		
Dodecamethylcyclohexasiloxane 540-97-6	sediment (marine water)				1,35 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Methylsilanetriyl triacetate 4253-34-3	Workers	inhalation	Long term exposure - systemic effects		25 mg/m3	no potential for bioaccumulation
Methylsilanetriyl triacetate 4253-34-3	Workers	inhalation	Acute/short term exposure - systemic effects		25 mg/m3	no potential for bioaccumulation
Methylsilanetriyl triacetate 4253-34-3	Workers	dermal	Long term exposure - systemic effects		14,5 mg/kg	no potential for bioaccumulation
Methylsilanetriyl triacetate 4253-34-3	Workers	dermal	Acute/short term exposure - systemic effects		14,5 mg/kg	no potential for bioaccumulation
Methylsilanetriyl triacetate 4253-34-3	General population	inhalation	Long term exposure - local effects		5,1 mg/m3	no potential for bioaccumulation
Methylsilanetriyl triacetate 4253-34-3	General population	inhalation	Acute/short term exposure - local effects		5,1 mg/m3	no potential for bioaccumulation
Methylsilanetriyl triacetate 4253-34-3	General population	dermal	Long term exposure - systemic effects		7,2 mg/kg	no potential for bioaccumulation
Methylsilanetriyl triacetate 4253-34-3	General population	dermal	Acute/short term exposure - systemic effects		7,2 mg/kg	no potential for bioaccumulation
Methylsilanetriyl triacetate 4253-34-3	General population	oral	Long term exposure - systemic effects		1 mg/kg	no potential for bioaccumulation
Methylsilanetriyl triacetate 4253-34-3	General population	oral	Acute/short term exposure - systemic effects		1 mg/kg	no potential for bioaccumulation
Octamethylcyclotetrasiloxane 556-67-2	Workers	inhalation	Long term exposure - systemic effects		73 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	Workers	inhalation	Long term exposure - local effects		73 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	inhalation	Long term exposure - systemic effects		13 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	inhalation	Long term exposure - local effects		13 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	oral	Long term exposure - systemic effects		3,7 mg/kg	
Decamethylcyclopentasiloxane 541-02-6	Workers	inhalation	Long term exposure - systemic effects		97,3 mg/m3	
Decamethylcyclopentasiloxane 541-02-6	Workers	inhalation	Long term exposure - local effects		24,2 mg/m3	
Decamethylcyclopentasiloxane 541-02-6	General population	oral	Long term exposure - systemic effects		5 mg/kg	
Decamethylcyclopentasiloxane 541-02-6	General population	inhalation	Long term exposure - systemic effects		17,3 mg/m3	
Decamethylcyclopentasiloxane 541-02-6	General population	inhalation	Long term exposure - local effects		4,3 mg/m3	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Delivery form	paste
Colour	Black
Odor	Vinegar
Physical state	solid
Melting point	Not applicable
Initial boiling point	Not determined
Flammability	The product is not flammable.
Explosive limits	Not applicable, The product is not flammable.
Flash point	> 150 °C (> 302 °F)
Auto-ignition temperature	Not applicable, The product is not flammable.
Decomposition temperature	> 200 °C (> 392 °F);
pH	Not applicable, Product is non-soluble (in water).
Viscosity (kinematic)	Currently under determination
Solubility (qualitative) (20 °C (68 °F); Solvent: Water)	Partially soluble
Solubility (qualitative) (20 °C (68 °F); Solvent: Acetone)	Insoluble
Solubility (qualitative) (Solvent: Ethanol)	Insoluble

Solubility (qualitative) (Solvent: White spirit)	Partially soluble
Solubility (qualitative) (Solvent: aromatic hydrocarbons)	Partially soluble
Partition coefficient: n-octanol/water	Not applicable
Vapour pressure (20 °C (68 °F))	Mixture < 0,1 mm hg
Density (20 °C (68 °F))	1,04 g/cm3 None
Relative vapour density: (20 °C)	Heavier than air.
Particle characteristics	Not applicable Product is a liquid

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with oxidants, acids and lyes

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.
Excessive heat.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

None if used for intended purpose.

SECTION 11: Toxicological information**General toxicological information:**

Acetic acid is liberated slowly upon contact with moisture.

Acetic acid released during polymerisation of acetoxycuring RTV silicones is irritating to the eyes

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Based on available data, the classification criteria are not met.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Methyltriacetoxysilane 4253-34-3	LD50	1.600 mg/kg	rat	OECD Guideline 401 (Acute Oral Toxicity)
Octamethylcyclotetrasiloxane 556-67-2	LD50	> 4.800 mg/kg	rat	equivalent or similar to OECD Guideline 401 (Acute Oral Toxicity)
Decamethylcyclopentasiloxane 541-02-6	LD50	> 5.000 mg/kg	rat	equivalent or similar to OECD Guideline 401 (Acute Oral Toxicity)
Dodecamethylcyclohexasiloxane 540-97-6	LD50	> 2.000 mg/kg	rat	OECD Guideline 423 (Acute Oral toxicity)

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Based on available data, the classification criteria are not met.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	LD50	> 2.375 mg/kg	rat	equivalent or similar to OECD Guideline 402 (Acute Dermal Toxicity)
Decamethylcyclopentasiloxane 541-02-6	LD50	> 2.000 mg/kg	rabbit	equivalent or similar to OECD Guideline 402 (Acute Dermal Toxicity)
Dodecamethylcyclohexasiloxane 540-97-6	LD50	> 2.000 mg/kg	rat	OECD Guideline 402 (Acute Dermal Toxicity)

Acute inhalative toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Based on available data, the classification criteria are not met.

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	LC50	36 mg/l	dust/mist	4 h	rat	OECD Guideline 403 (Acute Inhalation Toxicity)
Decamethylcyclopentasiloxane 541-02-6	LC50	8,67 mg/l	dust/mist	4 h	rat	OECD Guideline 403 (Acute Inhalation Toxicity)

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	corrosive	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
Octamethylcyclotetrasiloxane 556-67-2	not irritating		rabbit	equivalent or similar to OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
Decamethylcyclopentasiloxane 541-02-6	not irritating	24 h	rabbit	equivalent or similar to OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
Dodecamethylcyclohexasiloxane 540-97-6	not irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	Category 1 (irreversible effects on the eye)		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Octamethylcyclotetrasiloxane 556-67-2	not irritating		rabbit	equivalent or similar to OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Decamethylcyclopentasiloxane 541-02-6	not irritating		rabbit	equivalent or similar to OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Dodecamethylcyclohexasiloxane 540-97-6	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Based on available data, the classification criteria are not met.

Hazardous substances CAS-No.	Result	Test type	Species	Method
Methyltriacetoxysilane 4253-34-3	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)
Octamethylcyclotetrasiloxane 556-67-2	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)
Decamethylcyclopentasiloxane 541-02-6	not sensitising	Mouse local lymphnode assay (LLNA)	mouse	equivalent or similar to OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)
Dodecamethylcyclohexasiloxane 540-97-6	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Based on available data, the classification criteria are not met.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Methyltriacetoxysilane 4253-34-3	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Methyltriacetoxysilane 4253-34-3	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Octamethylcyclotetrasilox ane 556-67-2	negative	bacterial gene mutation assay	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Octamethylcyclotetrasilox ane 556-67-2	negative	in vitro mammalian chromosome aberration test	with and without		equivalent or similar to OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Octamethylcyclotetrasilox ane 556-67-2	negative	mammalian cell gene mutation assay	with and without		equivalent or similar to OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Decamethylcyclopentasilox ane 541-02-6	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Decamethylcyclopentasilox ane 541-02-6	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Decamethylcyclopentasilox ane 541-02-6	negative	mammalian cell gene mutation assay	with and without		equivalent or similar to OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Dodecamethylcyclohexasilox ane 540-97-6	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Dodecamethylcyclohexasilox ane 540-97-6	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Octamethylcyclotetrasilox ane 556-67-2	negative	inhalation		rat	equivalent or similar to OECD Guideline 475 (Mammalian Bone Marrow Chromosome Aberration Test)
Octamethylcyclotetrasilox ane 556-67-2	negative	oral: gavage		rat	equivalent or similar to OECD Guideline 478 (Genetic Toxicology: Rodent Dominant Lethal Test)
Decamethylcyclopentasilox ane 541-02-6	negative	inhalation		rat	OECD Guideline 486 (Unscheduled DNA Synthesis (UDS) Test with Mammalian Liver Cells in vivo)
Decamethylcyclopentasilox ane 541-02-6	negative	inhalation: vapour		rat	OECD Guideline 474 (Mammalian Erythrocyte Micronucleus Test)
Dodecamethylcyclohexasilox ane 540-97-6	negative	intraperitoneal		mouse	OECD Guideline 474 (Mammalian Erythrocyte Micronucleus Test)

Carcinogenicity

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Based on available data, the classification criteria are not met.

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Sex	Method
Decamethylcyclopentasiloxane 541-02-6	not carcinogenic	inhalation: vapour	2 y 6 h/d, 5 d/w	rat	male/female	EPA OPPTS 870.4300 (Combined Chronic Toxicity / Carcinogenicity)

Reproductive toxicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Based on available data, the classification criteria are not met.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
Methyltriacetoxysilane 4253-34-3	NOAEL P $\geq$ 1.000 mg/kg NOAEL F1 $\geq$ 1.000 mg/kg	screening	oral: gavage	rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)
Octamethylcyclotetrasiloxane 556-67-2	NOAEL P 300 ppm NOAEL F1 300 ppm	two- generation study	inhalation	rat	equivalent or similar to OECD Guideline 416 (Two- Generation Reproduction Toxicity Study)
Decamethylcyclopentasiloxane 541-02-6	NOAEL P $\geq$ 2,496 mg/l NOAEL F1 $\geq$ 2,496 mg/l NOAEL F2 $\geq$ 2,496 mg/l	two- generation study	inhalation: vapour	rat	EPA OPPTS 870.3800 (Reproduction and Fertility Effects)
Dodecamethylcyclohexasiloxane 540-97-6	NOAEL P 1.000 mg/kg NOAEL F1 1.000 mg/kg	screening	oral: gavage	rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)

STOT-single exposure:

No data available.

STOT-repeated exposure:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Based on available data, the classification criteria are not met.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
Methyltriacetoxysilane 4253-34-3	NOAEL 50 mg/kg	oral: gavage	28 - 51 d	rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)
Octamethylcyclotetrasiloxane 556-67-2	LOAEL 35 ppm	inhalation	6 h nose only inhalation 5 days/week for 13 weeks	rat	OECD Guideline 412 (Repeated Dose Inhalation Toxicity: 28/14-Day)
Octamethylcyclotetrasiloxane 556-67-2	NOAEL 960 mg/kg	dermal	3 Weeks	rabbit	equivalent or similar to OECD Guideline 410 (Repeated Dose Dermal Toxicity: 21/28-Day Study)
Decamethylcyclopentasiloxane 541-02-6	NOAEL $\geq$ 1.000 mg/kg	oral: gavage	90 d	rat	OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity in Rodents)
Decamethylcyclopentasiloxane 541-02-6	NOAEL $\geq$ 2,42 mg/l	inhalation: vapour	2 years	rat	equivalent or similar to OECD Guideline 453 (Combined Chronic Toxicity / Carcinogenicity Studies)
Decamethylcyclopentasiloxane 541-02-6	NOAEL $\geq$ 1.600 mg/kg	oral: gavage	28 d	rat	equivalent or similar to OECD Guideline 410 (Repeated Dose Dermal Toxicity: 21/28-Day Study)
Dodecamethylcyclohexasiloxane 540-97-6	NOAEL 1.000 mg/kg	oral: gavage	29 d	rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)

Aspiration hazard:

No data available.

11.2 Information on other hazards**11.2.1 Endocrine disrupting properties**

No substance data available.

No data available.

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains / surface water / ground water.
Self-classification according to Article 12(b) of (EU) 1272/2008.

12.1. Toxicity**Toxicity (Fish):**

LC50 (fish) > 100 mg/l (expert judgement)
NOEC (fish) > 1 mg/l (expert judgement)

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	LC50	> 110 mg/l	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Octamethylcyclotetrasiloxane 556-67-2	NOEC	0,0044 mg/l	93 d	Salmo gairdneri (new name: Oncorhynchus mykiss)	EPA OPPTS 797.1600 (Fish Early Life Stage Toxicity Test)
Octamethylcyclotetrasiloxane 556-67-2	LC50	No toxicity at the limit of solubility.	96 h	Oncorhynchus mykiss	EPA OTS 797.1400 (Fish Acute Toxicity Test)
Decamethylcyclopentasiloxane 541-02-6	LC50	No toxicity at the limit of solubility.	96 h	Leuciscus idus	OECD Guideline 204 (Fish, Prolonged Toxicity Test: 14-day Study)
Decamethylcyclopentasiloxane 541-02-6	NOEC	No toxicity at the limit of solubility.	90 d	Oncorhynchus mykiss	OECD Guideline 210 (fish early life stage toxicity test)
Dodecamethylcyclohexasiloxane 540-97-6	NOEC		90 d	Oncorhynchus mykiss	OECD Guideline 210 (fish early life stage toxicity test)

Toxicity (aquatic invertebrates):

EC50 (dafnia) >100 mg/l (OECD 211)

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	EC50	> 500 mg/l	48 h	Daphnia magna	EU Method C.2 (Acute Toxicity for Daphnia)
Octamethylcyclotetrasiloxane 556-67-2	EC50	No toxicity at the limit of solubility.	48 h	Daphnia magna	EPA OTS 797.1300 (Aquatic Invertebrate Acute Toxicity Test, Freshwater Daphnids)
Decamethylcyclopentasiloxane 541-02-6	EC50	No toxicity at the limit of solubility.	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity (aquatic invertebrates):

NOEC (dafnia) > 1 mg/l (OECD 211)

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	NOEC	100 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)
Octamethylcyclotetrasiloxane 556-67-2	NOEC	7.9 µg/l	21 d	Daphnia magna	EPA OTS 797.1330 (Daphnid Chronic Toxicity Test)
Decamethylcyclopentasiloxane 541-02-6	NOEC		21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

Dodecamethylcyclohexasiloxane 540-97-6	NOEC		21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)
---	------	--	------	---------------	---

Toxicity (Algae):

NOEC (Algae) > 1 mg/l (OECD 201)

EC50 (Algae) > 100 mg/l (OECD 201)

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	EC50	> 500 mg/l	72 h	Raphidocelis subcapitata (new name: Pseudokirchneriella subcapitata)	EU Method C.3 (Algal Inhibition test)
Methyltriacetoxysilane 4253-34-3	NOEC	500 mg/l	72 h	Raphidocelis subcapitata (new name: Pseudokirchneriella subcapitata)	EU Method C.3 (Algal Inhibition test)
Octamethylcyclotetrasiloxane 556-67-2	EC50		96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	EPA OTS 797.1050 (Algal Toxicity, Tiers I and II)
Octamethylcyclotetrasiloxane 556-67-2	EC10	0,022 mg/l	96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	EPA OTS 797.1050 (Algal Toxicity, Tiers I and II)
Decamethylcyclopentasiloxane 541-02-6	NOEC		96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	OECD Guideline 201 (Alga, Growth Inhibition Test)
Decamethylcyclopentasiloxane 541-02-6	EC50		96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	OECD Guideline 201 (Alga, Growth Inhibition Test)
Dodecamethylcyclohexasiloxane 540-97-6	NOEC		72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
Dodecamethylcyclohexasiloxane 540-97-6	EC50		72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity (microorganisms):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	EC10	> 100 mg/l	3 h	activated sludge of a predominantly domestic sewage	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)
Octamethylcyclotetrasiloxane 556-67-2	EC50		3 h	activated sludge	ISO 8192 (Test for Inhibition of Oxygen Consumption by Activated Sludge)
Decamethylcyclopentasiloxane 541-02-6	EC50		3 h	activated sludge, domestic	EU Method C.11 (Biodegradation: Activated Sludge Respiration Inhibition Test)

12.2. Persistence and degradability

Biodegradability (Screening Tests):

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Methyltriacetoxysilane 4253-34-3	readily biodegradable	aerobic	79,5 %	28 d	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)
Octamethylcyclotetrasiloxane 556-67-2	not readily biodegradable.	aerobic	3,7 %	29 d	OECD Guideline 310 (Ready BiodegradabilityCO ₂ in Sealed Vessels (Headspace Test)
Decamethylcyclopentasiloxane 541-02-6	not readily biodegradable.	aerobic	0,14 %	28 d	OECD Guideline 310 (Ready BiodegradabilityCO ₂ in Sealed Vessels (Headspace Test)
Dodecamethylcyclohexasiloxane 540-97-6	not readily biodegradable.	aerobic	4,47 %	28 d	OECD Guideline 310 (Ready BiodegradabilityCO ₂ in Sealed Vessels (Headspace Test)

(Bio)degradability (Simulation Tests):

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Environmental Compartment	DT50	Temperature	Method
Octamethylcyclotetrasiloxane 556-67-2	Fresh water sediment	242 d		OECD Test Guideline 308
Decamethylcyclopentasiloxane 541-02-6	Fresh water sediment	> 1.200 - 3.100 day		OECD Test Guideline 308
Dodecamethylcyclohexasiloxane 540-97-6	Fresh water sediment	> 800 - 3.100 day		OECD Test Guideline 308

12.3. Bioaccumulative potential

Partition Coefficient (octanol/water)

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	LogPow	Temperature	Method
Methyltriacetoxysilane 4253-34-3	0,25		QSAR (Quantitative Structure Activity Relationship)
Octamethylcyclotetrasiloxane 556-67-2	6,98	21,7 °C	other guideline:
Decamethylcyclopentasiloxane 541-02-6	8,07	24,6 °C	other guideline:
Dodecamethylcyclohexasiloxane 540-97-6	8,87	23,6 °C	other guideline:

Bioconcentration factor (BCF)

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Bioconcentration factor (BCF)	Exposure time	Temperature	Species	Method
Octamethylcyclotetrasiloxane 556-67-2	12.400	28 d		Pimephales promelas	EPA OTS 797.1520 (Fish Bioconcentration Test- Rainbow Trout)
Decamethylcyclopentasiloxane 541-02-6	7.060	35 d		Pimephales promelas	OECD Guideline 305 (Bioconcentration: Flow- through Fish Test)
Dodecamethylcyclohexasiloxane 540-97-6	6.605			Cyprinus carpio	OECD Guideline 305 (Bioconcentration: Flow- through Fish Test)

12.4. Mobility in soil

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	LogKoc	pH	Method
Octamethylcyclotetrasiloxane 556-67-2	4,22		OECD Guideline 106 (OECD 106: Adsorption - Desorption using a Batch Equilibrium Method)
Decamethylcyclopentasiloxane 541-02-6	5,17		OECD Guideline 106 (OECD 106: Adsorption - Desorption using a Batch Equilibrium Method)
Dodecamethylcyclohexasiloxane 540-97-6	5,9		QSAR (Quantitative Structure Activity Relationship)

12.5. Results of PBT / vPvB / PMT / vPvM assessment**PBT/vPvB**

The following table contains only substances that fulfill the criteria as PBT and/or vPvB.

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	PBT	vPvB
Octamethylcyclotetrasiloxane 556-67-2	Fulfilling PBT criteria	very Persistent and very Bioaccumulative (vPvB)
Decamethylcyclopentasiloxane 541-02-6	Fulfilling PBT criteria	very Persistent and very Bioaccumulative (vPvB)
Dodecamethylcyclohexasiloxane 540-97-6	Fulfilling PBT criteria	very Persistent and very Bioaccumulative (vPvB)

PMT/vPvM

This mixture does not contain any substances that are assessed to be a PMT or vPvM.
Based on available data, the classification criteria are not met.

12.6. Endocrine disrupting properties

No substance data available.

No data available.

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Do not empty into drains / surface water / ground water.

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09* waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information

- 14.1. UN number or ID number**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packing group**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Maritime transport in bulk according to IMO instruments**
not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Ozone Depleting Substance (ODS) (Regulation (EC) No 2024/590):	Not applicable
Prior Informed Consent (PIC) (Regulation (EU) No 649/2012):	Not applicable
Persistent organic pollutants (Regulation (EU) 2019/1021):	Not applicable

VOC content (2010/75/EC)	< 5,00 %
Seveso III (2012/18/EU):	Not applicable

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

EUH440 Accumulates in the environment and living organisms including in humans.
EUH441 Strongly accumulates in the environment and living organisms including in humans.
H226 Flammable liquid and vapour.
H302 Harmful if swallowed.
H314 Causes severe skin burns and eye damage.
H318 Causes serious eye damage.
H361f Suspected of damaging fertility.
H410 Very toxic to aquatic life with long lasting effects.

Abbreviations and acronyms:

ADG(-Code): Australian Dangerous Goods (Code)
ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR : European Agreement concerning the International Carriage of Dangerous Goods by Road
ASTM: American Society for Testing and Materials
ATE: acute toxicity estimate
AS: Australian Standard
AwSV: Ordinance on Installations for the Handling of Substances Hazardous to Water
CAS: Chemical Abstract Service
CLP: Regulation (EC) No 1272/2008
CMR: cancerogenic, mutagenic or reprotoxic
DIN: German Institute for Standardization
ECx: Effective concentration (x% effective level)
ECHA: European Chemicals Agency
EC-Nummer: Substance number in the EU-inventories EINECS/ELINCS
ECTLV: European community threshold limit value
ED: Substance identified as having endocrine disrupting properties
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
EN : European Standard
ENCS: Japanese chemical inventory
EPA: US Environmental Protection Agency
EU: European Union
EU EXPLD1: Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD2: Substance listed in Annex II, Reg (EC) No. 2019/1148
EWC: European Waste Catalogue
GHS: Globally Harmonised System for Classification and Labelling of Chemicals
GLP: Good Laboratory Practice
HSNO: Hazardous Substances and New Organisms
IARC: International Agency for Research of Cancer
IATA: International Air Transport Association
IBC-Code: International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk
IC50: half maximal inhibitory concentration
ICAO: International Civil Aviation Organization
IMDG-Code: International Maritime Code for Dangerous Goods
IMO: International Maritime Organization
ISO: International Standardization Organisation
LC50: Median lethal concentration
LD50: Median lethal dose
MARPOL: International Convention for the Prevention of Marine Pollution from Ships
n.o.s.: not otherwise specified
NO(A)EC: No (adverse) effect concentration
NO(A)EL: No (adverse) effect level
NZS: New Zealand Standard
OECD: Organisation for Economic Co-operation and Development
OEL: Occupational Exposure Limit
OPPT: US EPA Office of Pollution Prevention and Toxics
OPPTS: US EPA Office of Prevention, Pesticides and Toxic Substances
PBT: Persistent, bioaccumulative, toxic
PMT: Persistent, mobile and toxic
(Q)SAR: (Quantitative) structure–activity relationship

REACH: Regulation (EC) No. 1907/2006
RID: Regulations concerning the International Transport of Dangerous Goods by Rail
SADT: Self Accelerating Decomposition Temperature
SDS: Safety Data Sheet
STOT: Specific Target Organ Toxicity
STOT SE: Specific Target Organ Toxicity - single exposure
STOT RE: Specific Target Organ Toxicity - repeated exposure
SUSMP: Standard for the Uniform Scheduling of Medicines and Poisons
SVHC: Substance of very high concern (REACH Candidate List)
TRGS: German Technical Rules for hazardous substances
UN: United Nations
VOC: Volatile Organic Compound
814.018 VOC Reg CH: Swiss Ordinance 814.018 on the Incentive Tax on Volatile Organic Compounds
vPvB: Very persistent, very bioaccumulative
vPvM: Very persistent and very mobile
VwVwS: Administrative Regulation on Substances Hazardous to Waters
WGK: Water hazard class

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (SDSinfo.Adhesive@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.