

Product Change Notification / SYST-14UBBA015

Date:

16-Nov-2023

Product Category:

Linear Regulators

PCN Type:

Document Change

Notification Subject:

Data Sheet - TC1014/1015/1185 - 50 mA, 100 mA and 150 mA CMOS LDOs with Shutdown and Reference Bypass Data Sheet

Affected CPNs:

SYST-14UBBA015_Affected_CPN_11162023.pdf SYST-14UBBA015_Affected_CPN_11162023.csv

Notification Text:

SYST-14UBBA015

Microchip has released a new Datasheet for the TC1014/1015/1185 - 50 mA, 100 mA and 150 mA CMOS LDOs with Shutdown and Reference Bypass Data Sheet of devices. If you are using one of these devices please read the document located at TC1014/1015/1185 - 50 mA, 100 mA and 150 mA CMOS LDOs with Shutdown and Reference Bypass Data Sheet.

Data Sheet - TC1014/1015/1185 - 50 mA, 100 mA and 150 mA CMOS LDOs with Shutdown and Reference Bypass Data Sheet

Notification Status: Final

Description of Change:

Added automotive qualification to Features and examples to Product Identification System.

- Updated Absolute Maximum Ratings to better describe the part.
- Updated Section 6.0, Packaging Information.
- · Made minor text and format changes throughout the document.

Impacts to Data Sheet: None Reason for Change: To Improve Productivity Change Implementation Status: Complete Date Document Changes Effective: 16 Nov 2023 NOTE: Please be advised that this is a change to the document only the product has not been changed.

Markings to Distinguish Revised from Unrevised Devices: $\ensuremath{\mathsf{N/A}}$

Attachments:

TC1014/1015/1185 - 50 mA, 100 mA and 150 mA CMOS LDOs with Shutdown and Reference Bypass Data Sheet

Please contact your local Microchip sales office with questions or concerns regarding this notification.

Terms and Conditions:

If you wish to <u>receive Microchip PCNs via email</u> please register for our PCN email service at our PCN home page select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the PCN FAQ section.

If you wish to <u>change your PCN profile</u>, <u>including opt out</u>, please go to the <u>PCN home page</u> select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections. Affected Catalog Part Numbers (CPN)

TC1014-1.8VCT713 TC1014-2.5VCT713 TC1014-2.6VCT713 TC1014-2.7VCT713 TC1014-2.85VCT713 TC1014-2.8VCT713 TC1014-3.0VCT713 TC1014-3.0VCT713-VAO TC1014-3.1VCT713 TC1014-3.3VCT713 TC1014-3.3VCT713-VAO TC1014-3.6VCT713 TC1014-4.0VCT713 TC1014-5.0VCT713 TC1015-1.8VCT713 TC1015-1.8VCT713-V03 TC1015-2.5VCT713 TC1015-2.6VCT713 TC1015-2.6VCT713BAE TC1015-2.7VCT713 TC1015-2.85VCT713 TC1015-2.85VCT713-V02 TC1015-2.85VCT713BAF TC1015-2.8VCT713 TC1015-2.8VCT713BAB TC1015-3.0VCT713 TC1015-3.3VCT713 TC1015-3.3VCT713-VAO TC1015-3.3VCT713BAC TC1015-3.6VCT713 TC1015-4.0VCT713 TC1015-5.0VCT713 TC1185-1.8VCT713 TC1185-2.0VCT713 TC1185-2.5VCT713 TC1185-2.6VCT713 TC1185-2.7VCT713 TC1185-2.85VCT713 TC1185-2.8VCT713 TC1185-2.95VCT713 TC1185-3.0VCT713 TC1185-3.3VCT713 TC1185-3.6VCT713 TC1185-4.0VCT713 TC1185-4.15VCT713 TC1185-5.0VCT713

SYST-14UBBA015 - Data Sheet - TC1014/1015/1185 - 50 mA, 100 mA and 150 mA CMOS LDOs with Shutdown and Reference Bypass Data Sheet

TC1185-5.0VCT713-VAO



TC1014/TC1015/TC1185

50 mA, 100 mA and 150 mA CMOS LDOs with Shutdown and Reference Bypass

Features

- AEC-Q100 Automotive Qualified, See Product Identification System
- Low Supply Current (50 µA, typical)
- Low Dropout Voltage
- Choice of 50 mA (TC1014), 100 mA (TC1015) and 150 mA (TC1185) Output
- · High Output Voltage Accuracy
- · Standard or Custom Output Voltages
- · Power-Saving Shutdown Mode
- Reference Bypass Input for Ultra Low-Noise
 Operation
- · Overcurrent and Overtemperature Protection
- Space-Saving 5-Pin SOT-23 Package
- · Pin-Compatible Upgrades for Bipolar Regulators
- · Standard Output Voltage Options:
 - 1.8V, 2.5V, 2.6V, 2.7V, 2.8V, 2.85V, 3.0V, 3.3V, 3.6V, 4.0V, 5.0V

Applications

- · Battery-Operated Systems
- · Portable Computers
- · Medical Instruments
- Instrumentation
- Cellular/GSM/PHS Phones
- · Linear Post-Regulator for SMPS
- Pagers

General Description

The TC1014/TC1015/TC1185 are high accuracy (typically $\pm 0.5\%$) CMOS upgrades for older (bipolar) Low Dropout Regulators (LDOs) such as the LP2980. Designed specifically for battery-operated systems, the devices' CMOS construction eliminates wasted ground current, significantly extending battery life. Total supply current is typically 50 µA at full load (20 to 60 times lower than in bipolar regulators).

The devices' key features include ultra low-noise operation (plus optional Bypass input), fast response to step changes in load, and very low dropout voltage, typically 85 mV (TC1014), 180 mV (TC1015), and 270 mV (TC1185) at full load. Supply current is reduced to 0.5 μ A (max) and V_{OUT} falls to zero when the shutdown input is low. The devices incorporate both overtemperature and overcurrent protection.

The TC1014/TC1015/TC1185 are stable with an output capacitor of only 1 μ F and have a maximum output current of 50 mA, 100 mA and 150 mA, respectively. For higher output current regulators, refer to the Microchip Data Sheets: TC1107 (www.microchip.com/DS21356), TC1108 (www.microchip.com/DS21357), TC1173 (www.microchip.com/DS21362) (IOUT = 300 mA).

Package Type



TC1014/TC1015/TC1185

Typical Application



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings[†]

Input Voltage	6.5V
Output Voltage	(-0.3V) to (V _{IN} + 0.3V)
Power Dissipation	Internally Limited (Note 7)
Maximum Voltage on Any Pin	V _{IN} +0.3V to -0.3V
Operating Temperature Range	40°C < T _J < 125°C
Storage Temperature	65°C to +150°C
ESD Protection on all pins ⁽¹⁾ :	
Human Body Model	±2000V
Machine Model	±200V
Charged Device Model	±2000V

- **†** Notice: Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions above those indicated in the operation sections of the specifications is not implied. Exposure to Absolute Maximum Rating conditions for extended periods may affect device reliability.
- Note 1: Testing was performed per AEC-Q100 standard. For additional information, please contact your local Microchip sales office.

TC1014/TC1015/TC1185 ELECTRICAL SPECIFICATIONS

Electrical Specifications: $V_{IN} = V_R + 1V$, $I_L = 100 \mu$ A, $C_L = 1.0 \mu$ F, $\overline{SHDN} > V_{IH}$, $T_A = +25^{\circ}$ C, unless otherwise noted. Boldface type specifications apply for junction temperatures of -40°C to +125°C.

,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,				1		1	
Parameter	Sym.	Min.	Тур.	Max.	Units	Device	Conditions
Input Operating Voltage	V _{IN}	2.7	-	6.0	V		Note 1
Maximum Output Current	I _{OUTMAX}	50 100	_	_	mA	TC1014	
		150	_	_		TC1185	
Output Voltage	V _{OUT}	V _R - 2.5%	V _R ±0.5%	V _R + 2.5%	V	—	Note 2
V _{OUT} Temperature Coefficient	TCV _{OUT}	_	20 40		ppm/°C	—	Note 3
Line Regulation	ΔV _{OUT} / ΔV _{IN}	_	0.05	0.35	%	—	$(V_R + 1V) \le V_{IN} \le 6V$
Load Regulation	ΔV _{OUT} / V _{OUT}	—	0.5 0.5	2 3	%	TC1014; TC1015 TC1185	$I_L = 0.1 \text{ mA to } I_{OUTMAX}$ $I_L = 0.1 \text{ mA to } I_{OUTMAX}$ (Note 4)
Dropout Voltage	V _{IN} - V _{OUT}	 	2 65 85 180 270	 120 250 400	mV	— — TC1015; TC1185 TC1185	I _L = 100 μA I _L = 20 mA I _L = 50 mA I _L = 100 mA I _L = 150 mA (Note 5)
Supply Current (Note 8)	I _{IN}	—	50	80	μA	—	$\overline{\text{SHDN}} = V_{\text{IH}}, I_{\text{L}} = 0$

Note 1:

The minimum V_{IN} has to meet two conditions: V_{IN} \geq 2.7V and V_{IN} \geq V_R + V_{DROPOUT}. V_R is the regulator output voltage setting. For example: V_R = 1.8V, 2.5V, 2.6V, 2.7V, 2.8V, 2.85V, 3.0V, 3.3V, 3.6V, 4.0V, 5.0V. 2: 3: TC V_{OUT} = $(V_{OUTMAX} - V_{OUTMIN}) \times 10^6$

- V_{OUT} x ΔT
- 4: Regulation is measured at a constant junction temperature using low duty cycle pulse testing. Load regulation is tested over a load range from 1.0 mA to the maximum specified output current. Changes in output voltage due to heating effects are covered by the thermal regulation specification.

Dropout voltage is defined as the input to output differential at which the output voltage drops 2% below its nominal value at a 1V 5: differential.

Thermal Regulation is defined as the change in output voltage at a time T after a change in power dissipation is applied, excluding load 6: or line regulation effects. Specifications are for a current pulse equal to ILMAX at VIN = 6V for T = 10 ms.

The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the 7: thermal resistance from junction-to-air (i.e., T_A , T_J , θ_{JA}). Exceeding the maximum allowable power dissipation causes the device to initiate thermal shutdown. Please see Section 5.0 "Thermal Considerations" for more details.

Apply for Junction Temperatures of -40°C to +85°C. 8:

TC1014/TC1015/TC1185 ELECTRICAL SPECIFICATIONS (CONTINUED)

Electrical Specifications: $V_{IN} = V_R + 1V$, $I_L = 100 \ \mu$ A, $C_L = 1.0 \ \mu$ F, SHDN > V_{IH} , $T_A = +25^{\circ}$ C, unless otherwise noted. Boldface type specifications apply for junction temperatures of -40°C to +125°C.

Parameter	Sym.	Min.	Тур.	Max.	Units	Device	Conditions
Shutdown Supply Current	I _{INSD}	_	0.05	0.5	μA		SHDN = 0V
Power Supply Rejection Ratio	PSRR	_	64	_	dB	—	F _{RE} ≤ 1 kHz
Output Short Circuit Current	IOUTSC	—	300	450	mA	—	V _{OUT} = 0V
Thermal Regulation	ΔV _{OUT} / ΔP _D	—	0.04	—	V/W		Note 6, Note 7
Thermal Shutdown Die Temperature	T _{SD}	—	160	—	°C	—	
Thermal Shutdown Hysteresis	ΔT_{SD}	—	10	—	°C	—	
Output Noise	eN	_	600	_	nV/√Hz	_	I _L = I _{OUTMAX} , F = 10 kHz 470 pF from Bypass to GND
SHDN Input High Threshold	V _{IH}	45	—	—	%V _{IN}	_	V _{IN} = 2.5V to 6.5V
SHDN Input Low Threshold	VIL		_	15	%V _{IN}		V _{IN} = 2.5V to 6.5V

Note 1: The minimum V_{IN} has to meet two conditions: $V_{IN} \ge 2.7V$ and $V_{IN} \ge V_R$ + $V_{DROPOUT}$.

2: V_R is the regulator output voltage setting. For example: V_R = 1.8V, 2.5V, 2.6V, 2.7V, 2.8V, 2.85V, 3.0V, 3.3V, 3.6V, 4.0V, 5.0V.

TC V_{OUT} = $(V_{OUTMAX} - V_{OUTMIN})x 10^6$

V_{OUT} x ΔT

3:

4: Regulation is measured at a constant junction temperature using low duty cycle pulse testing. Load regulation is tested over a load range from 1.0 mA to the maximum specified output current. Changes in output voltage due to heating effects are covered by the thermal regulation specification.

5: Dropout voltage is defined as the input to output differential at which the output voltage drops 2% below its nominal value at a 1V differential.

6: Thermal Regulation is defined as the change in output voltage at a time T after a change in power dissipation is applied, excluding load or line regulation effects. Specifications are for a current pulse equal to I_{LMAX} at V_{IN} = 6V for T = 10 ms.

7: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction-to-air (i.e., T_A, T_J, θ_{JA}). Exceeding the maximum allowable power dissipation causes the device to initiate thermal shutdown. Please see Section 5.0 "Thermal Considerations" for more details.

8: Apply for Junction Temperatures of -40°C to +85°C.

TEMPERATURE CHARACTERISTICS

Electrical Specifications: $V_{IN} = V_R + 1V$, $I_L = 100 \ \mu$ A, $C_L = 1.0 \ \mu$ F, $\overline{SHDN} > V_{IH}$, $T_A = +25^{\circ}$ C, unless otherwise noted. Boldface type specifications apply for junction temperatures of -40°C to +125°C.

			i			
Parameter	Sym.	Min.	Тур.	Max.	Units	Conditions
Temperature Ranges:						
Extended Temperature Range	T _A	-40	_	+125	°C	
Operating Temperature Range	T _A	-40	—	+125	°C	
Storage Temperature Range	T _A	-65	—	+150	°C	
Thermal Package Resistances:						
Thermal Resistance, 5L-SOT-23	θ _{JA}	_	256	_	°C/W	

2.0 TYPICAL PERFORMANCE CURVES

Note: Unless otherwise specified, all parts are measured at temperature = +25°C.

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.



FIGURE 2-1: Temperature.



Dropout Voltage vs.



FIGURE 2-2: Temperature.



FIGURE 2-3: Voltage (V_{IN}).

Ground Current vs. Input



FIGURE 2-4: Temperature.

Dropout Voltage vs.



FIGURE 2-5: Temperature.

Dropout Voltage vs.



FIGURE 2-6: Voltage (V_{IN}).

Ground Current vs. Input



Voltage (V_{IN}).



FIGURE 2-8: Output Voltage (V_{OUT}) vs. Input Voltage (V_{IN}).



FIGURE 2-9: Temperature.

Output Voltage (V_{OUT}) vs.



FIGURE 2-10: Output Voltage (V_{OUT}) vs. Input Voltage (V_{IN}).



FIGURE 2-11: Temperature.

Output Voltage (V_{OUT}) vs.







FIGURE 2-13:





FIGURE 2-14: Output Voltage (V_{OUT}) vs. Temperature.





I_{GND} vs. Temperature.



FIGURE 2-16: AC Characteristics.



FIGURE 2-17: Measure Rise Time of 3.3V with Bypass Capacitor.



FIGURE 2-18: Measure Fall Time of 3.3V with Bypass Capacitor.



FIGURE 2-19: Measure Rise Time of 3.3V without Bypass Capacitor.



FIGURE 2-20: Measure Fall Time of 3.3V without Bypass Capacitor.



FIGURE 2-21: Measure Rise Time of 5.0V with Bypass Capacitor.



FIGURE 2-22: Measure Fall Time of 5.0V with Bypass Capacitor.



FIGURE 2-23: Measure Rise Time of 5.0V without Bypass Capacitor.



FIGURE 2-24: Measure Fall Time of 5.0V without Bypass Capacitor.

Note: Unless otherwise specified, all parts are measured at temperature = +25°C.



FIGURE 2-25: Load Regulation of 3.3V LDO.



FIGURE 2-26: Load Regulation of 3.3V LDO.



FIGURE 2-27: Load Regulation of 3.3V LDO.



LDO.

Load Regulation of 3.3V





FIGURE 2-30: Thermal Shutdown Response of 5.0V LDO.

3.0 PIN DESCRIPTION

The descriptions of the pins are listed in Table 3-1.

Pin Number (5-Pin SOT-23)	Symbol	Description
1	V _{IN}	Unregulated supply input
2	GND	Ground terminal
3	SHDN	Shutdown control input; the regulator is fully enabled when a logic high is applied to this input. The regulator enters shutdown when a logic low is applied to this input. During shutdown, output voltage falls to zero and supply current is reduced to $0.5 \ \mu A$ (maximum).
4	Bypass	Reference bypass input; connecting a 470 pF to this input further reduces output noise.
5	V _{OUT}	Regulated voltage output

TABLE 3-1: PIN FUNCTION TABLE

3.1 Input Voltage (V_{IN})

Connect the V_{IN} pin to the unregulated source voltage. Like all low dropout linear regulators, low source impedance is necessary for the stable operation of the LDO. The amount of capacitance required to ensure low source impedance will depend on the proximity of the input source capacitors or battery type. For most applications, 1.0 μ F of capacitance will ensure stable operation of the LDO circuit. The type of capacitor used can be ceramic, tantalum or aluminum electrolytic. The low-ESR (Effective Series Resistance) characteristics of the ceramic will yield better noise and PSRR (Power Supply Ripple Rejection) performance at high frequency.

3.2 Ground Terminal (GND)

Connect the ground pin to the input voltage return. For the optimal noise and PSRR performance, the GND pin of the LDO should be tied to a quiet circuit ground. For applications have switching or noisy inputs, tie the GND pin to the return of the output capacitor. Ground planes help lower inductance and voltage spikes caused by fast transient load currents and are recommended for applications that are subjected to fast load transients.

3.3 Shutdown (SHDN)

The Shutdown input is used to turn the LDO on and off. When the SHDN pin is at a logic high level, the LDO output is enabled. When the SHDN pin is pulled to a logic low, the LDO output is disabled. When disabled, the quiescent current used by the LDO is less than 0.5 µA max.

3.4 Bypass

Connecting a low-value ceramic capacitor to the Bypass pin will further reduce output voltage noise and improve the PSRR performance of the LDO. While smaller and larger values can be used, these affect the speed at which the LDO output voltage rises when the input power is applied. The larger the bypass capacitor, the slower the output voltage will rise.

3.5 Output Voltage (V_{OUT})

Connect the output load to V_{OUT} of the LDO. Also connect one side of the LDO output capacitor as close as possible to the V_{OUT} pin.

4.0 DETAILED DESCRIPTION

The TC1014, TC1015 and TC1185 are precision fixed output voltage regulators (if an adjustable version is needed, see the TC1070, TC1071 and TC1187 data sheet at www.microchip.com/DS21353). Unlike bipolar regulators, the TC1014, TC1015 and TC1185 supply current does not increase with load current. In addition, the LDOs' output voltage is stable using 1 μ F of capacitance over the entire specified input voltage range and output current range.

Figure 4-1 shows a typical application circuit. The regulator is enabled anytime the shutdown input (SHDN) is at or above V_{IH} , and disabled when SHDN is at or below V_{IL} . SHDN may be controlled by a <u>CMOS</u> logic gate or I/O port of a microcontroller. If the SHDN input is not required, it should be connected directly to the input supply. While in shutdown, the supply current decreases to 0.05 μ A (typical) and V_{OUT} falls to zero volts.



FIGURE 4-1:

Typical Application Circuit.

4.1 Bypass Input

A 470 pF capacitor connected from the Bypass input to ground reduces noise present on the internal reference, which in turn, significantly reduces output noise. If output noise is not a concern, this input may be left unconnected. Larger capacitor values may be used, but results in a longer time period to rated output voltage when power is initially applied.

4.2 Output Capacitor

A 1 μ F (min) capacitor from V_{OUT} to ground is required. The output capacitor should have an effective series resistance greater than 0.1 Ω and less than 5 Ω . A 1 μ F capacitor should be connected from V_{IN} to GND if there is more than 10 inches of wire between the regulator and the AC filter capacitor, or if a battery is used as the power source. Aluminum electrolytic or tantalum capacitor types can be used (since many aluminum electrolytic capacitors freeze at approximately -30°C, solid tantalums are recommended for applications operating below -25°C). When operating from sources other than batteries, supply-noise rejection and transient response can be improved by increasing the value of the input and output capacitors and employing passive filtering techniques.

4.3 Input Capacitor

A 1 µF capacitor should be connected from V_{IN} to GND if there is more than 10 inches of wire between the regulator and this AC filter capacitor, or if a battery is used as the power source. Aluminum electrolytic or tantalum capacitors can be used (since many aluminum electrolytic capacitors freeze at approximately -30°C, solid tantalum is recommended for applications operating below -25°C). When operating from sources other than batteries, supplynoise rejection and transient response can be improved by increasing the value of the input and output capacitors and employing passive filtering techniques.

5.0 THERMAL CONSIDERATIONS

5.1 Thermal Shutdown

Integrated thermal protection circuitry shuts the regulator off when die temperature exceeds 160°C. The regulator remains off until the die temperature drops to approximately 150°C.

5.2 Power Dissipation

The amount of power the regulator dissipates is primarily a function of input and output voltage, and output current. Equation 5-1 is used to calculate worst-case actual power dissipation:

EQUATION 5-1:

$$P_D \approx (V_{INMAX} - V_{OUTMIN})I_{LOADMAX}$$

Where:

P _D	=	Worst-case actual power dissipation
V _{INMAX}	=	Maximum voltage on V _{IN}
V _{OUTMIN}	=	Minimum regulator output voltage
ILOADMAX	=	Maximum output (load) current

The maximum allowable power dissipation (Equation 5-2) is a function of the maximum ambient temperature (T_{AMAX}), the maximum allowable die temperature (T_{JMAX}) and the thermal resistance from junction-to-air (θ_{JA}). The 5-pin SOT-23 package has a θ_{JA} of approximately 220°C/Watt.

EQUATION 5-2:

$$P_{DMAX} = \frac{(T_{JMAX} - T_{AMAX})}{\theta_{JA}}$$

Where all terms are previously defined.

Equation 5-1 can be used in conjunction with Equation 5-2 to ensure regulator thermal operation is within limits. For example:

Given:

V _{INMAX}	=	3.0V +10%
V _{OUTMIN}	=	2.7V - 2.5%
I _{LOADMAX}	=	40 mA
T _{JMAX}	=	125°C
T _{AMAX}	=	55°C
Find:		

A . t. . . I

Actual power dissipation
 Maximum allowable dissipation

Actual power dissipation:

$$P_D \approx (V_{INMAX} - V_{OUTMIN})I_{LOADMAX}$$

= [(3.0 x 1.1) – (2.7 x .975)]40 x 10⁻³ = 26.7 mW

Maximum allowable power dissipation:

$$P_{DMAX} = \frac{(T_{JMAX} - T_{AMAX})}{\theta_{JA}}$$
$$= \frac{(125 - 55)}{220}$$
$$= 318 \text{ mW}$$

In this example, the TC1014 dissipates a maximum of 26.7 mW below the allowable limit of 318 mW. In a similar manner, Equation 5-1 and Equation 5-2 can be used to calculate maximum current and/or input voltage limits.

5.3 Layout Considerations

The primary path of heat conduction out of the package is via the package leads. Layouts having a ground plane, wide traces at the pads, and wide power supply bus lines combine to lower θ_{JA} and therefore increase the maximum allowable power dissipation limit.

6.0 PACKAGING INFORMATION

6.1 Package Marking Information



0&2	represents part number code + temperature range and voltage
3	represents year and 2-month period code
4	represents lot ID number

TABLE 6-1: PART NUMBER CODE AND TEMPERATURE RANGE

(V)	TC1014 Code	TC1015 Code	TC1185 Code
1.8	AY	BY	NY
2.5	A1	B1	N1
2.6	NB	BT	NT
2.7	A2	B2	N2
2.8	AZ	BZ	NZ
2.85	A8	B8	N8
3.0	A3	B3	N3
3.3	A5	B5	N5
3.6	A9	B9	N9
4.0	A0	B0	NO
5.0	A7	В7	N7

5-Lead Plastic Small Outline Transistor (CXX) [SOT-23]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-091-CXX Rev H Sheet 1 of 2

TC1014/TC1015/TC1185

5-Lead Plastic Small Outline Transistor (CXX) [SOT-23]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



VIEW A-A SHEET 1

	Ν	IILLIMETER	S	
Dimension	Limits	MIN	NOM	MAX
Number of Pins	N		5	
Pitch	е		0.95 BSC	
Outside lead pitch	e1		1.90 BSC	
Overall Height	Α	0.90	-	1.45
Molded Package Thickness	A2	0.89	-	1.30
Standoff	A1	-	-	0.15
Overall Width	E	2.80 BSC		
Molded Package Width	E1	1.60 BSC		
Overall Length	D	2.90 BSC		
Foot Length	L	0.30	-	0.60
Footprint	L1	0.60 REF		
Foot Angle	θ	0°	-	10°
Lead Thickness	С	0.08	-	0.26
Lead Width	b	0.20	-	0.51

Notes:

1. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.25mm per side. 2. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-091-CXX Rev H Sheet 2 of 2

5-Lead Plastic Small Outline Transistor (CXX) [SOT-23]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Ν	ILLIMETER	S	
Dimension	Limits	MIN	NOM	MAX
Contact Pitch	Е		0.95 BSC	
Contact Pad Spacing	С		2.80	
Contact Pad Width (X5)	Х			0.60
Contact Pad Length (X5)	Y			1.10
Distance Between Pads	G	1.70		
Distance Between Pads	GX	0.35		
Overall Width	Z			3.90

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2091-CXX Rev H

TC1014/TC1015/TC1185

6.2 Taping Form



TC1014/TC1015/TC1185

NOTES:

APPENDIX A: REVISION HISTORY

Revision F (November 2023)

- Added automotive qualification to Features and examples to Product Identification System.
- Updated Absolute Maximum Ratings† to better describe the part.
- Updated Section 6.0, Packaging Information.
- Made minor text and format changes throughout the document.

Revision E (February 2007)

- Changed Dropout Voltage from mA to µA in Section 1.0, Electrical Characteristics.
- Updated Product Identification System, page 23.
- Updated Section 6.0, Packaging Information.

Revision D (April 2006)

- Removed "ERROR is open circuited" from SHDN pin description in Pin Function Table.
- Added verbiage for pinout descriptions in Pin Function Table.
- Replaced verbiage in first paragraph of **Section 4.0, Detailed Description**.
- Added Section 4.3, Input Capacitor.

Revision C (January 2006)

• Changed TR suffix to 713 suffix in Taping Form in Package Marking section.

Revision B (May 2002)

• Converted Telcom data sheet to Microchip standard for Analog Handbook.

Revision A (February 2001)

• Original release of this document under Telcom.

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or	delivery, refer to the factory or the listed sales office.
---	--

	x x			Examples for TC1014:		
Device Out	put Temperature	Package	Qualification	a)	TC1014-1.8VCT713:	1.8V, 5LD SOT-23, Tape and Reel
Volta	age Range			b)	TC1014-2.85VCT713:	2.85V, 5LD SOT-23, Tape and Reel
Device:	TC1014: 50 mA LDO	vith Shutdown and V _{REF} Bypass with Shutdown and V _{REF} Bypass		c)	TC1014-3.3VCT713:	3.3V, 5LD SOT-23, Tape and Reel
Output Voltage:	TC1185: 150 mA LDO with Shutdown and V_{REF} Bypass			d)	TC1014-3.0VCT713VA	AO: 3.3V, 5LD SOT23, Tape and Reel, Automotive Qualified
Output voitage.	2.5 = 2.5V 2.6 = 2.6V 2.7 = 2.7V			e)	TC1014-3.3VCT713V	AO: 3.0V, 5LD SOT23, Tape and Reel, Automotive Qualified
	2.8 = 2.8V 2.85 = 2.85V	2.8V 2.85V		Ex	amples for TC1015:	
	3.0 = 3.0V 3.3 = 3.3V 3.6 = 3.6V			a)	TC1015-1.8VCT713:	1.8V, 5LD SOT-23, Tape and Reel
	4.0 = 4.0V 5.0 = 5.0V			b)	TC1015-2.85VCT713:	2.85V, 5LD SOT-23, Tape and Reel
Temperature Range:	V = -40° C to +125°	°C		c)	TC1015-3.0VCT713:	3.0V, 5LD SOT-23, Tape and Reel
Package:	CT713 = Plastic Small 5-lead, Tape	Outline Transis	stor (SOT-23),	d)	TC1015-3.3VCT713VA	AO: 3.3V, 5LD SOT-23, Tape and Reel, Automotive Qualified
				Examples for TC1185:		
Qualification*:	Blank = Standard Par VAO = AEC-Q100 A	t utomotive Qual	lified	a)	TC1185-1.8VCT713:	1.8V, 5LD SOT-23, Tape and Reel
	*All currently available \ examples.	/AO variants ar	e shown in the	b)	TC1185-2.8VCT713:	2.8V, 5LD SOT-23, Tape and Reel
	Contact your local Micro automotive qualified var voltage options.	iants for other p	e to request backages types or	c)	TC1185-5.0VCT713VA	C: 5.0V, 5LD SOT-23, Tape and Reel, Automotive Qualified

NOTES:

Note the following details of the code protection feature on Microchip products:

- · Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not
 mean that we are guaranteeing the product is "unbreakable" Code protection is constantly evolving. Microchip is committed to
 continuously improving the code protection features of our products.

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at https:// www.microchip.com/en-us/support/design-help/client-supportservices.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WAR-RANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDI-RECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSE-QUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, TimeCesium, TimeHub, TimePictra, TimeProvider, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, Clockstudio, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, EyeOpen, GridTime, IdealBridge, IGaT, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, IntelliMOS, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, MarginLink, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, mSiC, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, Power MOS IV, Power MOS 7, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O. simpleMAP. SimpliPHY. SmartBuffer. SmartHLS. SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, Trusted Time, TSHARC, Turing, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2023, Microchip Technology Incorporated and its subsidiaries.

All Rights Reserved.

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

ISBN: 978-1-6683-3461-4



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

China - Beijing Tel: 86-10-8569-7000 China - Chengdu

Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen Tel: 86-592-2388138 China - Zhuhai

Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631 India - Pune

Tel: 91-20-4121-0141 Japan - Osaka

Tel: 81-6-6152-7160

Japan - Tokyo Tel: 81-3-6880- 3770 Korea - Daegu

Tel: 82-53-744-4301 Korea - Seoul

Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

Singapore Tel: 65-6334-8870

Taiwan - Hsin Chu

Tel: 886-3-577-8366 Taiwan - Kaohsiung Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

Netherlands - Drunen

EUROPE

Austria - Wels

Tel: 43-7242-2244-39

Tel: 45-4485-5910

Fax: 45-4485-2829

Tel: 358-9-4520-820

Tel: 33-1-69-53-63-20

Fax: 33-1-69-30-90-79

Germany - Garching

Tel: 49-2129-3766400

Germany - Heilbronn

Germany - Karlsruhe

Tel: 49-7131-72400

Tel: 49-721-625370

Germany - Munich

Tel: 49-89-627-144-0

Fax: 49-89-627-144-44

Germany - Rosenheim

Tel: 49-8031-354-560

Israel - Ra'anana

Italy - Milan

Italy - Padova

Tel: 972-9-744-7705

Tel: 39-0331-742611

Fax: 39-0331-466781

Tel: 39-049-7625286

Tel: 49-8931-9700

Germany - Haan

Finland - Espoo

France - Paris

Fax: 43-7242-2244-393

Denmark - Copenhagen

Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820