Cooper Hand Tools



Electronics Pliers, Cutters and Tweezers





Content

Page
4-16 5-10
10-11
11
12-13
13
14 15
15
16
17-36
21-27
27-28
29-33
33
34-35
36
37-39
40-42
42-43
44-48
44-45
46-48
48-49
48
48
49
50
51
52-55
58-59






Erem Tools - Precision Made in Switzerland

Precision is sought by many but achieved by few. The quality and performance of Erem hand tools is the result of more than 25 years of research and manufacturing expertise. Erem is constantly innovating and developing new tools for use in areas as diverse as electronics, aviation, biology, medical (cardio-vascular, cannulae applications), watch and clock industry, telecoms.

Although your initial investment in Erem tools may be higher than some other tools, the final cost based on medium to long term use will be lower due to the economy resulting from the quality of the tools and in the case of the cutters, the free of charge resharpening. The inherent precision of the tools will be reflected in the quality of your products.







Erem Tweezers

Erem tweezers are high precision tools of constant high quality. Precise finished and symmetrical tips together with easy handling and perfect balance makes them outstanding tools. The range of Erem tweezers covers a wide diversity of applications. It is produced in many shapes and can be manufactured from different materials. The most popular models are available in a lower cost economy (SL) range. In all models, the type number of the tweezers is stamped, not printed.

The Material

Erem offers a wide variety of materials, carbon steel, stainless steel, Erem special stainless steel, Nickel plated, Brass or Titanium. The most common ones' are explained below:

Carbon Steel

Carbon steel tweezers have hard tips but the rust resistance is low and they are magnetic. Carbon steel tweezers have no suffix.

Stainless Steel

Tweezers from stainless steel have strong tips and are rust resistant but are not as hard and longlasting as carbon steel tweezers. Stainless steel tweezers have the suffix "S".

Erem Special Stainless Steel

This grade of steel is a non magnetic, rust resistant, anti acid alloy. It is temperature resistant up to 300°C.
Tweezers from special stainless steel have the suffix "SA"

Coating

The Pyroplast coating is an exclusive by Erem. The advantages are:

- heat resistance up to 500°C (932°F), almost twice as much as PTFE, Cralon, etc.
- no capillary effect on tips while soldering (non-stick property)
- no contamination caused by positive or negative charge
- hydrophobic
- radiation resistant
- thickness 60-80 μ

the suffix is "PYR".

Note: The Pyroplast coating is not available for all Erem tweezers. It is made to order and needs a minimum order quantity. Please ask for further information.

Ergonomic

Developed by Erem, tweezers with ergonomically shaped handles to alleviate the problem of **Repetitive Strain Injuries (RSI)** and reduce operator fatigue. The range has been selected to include the most popular tip shapes (see page 11). The main features are:

- ergonomic design for operator comfort and ease of control
- two colour, thermally insulated soft grip handles moulded from a synthetic material
- ESD safe
- the grips absorb heat for additional user protection
- manufactured from non magnetic, acid resistant, stainless steel alloy
- supplied in a rigid, transparent plastic box for protection and storage The prefix for ergonomic tweezers is "E".

Suffix

None carbon steel E (Prefix) ergonomic handles

M Brass, soft material to avoid damage, no sparks

N Nickel-Silver alloy PYR Pyroplast coating RU anti adhesive coating

S stainless steel

SA, CA special stainless steel, non-magnetic, acid resistant

SL economy version

TA Titanium, non-magnetic, lightweight, high temperature resistant

Z Nickel plated










Pointed Tips Straight



Pointed Tips Straight

Main applications: for conventional and precision handling of small parts like tissue, components, wires. For tasks in micro electronics industry, medicine, laboratories and other applications where high precision is required.



Length 80 mm



Model	Length	Weight	Description
M5S	80 mm	6 g	Stainless steel, anti-glare finish
			Micro tweezers, very small, very fine tips, e.g. for work under microscope

Length 108 mm



Model	Length	Weight	Description
ACSA	108 mm	16 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers with serrated grips for anti-slip handling. For bending and handling.
20AS	108 mm	12 g	Stainless steel, anti-glare finish
			Precision tweezers with serrated grips and inside serrated tips for anti-slip handling. Guide pin to avoid tip overlapping. For bending and handling.

Length 110 mm



Model	Length	Weight	Description
3CS	110 mm	11 g	Stainless steel, anti-glare finish
			Precision tweezers with long tips for delicate circuit board assembly.
3CSA	110 mm	11 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers for delicate circuit board assembly.
3CSASL	110 mm	11 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as 3CSA but economy model.
ЗСТА	110 mm	8 g	Titanium, non-magnetic
			Same as 3CSA but Titanium for heat resistance and light weight.
53CSA	110 mm	11 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers with crush-proof design for handling of delicate parts.



Pointed Tips Straight

Length 120 mm







Model	Length	Weight	Description
3SA	120 mm	14 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers for micro electronics. Precision work.
3SASL	120 mm	14 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as 3SA but economy model.
1SA	120 mm	14 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers for general use.
1SASL	120 mm	14 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as 1SA but economy model.
OOSA	120 mm	20 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers for general purpose e.g. electronic assembly, very sturdy.
OOSASL 1	120 mm	20 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as 00SA but economy model.
OOCSA	120 mm	18 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as 00SA but smaller version.
OOBSA	120 mm	20 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as 00SA but with serrated grips.
OODSA	120 mm	20 g	Special stainless steel, anti-glare finish, non-magnetic
BEAUTIFIED TO			Same as 00SA but with serrated grips and inside serrated tips.
64SA	120 mm	17 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers with serrated grips.
11N	120 mm	17 g	Nickel-Silver alloy, anti-glare finish, non-magnetic
			Precision tweezers Nickel-Silver alloy, perfect non-magnetic.
AAZ	120 mm	16 g	Nickel plated
			Precision tweezers Nickel plated, for electronics assembly.

Length 125 mm



Model	Length	Weight	Description
AAS	125 mm	16 g	Stainless steel, anti-glare finish
			Precision tweezers with strong but fine tips. For universal use.
AASSL	125 mm	16 g	Stainless steel, anti-glare finish
			Same as AAS but economy model.

6



Pointed Tips Straight



Model	Length	Weight	Description
AASA	125 mm	16 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers with strong but fine tips. For universal use.
AASASL	125 mm	16 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as AASA but economy model.
AM	125 mm	17 g	Brass, polished
			Precision tweezers brass. Soft metal protects sensitive parts against damage. No sparks.

Length 130 mm



Model	Length	Weight	Description
249SA	130 mm	20 g	Special stainless steel / PPS, anti-glare finish, non- magnetic ESD safe, suitable for fibre optics
			Precision tweezers with serrated grips and synthetic tips (PPS). Heat resistant up to 250°C (480°F). Resistant to acids and solder. Waterproof, ESD safe. Does not damage fibre optic cores.
249CER	130 mm	24 g	Special stainless steel / Ceramic anti-glare finish, non- magnetic
			Same as 249SA but with Ceramic tips for heat resistance up to 900°C (1500°F).

Length 140 mm



Model	Length	Weight	Description
RRS	140 mm	30 g	Stainless steel, anti-glare finish
			Precision tweezers, long version, very strong.
SSSA	140 mm	11 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers with narrow grips and low tension. Extra long for use near heat, die attachment.
SSSASL	140 mm	11 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as SSSA but economy model.

Length 150 mm



Model	Length	Weight	Description
29SA	150 mm	26 g	Special stainless steel, anti-glare finish, non-magnetic, reverse action
			Precision tweezers with fibre-grip handles for heat protection. Reverse action for permanent holding parts.

Length 160 mm



Model	Length	Weight	Description
21SA	160 mm	23 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers, long version, with serrated grips and inside serrated tips, strong.



Pointed Tips Straight Relieved



Pointed Tips Straight Relieved

Main application: for better product visibility e.g. under microscope or working in confined areas, for handling tiny components.

Length 90 mm



Model	Length	Weight	Description
M4AS	90 mm	9 g	Stainless steel, anti-glare finish
			Micro tweezers with very small, very fine tips, e.g. for working under microscope or handling tiny parts in HF assembly. Strong tips due to hardened stainless steel.

Length 110 mm



Model	Length	Weight	Description
4SA	110 mm	13 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers with very fine points
4SASL	110 mm	13 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as 4SA but economy model.

Length 115 mm



Length	Weight	Description
115 mm	12 g	Stainless steel, anti-glare finish
		Precision tweezers with extremely fine tips ($\sim 0.03 \times 0.07$ mm) for use in dissection procedures and handling of very small samples e.g. under microscope. Only for use with soft materials.
115 mm	12 g	Special stainless steel, anti-glare finish, non-magnetic
		Precision tweezers with extremely fine tips (\sim 0,05 x 0,1 mm) for use in dissection procedures and handling of very small samples e.g. under microscope. Only for use with soft materials.
115 mm	12 g	Special stainless steel, anti-glare finish, non-magnetic
		Precision tweezers with very fine tips e.g. for handling fine wires.
115 mm	12 g	Special stainless steel, anti-glare finish, non-magnetic
		Same as 5SA but economy model
115 mm	16 g	Special stainless steel, anti-glare finish, non-magnetic
		Precision tweezers with medium tips.
115 mm	16 g	Special stainless steel, anti-glare finish, non-magnetic
	-	Same as 2SA but economy model.
	115 mm 115 mm 115 mm	115 mm 12 g 115 mm 12 g 115 mm 12 g 115 mm 16 g

8



Pointed Tips Straight Relieved

Length 120 mm



Model	Length	Weight	Description
258SA	120 mm	15 g	Special stainless steel/PPS, anti-glare finish, non- magnetic, ESD safe
			Precision tweezers with serrated grips and synthetic tips (PPS). Heat resistant up to 250°C (480°F). Resistant to acids and solder. Waterproof, ESD safe.

Pointed Tips Bent



Pointed Tips Bent Main application: for better product visibility and handling e.g. working in confined areas and under microscope.

Length 110 mm



Model	Length	Weight	Description
3CBS	110 mm	11 g	₹40°, stainless steel, anti-glare finish
			Precision tweezers bent for delicate circuit board assembly.

Length 115 mm



Model	Length	Weight	Description
5CSA	115 mm	12 g	
			Precision tweezers curved, relieved.
5BSA	115 mm	12 g	
			Precision tweezers curved, relieved.
51SA	115 mm	12 g	
			Precision tweezers curved, relieved. Very fine tips.
51SASL	115 mm	12 g	
			Same as 51SA but economy model.
5ASA	115 mm	12 g	
			Precision tweezers oblique, relieved. Fine tips.
5ASASL	115 mm	12 g	† 15°, special stainless steel, anti-glare finish, non-magnetic
			Same as 5 ASA but economy model.



Pointed Tips Bent

Length 120 mm



Model	Length	Weight	Description
7SA	120 mm	15 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers curved, relieved. For easy handling in confined areas.
7SASL	120 mm	15 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as 7SA but economy model.

Length 140 mm



Model	Length	Weight	Description
65ASA	140 mm	11 g	∮50°, special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers bent. Very fine points. For handling extra fine components.

Length 150 mm



Model	Length	Weight	Description
24SA	150 mm	22 g	₹40°, special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers bent. Serrated grips and inside serrated tips. Alignment pin. Useful for all soldering jobs and assembly.
30SA	150 mm	26 g	₹50°, special stainless steel, anti-glare finish, non-magnetic, reverse action
			Precision tweezers bent. With fibre-grip handles for heat protection. Reverse action for permanent holding parts. Useful e.g. for soldering jobs.

Flat Round Tips Straight



Flat Round Tips Straight Main application: for conventional holding and gripping applications.



Length 120 mm



Model	Length	Weight	Description
2ASA	120 mm	15 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers with medium tips for gripping.



Flat Round Tips Straight




Model	Length	Weight	Description
2ASASL	120 mm	15 g	Special stainless steel, anti-glare finish, non-magnetic
			Same as 2ASA but economy model.
2ASASLT	120 mm	16 g	Special stainless steel/PTFE,coated, anti-glare finish, non-magnetic
			Same as 2ASA but PTFE, coated tips for handling delicate parts.
2ASARU	120 mm	16 g	Special stainless steel/coated, anti-glare finish, non-magnetic
			Same as 2ASA but coated tips for handling adhesive parts, gaskets, Kapton ribbons, labels with negligible capillary effect.
25SA	120 mm	15 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers with flat round tips. For gripping.
52ASA	120 mm	15 g	Special stainless steel, anti-glare finish, non-magnetic
			Precision tweezers with crush-proof design for handling of delicate parts.

Precision Tweezers with Ergomomic Handles*

Main applications:

Thermally insulated soft grips, ESD safe, ergonomically shaped to reduce operator's hand fatigue.





Model	Length	Weight	Description
E5SA	120 mm	25 g	Special stainless steel, ergonomic handles, non-magnetic, ESD-safe
			Ergonomic precision tweezers straight, very fine tips, e.g. for handling fine wires.
E3CSA	120 mm	25 g	Special stainless steel, ergonomic handles, non-magnetic, ESD-safe
			Ergonomic precision tweezers straight, long fine tips, for delicate circuit board assembly.
E00SA	120 mm	30 g	Special stainless steel, ergonomic handles, non-magnetic, ESD-safe
			Ergonomic precision tweezers straight, fine tips, for general use. Very sturdy.
E7SA	120 mm	28 g	Special stainless steel, ergonomic handles, non-magnetic, ESD-safe
			Ergonomic precision tweezers curved, fine tips, for easy manipulation in confined areas.
E2ASA	120 mm	28 g	Special stainless steel, ergonomic handles, non-magnetic, ESD-safe
			Ergonomic precision tweezers straight, flat round tips, for gripping.

Note: colour coatings subject to variations without prior notice. * Ergonomic features see page 4.




SMD Tweezers



Angled Head

Main application: for handling chips or miniature SMD components. For mounting on SMD boards or Ceramic substrates.







Model	Length	Weight	Description
102ACA	115 mm	15 g	Special stainless steel, anti-glare finish, non-magnetic
0,5 mm ↓ ↑ → 1+-1,5			SMD tweezers with angled head and blunt edges to avoid board damage. For handling small components, mounting on SMD boards, hybrids ICs, watch hands, etc.
102ACAX ↓	115 mm	14 g	Special stainless steel, anti-glare finish, non-magnetic, reverse action
1),25 mm/.098"		Same as 102ACA but reverse action.
103ACA	115 mm	15 g	45°, special stainless steel, anti-glare finish, non-magnetic
1 mm -	-2 mm		SMD tweezers with angled head and blunt edges to avoid board damage. For handling of small components.

Rounded Head





Model	Length	Weight	Description	
39SA	39SA 110 mm 15 g		\emptyset 0,3 mm, special stainless steel, anti-glare finish, non-magnetic	
			Straight, serrated grips. For gripping wires and small cylindrical parts.	
40 SA	110 mm	15 g	Ø 0,4 mm, special stainless steel, anti-glare finish, non-magnetic	
			Straight, serrated grips. For gripping wires and small cylindrical parts.	
150SAMF 120 mm		13 g	\emptyset 1,2 – 2,5 mm, special stainless steel, anti-glare finish, non-magnetic	
			SMD tweezers straight, serrated grips. For gripping small cylindrical parts, mini MELFs. Very narrow tips.	
150SAD 120 mm 120 mm 150SAD 4 (.157)		13 g	Ø 1,5 – 3 mm, special stainless steel, anti-glare finish, non-magnetic	
			SMD tweezers straight, serrated grips. For gripping small cylindrical parts.	



Rounded Head



Model	Length	Weight	Description				
150SA	120 mm	13 g	\emptyset 1,5 – 3 mm, special stainless steel, anti-glare finish, non-magnetic				
2 mm			SMD tweezers straight, serrated grips. For gripping small cylindrical parts.				
151SA	120 mm	13 g	Ø 3 – 6 mm, special stainless steel, anti-glare finish, non-magnetic				
6,8 mm			SMD tweezers straight, serrated grips. For gripping small cylindrical parts.				

Rounded Head Bent



Model	Length	Weight	Description
32BSA	BSA 115 mm 17 g		45°, Ø 5 mm, special stainless steel, anti-glare finish, non-magnetic
			SMD tweezers bent. For small cylindrical components or insulated fibres.
32BSA20	115 mm	17 g	45°, Ø 2 mm, special stainless steel, anti-glare finish, non-magnetic
			Same as 32BSA but Ø 2 mm.
32BSA25	115 mm	17 g	45°, \varnothing 2,5 mm, special stainless steel, anti-glare finish, non-magnetic
			Same as 32BSA but Ø 2,5 mm.
150SAMB	150SAMB 115 mm 1		40°, \varnothing 1,2 - 2,5 mm, special stainless steel, anti-glare finish, non-magnetic
			SMD tweezers bent, serrated grips. For gripping small cylindrical parts.

Special Gripping Tweezers



Model	Length	Weight	Description
940AS	120 mm	17 g	Stainless steel, anti-glare finish
			Gripping tweezers with locking clip. For various applications. Resists a tensile force of \sim 5 kg.





Wafer Tweezers



Wafer Tweezers

Main application: for handling wafers from 3" to 6". Different coatings or sizes on request.







Model	Length	Α	В	Weight	Description
91SA	125 mm	12 mm	7 mm	15 g	3"- 4", special stainless steel, anti-glare finish, non-magnetic
					Standard wafer tweezers to pick up 3" or 4" Silicon wafers. Serrated grips.
500ASA	130 mm	16 mm	8 mm	22 g	4"- 5", special stainless steel, anti-glare finish, non-magnetic
					Wafer tweezers with fingers to reduce the risk of damage. For 4" and 5" wafers. Serrated grips.
600ASA	130 mm	19,5 mm	8 mm	23 g	6", special stainless steel, anti-glare finish, non-magnetic
					Wafer tweezers with fingers to reduce the risk of damage. For 6" wafers. Serrated grips.
608ASA	130 mm	30 mm	8,5 mm	23 g	6", special stainless steel, anti-glare finish, non-magnetic
					Same as 600ASA but with 30 mm width.
600JSA	130 mm	20 mm	8 mm	24 g	4"- 6", special stainless steel, anti-glare finish, non-magnetic
					Wafer tweezers with free-floating PTFE, paddle for self adjustment on 4"- 6" wafers. Serrated grips.
140SA	120 mm	30 mm	5 mm	20 g	4" - 5", special stainless steel/Polyester, anti-glare finish, non-magnetic
					Wafer tweezers with Delrin tips. Available with adjustable opening screw. For 4" to 5" wafers. Serrated grips. Temperature resistance 170°C .
141SAP	150 mm	30 mm	8 mm	30 g	5"- 6", special stainless steel/PTFE,, anti-glare finish, non-magnetic
					Wafer tweezers with Polyester tips. The perfect wafer tweezers. Will not damage Si, GaAs or Ti wafers. Serrated grips.
141SAPH	150 mm	30 mm	8 mm	30 g	5"- 6", special stainless steel/Halar, anti-glare finish, non-magnetic
					Same as 141SAP but with Halar coating and plastic tips without pigmentation. Halar is acids resistant.




Cutting Tweezers



Cutting Tweezers

Main application: e.g. for cutting soft wires on micro electronics circuits, very precise.





Model	Length	Weight	Description		
15AGS	115 mm	21 g	Anti-glare finish		
	5,5 mm		Cutting tweezers with fine oblique head and induction hardened cutting blades for increasing life time. For soft wires up to \varnothing 0,25 mm.		
15AGW	W 115 mm 26 g		Anti-glare finish		
9,5 mm			Cutting tweezers with oblique head. Induction hardened cutting blades improves cutting capability and life time. For soft wires up to Ø 0,25 mm.		

Stripping Tweezers



Stripping Tweezers

Main application: for stripping small wires, standard or PTFE, insultations, very precise.









Model	Length	Weight	Description	
29Y	120 mm	22 g	Stainless steel, anti-glare finish	
			Miniature stripping tweezers. Serrated grips. Will strip tiny wires between AWG 42 and 32 (0,06 to 0,20 mm). Wire samples required.	
29W30	120 mm	28 g	Stainless steel/fibre handles, anti-glare finish, reverse action	
			Stripping tweezers with fibre-grip handles. For standard or PTFE, wires between AWG 30 and 28 (0,25 mm – 0,3 mm). Reverse action.	



Extraction Tweezers



Extraction TweezersMain application:
to extract connected wires
from the rear of the
connectors.





Model	Length	Ø A	Ø B	С	Weight	Description
024C	120 mm	1,75 mm	2,15 mm	8 mm	20 g	Stainless steel Extraction tweezers for Sub-D types. For ITT-Canon / TRW CET 20D, Honda connectors, Siemens, Philips, Souriau-Framatome, etc.
028	120 mm	1,9 mm	2,15 mm	8 mm	20 g	Stainless steel Same as 024C but with thinner nozzle wall for wires with larger insulations.



Cutters and Pliers

Erem Cutters and Pliers

Erem cutters and pliers are unique in the degree of quality, precision, reliability, ergonomy and long life they offer when compared to other professional tools, for the following reasons:




The Steel



Erem cutters and pliers are not forged. They are manufactured from billets of **high grade tool steel**, which uses a Swiss developed lamination technique. It employs a multiple extrusion process to super compact the steel imparting **additional strength** and toughness to the tools. This results in reliable and **long lasting** tools.

The Joints




The surfaces between the two halves of the joint are machine finished and in conjunction with the interlocking precision screw that is used to join both halves together ensure **wobble free** operation and eliminates blade overlap which could cause mechanical shock and damage components.

The Springs



The return springs are mounted internally in the head of the tools and are guaranteed for **1 million operations.** They operate with a constant resistance over the movement of handles to reduce operator fatigue making them superior to leaf or coil springs.

EMOS



Erem Maximum Opening Stop, limits the handle spread by preventing the tips of the blades from opening more than 5mm. To promote operator comfort and ergonomy.



Cutters and Pliers



Customer Service

1. Spare parts

Erem pliers and cutters and their spare parts are guaranteed against manufacturing defects. The following parts will be supplied free of charge should a defect be found

- Foam grips
- Springs
- Opening stops

Please contact your local Cooper Hand Tools office for advice on procedure.



2. Resharpening

Erem cutters can be returned to Erem Switzerland for free of charge resharpening. It is possible to resharpen tools up to three times depending on their condition. Tools will be returned to you fitted with new handles depending on their shape. You will be invoiced for transport costs only.



Specials

Erem is able to offer tools for special applications without minimum order quantity. Dimensioned drawings /and or samples of your application will be required.

Ergonomic Handles




Erem Cutters and Pliers with Ergonomic Handles

The Work Related Upper Limb Disorder (WRULD) is a muscular skeletal problem related to the arm. WRULDS can be caused by positional fatigue or nerve damage caused e.g. by repetitive use of non ergonomic hand tools, the socalled Repetitive Strain Injuries (RSI). The ability to grip and hold objects can be impaired. Repetitive movements can cause compression of the median nerve and produce sensations of pins and needles.



WRULDS is a direct result of companies manufacturing processes and working practices and will as result detrimental to the quality of a companies products. Therefore a reduction of the factors which cause WRULDS will improve working practice and product quality. In fact it is arguable that without quality working practice there can be no quality product.



To alleviate the problem of RSI and Erem have designed a range of tools with ergonomic handles. The compound curves of the handles of the Erem ergonomic cutters and pliers allow the pressure applied to the handles when cutting or gripping to be evenly spread over the palm of the hand. The thumb and fingers are self- positioned by the handles, making the tool comfortable for the operator to use and reducing the incidence of WRULDS. The comfortable foam grips are ESD safe and easily interchangeable.



The following tools are available with ergonomic handles:

- Side Cutters see page 27 28
- Tip Cutters see page 33
- Pliers see page 39




Cutters and Pliers




ESD Safety

The foam cushion grips are static dissipative and are fitted a standard to all models.




Cost Per Cut Comparison


The best way to compare the real costs between different hand tools is to consider the number of cuts - besides the work itself and the performance. The parameters below indicate how Erem tools - representing a higher initial investment - become even more economical than lower quality cutters on a medium or long-term basis.






Cutting Capabilities







***Note:** There is no max. Cu indication for Tungsten Carbide cutters. Please ask for the according cutting capabilities.



Side Cutters

Side Cutters

Erem offers a wide range of precision side cutters. To establish which cutter is correct for your application follow the steps below



Head Form



Oval Head

The most common head shape. For standard cutting applications where access is not the problem.



Tapered Head

For cutting tasks where easier access is required. The tapered head shape allows better tip access than the oval head but without much reducing the cutting capability.



Relieved Head

For cutting in confined areas. This is the smallest head shape available. One side is cut away for access even in confined areas. Due to the cut away the cutting capability is reduced. Flush tip cutting.



Cut




Semi Flush

These blades allow a very high resistance. Will cut from tip to heel, malleable wires like Copper as well as hard wires. Leaves a pinch at the end of the wire. For all applications where the cutting type is not so important.



Flush

Allows a flat cut with the same cutting capacities. The edge of the wire is cut off flat. Thanks to faster penetration into the component the operator's effort is substantially reduced. No solder spikes after using wave soldering process.




1. Erem Cut

Cut 2. Others



Super Full Flush

An Erem exclusivity. This absolute full flush cut leaves a perfect flat surface on cut leads It prevents any pinching of leads. Flat, clean cut. No cutting rework after soldering. Soft wires only.



Size

110 mm Small short head for increased cutting resistance. For almost all cutting applications.

115 mm Longer and finer head.

For cutting applications where easy access is more important than a high cutting capacity.

120 mm Strong version.

For all cutting applications where high cutting capacity is required.




Safety Lead Device

Cutting safety device, holds wire scraps.
Can be adapted on all side cutters series 500, 600 and 2200.
Add "W" when ordering, e.g. 595EW



Oval Head





Length 110 mm

Model	L	Α	В	С	Max. Cu	Weight	Description
612N	110 mm	9 mm	9 mm	6 mm	Ø 1,25 mm	48 g	Semi flush cut, high grade tool steel, burnished, ESD safe, resharpenable Miniature side cutter. Economical line. Small head.
611E	110 mm	9 mm	9 mm	6 mm	ø 1,5 mm	48 g	Semi flush cut, high grade tool steel, burnished, ESD safe, resharpenable Miniature side cutter. Small head.
612E	110 mm	10,5 mm	9 mm	6 mm	ø 1,5 mm	48 g	Semi flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable Miniature side cutter. Standard head width.
622N	110 mm	9 mm	9 mm	6 mm	ø 1,25 mm	48 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable Miniature side cutter. Economical line. Small head.
632N	110 mm	9 mm	9 mm	6 mm	ø 1,25 mm	48 g	Super full flush cut, high grade tool steel, anti- glare finish, ESD safe, resharpenable Miniature side cutter. Economical line. Small head. Perfect full flush cut. Soft wires only.
710E	110 mm	8,8 mm	9 mm	6 mm	ø 1,0 mm	48 g	Super full flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable Miniature side cutter. Standard head width. Perfect full flush cut. Soft wires only.

Length 115 mm

Model	L	Α	В	С	Max. Cu	Weight	Description
512N	115 mm	10 mm	10,5 mm	6,5 mm	ø 1,6 mm	67 g	Semi flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Side cutter for universal use. Medium size. Economical line.

22



Oval Head

Model	L	A	В	С	Max. Cu	Weight	Description
511E	115 mm	10 mm	10,5 mm	6,5 mm	ø 1,6 mm	67 g	Semi flush cut, high grade tool steel, burnished, ESD safe, resharpenable
							Side cutter for universal use. Medium size.
512E	115 mm	12 mm	10,5 mm	6,5 mm	ø 1,6 mm	67 g	Semi flush cut, high grade tool steel, burnished, ESD safe, resharpenable
C A							Side cutter for universal use. Medium size. For tough cutting applications.
597E	115 mm	12 mm	10,5 mm	6,5 mm	ø 1,6 mm	67 g	Semi flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Side cutter with strong head. For soft and small hard wires.
599T	115 mm	11,5 mm	10,5 mm	6,5 mm	ask for cutting	67 g	Semi flush cut, Tungsten Carbide blades, anti-glare finish, ESD safe
					capability*		Side cutter with Tungsten Carbide blades for constant quality cuts. Resistant to small stainless steel wires.
599TFO	115 mm	15 mm	10,5 mm	6,5 mm	ask for cutting	67 g	Semi flush cut, Tungsten Carbide blades, anti-glare finish, ESD safe
					capability*		Side cutter with Tungsten Carbide blades. For cutting Vectran braided wires, fibre optics, Kevlar and small stainless steel braids. Ask for special application.
521E	115 mm	10 mm	10,5 mm	6,5 mm	ø 1,2 mm	67 g	Flush cut, high grade tool steel, polished head, ESD safe, resharpenable
							Side cutter for universal use. Medium size.
522N	115 mm	10 mm	10,5 mm	6,5 mm	ø 1,6 mm	67 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Side cutter for universal use. Medium size. Economical line.
522E	115 mm	12 mm	10,5 mm	6,5 mm	ø 1,2 mm	67 g	Flush cut, high grade tool steel, polished head, ESD safe, resharpenable
							Side cutter for universal use.
599E	115 mm	12 mm	10,5 mm	6,5 mm	ø 1,6 mm	67 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe
							Side cutter with robust head.
599TF	115 mm	11,5 mm	10,5 mm	6,5 mm	ask for cutting	67 g	Flush cut, Tungsten Carbide blades, anti-glare finish, ESD safe
					capability*		Side cutter with Tungsten Carbide blades for constant quality cuts. Resistant to small stainless steel wires.
532N	115 mm	10 mm	10,5 mm	6,5 mm	ø 1,6 mm	67 g	Super full flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Side cutter for universal use. Medium size. Economical line. Perfect full flush cut. Soft wires only.
	* 51	ovide wire sa				I	

^{*} Please provide wire sample.



Oval Head

Length 120 mm

Model	L	Α	В	С	Max. Cu	Weight	Description
812N	120 mm	15 mm	13,5 mm	7,5 mm	ø 1,8 mm	85 g	Semi flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable Side cutter for large wires. Economical line.
896E	120 mm	15 mm	13,5 mm	7,5 mm	ø 1,8 mm	85 g	Semi flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable Side cutter for hard leads, Kovar wires, connector pins, etc.
822N	120 mm	15 mm	13,5 mm	7,5 mm	ø 1,8 mm	85 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable Side cutter for large wires. Economical line.

Tapered Head



Tapered HeadMain application: cutting applications where easy access is required.

Length 110 mm

Model	L	Α	В	С	Max. Cu	Weight	Description
622NA	110 mm	9 mm	9 mm	6 mm	ø 1,0 mm	48 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Miniature side cutter. Small tapered head allows very good access. Economical line.
677E	110 mm	9 mm	9 mm	6 mm	ø 1,0 mm	48 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Miniature side cutter. Small tapered head allows very good access.

Length 115 mm

Model	L	Α	В	С	Max. Cu	Weight	Description
595T	115 mm	12 mm	10,5 mm	6,5 mm	ask for cutting	67 g	Semi flush cut, Tungsten Carbide blades, anti-glare finish, ESD safe
					capability*		Side cutter with Tungsten Carbide blades for constant quality cuts. Resistant to small stainless steel wires. Ask for special application.

^{*} Please provide wire sample.



Tapered Head

Length 115 mm

Model	L	Α	В	С	Max. Cu	Weight	Description
577E	115 mm	9 mm	10,5 mm	6,5 mm	ø 1,2 mm	67 g	Flush, high grade tool steel, anti-glare finish, ESD safe, resharpenable
OA							Side cutter for universal use. Medium size.
595E	115 mm	9 mm	10,5 mm	6,5 mm	ø 1,2 mm	67 g	Flush, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Side cutter for universal use. Medium size.
595TF	115 mm	12 mm	10,5 mm	6,5 mm	ask for cutting	67 g	Flush cut, Tungsten Carbide blades, anti-glare finish, ESD safe
					capability*		Side cutter with Tungsten Carbide blades for constant quality cuts. Resistant to small stainless steel wires.

^{*} Please provide wire sample.

Length 120 mm

Model	L	Α	В	C	Max. Cu	Weight	Description
886E	120 mm	15 mm	13,5 mm	7,5 mm	ø 1,8 mm	83 g	Flush, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Side cutter for large wires.

Relieved Head



Relieved Head

Main application: cutting applications in confined areas.

Length 110 mm

Model	L	Α	В	С	Max. Cu	Weight	Description
662NB	110 mm	9 mm	9 mm	6 mm	ø 0,8 mm	48 g	Flush, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Miniature side cutter. Super fine relieved head allows very good access. Economical line.



Relieved Head

Length 110 mm

Model	L	А	В	С	Max. Cu	Weight	Description
676E	110 mm	9 mm	9 mm	6 mm	ø 1,0 mm	48 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Miniature side cutter. Super fine relieved head allows very good access.
776E	110 mm	9 mm	9 mm	6 mm	ø 1,0 mm	48 g	Super full flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Miniature side cutter. Super fine relieved head allows very good access. Soft wires only.
632NCF	110 mm	9 mm	9 mm	6 mm	ask for cutting	48 g	Super full flush cut, high grade tool steel, anti-glare finish, ESD safe, soft materials only
					capability*		Miniature side cutter. Special fine, high precision cut exclusively designed for soft materials like small Silicone tubing in medical applications, precision connector sealing, miniature rubber gaskets or cutting of molded soft synthetic parts. Super fine relieved head allows very good access.

^{*} Please provide wire sample.

Length 115 mm

Model	L	Α	В	С	Max. Cu	Weight	Description
576Z	115 mm	9 mm	10,5 mm	6,5 mm	ø 1,2 mm	67 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Side cutter with fine relieved head. Medium size. For fine wires.
592E	115 mm	12 mm	10,5 mm	6,5 mm	ø 0,6 mm	67 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Side cutter with relieved head. Medium size. For Copper wires.
576TX	115 mm	11 mm	10,5 mm	6,5 mm	ask for cutting	67 g	Flush cut, Tungsten Carbide blades, anti-glare finish, ESD safe
					capability*		Miniature side cutter. Super fine relieved head allows very good access. Tungsten Carbide blades for constant quality cuts. Resistant to small stainless steel wires.
792E	115 mm	13 mm	10,5 mm	6,5 mm	ø 0,6 mm	67 g	Super full flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
							Side cutter with relieved head. Medium size. For fine soft wires.

Length 120 mm

Model	L	A	В	С	Max. Cu	Weight	Description
884E	120 mm	15 mm	13,5 mm	7,5 mm	ø 1,8 mm	81 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable Side cutter for large wires.

26




Specials



Specials

Model	L	Α	В	С	Max. Cu	Weight	Description
147A	120 mm	12 mm	10,5 mm	7,5 mm	ø 2,0 mm	100 g	Semi flush cut, high grade tool steel, anti-glare finish, ESD safe, compound action
MA							Compound action side cutter. Easy cutting for hard wires. 3,5 times less force needed than with conventional cutters. High cutting capacity: hard wires up to 0,5 mm, soft wires up to 2,0 mm. Flush cut on request.
884EPCM	115 mm	max.D 0,8	mm max.	B 2,0 mm	-	79 g	Flush cut, high grade tool steel, anti-glare finish,
71		В→		D			ESD safe, PCB separation Side cutter for PCB separation only. New improved design for higher blade resistance. No breakage guarantee.

Side Cutters with Ergonomic Handles*





Model	L	А	В	С	Max. Cu	Weight	Description
2212E	140 mm	10 mm	10 mm	5,8 mm	ø 1,25 mm	70 g	Semi flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable, Ergonomic Ergonomic side cutter for universal use.
2222E	140 mm	10 mm	10 mm	5,8 mm	ø 1,25 mm	70 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable, Ergonomic Ergonomic side cutter for universal use.
2232E	140 mm	10 mm	10 mm	5,8 mm	ø 1,25 mm	70 g	Super full flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable, Ergonomic Ergonomic side cutter for fine and soft wires.

^{*}Ergonomic features see page 18



Tapered Head



Tapered Head

Model	L	Α	В	C	Max. Cu	Weight	Description
2222EA	140 mm	10 mm	10 mm	5,8 mm	ø 1,0 mm	70 g	Flush, high grade tool steel, anti-glare finish, ESD safe, resharpenable, Ergonomic
							Ergonomic side cutter for universal use. Tapered head for easier access.

Relieved Head



Relieved Head

Model	L	А	В	С	Max. Cu	Weight	Description
2222EB	140 mm	10 mm	10 mm	5,8 mm	ø 0,8 mm	70 g	Flush, high grade tool steel, anti-glare finish, ESD safe, resharpenable, Ergonomic
							Ergonomic side cutter for universal use. Relieved head for working in confined areas.



Tip Cutters

Tip Cutters

Erem offers the largest variety of high precision tip cutters.

All edges are finely radiused to avoid board damaging. To find the cutter for your demand just follow the steps



Erem Blade Protection


All tip cutters have an "anti-overbite" system which prevents blades from overlapping.



Head Form

Angled

For standard tip cutting applications.



Angled Narrow

For applications in confined areas. Longer but narrow head for better reach between parts and into areas with limited access.

Straight

For vertical or horizontal tip cutting applications.



Cut


Semi Flush



These blades allow a very high resistance. Will cut malleable wires like Copper as well as hard wires. Leaves a pinch at the end of the wire.




Allow a flat cut with high cutting capacities. The edge of the wire is cut off almost squarely. Guaranteed precision even after constant usage. Thanks to faster penetration into the component the operator's effort is substantially reduced.



1. Erem Cut

2. Others



Size

110 mm Small short head, for increased cutting resistance. For almost all cutting applications.

115 mm Longer and finer head.

For cutting applications where easy access is more important than a high cutting capacity.

120 mm Strong version.

For all cutting applications where high cutting capacity is required.




Safety Lead Device

Cutting safety device, holds wire scraps. Can be adapted on 582E only. Add "W" when ordering, e.g. 582EW.



Angled Head





Length 110 mm

Model	L	Α	В	С	D	Max. Cu	Weight	Description
503ET	110 mm	12 mm	10,5 mm	6,5 mm		ask for cutting capability*	67 g	→ 30°, semi flush cut, Tungsten Carbide, anti-glare finish, ESD safe Tip cutter. Standard size. Tungsten Carbide blades for constant quality cuts even on hard wires.
503E	110 mm	12 mm	10,5 mm	6,5 mm	10 mm	ø 1,2 mm	67 g	→ 30°, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable Tip cutter. Standard size. For universal use.
504AE	110 mm	13 mm	10,5 mm	6,5 mm	10 mm	ø 1,2 mm	67 g	
503ETF	110 mm	12 mm	10,5 mm	6,5 mm		ask for cutting capability*	67 g	

^{*} Please provide wire sample.

Angled Head Small



Angled Head Small

Main applications:

for applications in confined areas.

Length 110 mm

Model	L	Α	В	С	D	Max. Cu	Weight	Description
575E	110 mm	15 mm	10,5 mm	6,5 mm	10 mm	ø 0,6 mm	67 g	
								Tip cutter. Small size. For delicate work on hybrid circuits or micro modules.



Angled Head Small

Length 115 mm


Model	L	Α	В	С	D	Max. Cu	Weight	Description
572E	115 mm	18 mm	10,5 mm	6,5 mm	6,5 mm	ø 0,6 mm	68 g	
								Tip cutter. Medium size. Relieved jaws for easier access.
593AE	115 mm	20 mm	10,5 mm	6,5 mm	4 mm	ø 1,0 mm	68 g	₹50°, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
								Tip cutter. Cuts easily DIL leads from the rear. Cuts pins on dense PCB. Ideal maintenance tool.
582E	115 mm	19 mm	10,5 mm	6,5 mm	7 mm	ø 1,0 mm	68 g	₹ 45°, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
								Tip cutter medium size. A must when working on PCB's, cutting component leads. Also ideal for rework.
582EW	115 mm	19 mm	10,5 mm	6,5 mm	7 mm	ø 1,0 mm	70 g	₹45°, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable, retention clip
								Same as 582E but with retention clip, holds wire scraps after cutting.


Length 120 mm

Model	L	Α	В	C	D	Max. Cu	Weight	Description
555E	120 mm	21 mm	10,5 mm	6 mm	6,5 mm	ø 1,2 mm	68 g	₹ 40°, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
								Tip cutter. Strong version.



Straight Tapered Head





Length 110 mm

Model	L	Α	В	С	D	Max. Cu	Weight	Description
670E	110 mm	10,5mm	9 mm	6 mm	3 mm	ø 0,6 mm	48 g	Horizontal, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
307								Miniature tip cutter. For cutting small wires in dense working areas. Vertical SMD cutter.
670EP	110 mm	10 mm	9 mm	6 mm	2 mm	ø 0,25 mm	48 g	Vertical tip cutter, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
201								Miniature tip cutter. High precision SMD lead cutting. Micro-packages up to 0,25 fine pitches before desoldering. No breakage guarantee.
								For μ-pitches under 0,5 mm use 670 EPF


Length 120 mm

Model	L	Α	В	С	D	Max. Cu	Weight	Description
570E	120 mm	22 mm	9 mm	6,5 mm	4 mm	ø 0,6 mm	67 g	Flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
								Tip cutter for horizontal or vertical tip cutting. For cutting at extreme tips.

32




Straight Head



Model	L	Α	В	C	D	Max. Cu	Weight	Description
573E	120 mm	23 mm	9 mm	6,5 mm	3,5 mm	ø 0,8 mm	67 g	Vertical, flush cut, high grade tool steel, anti-glare finish, ESD safe, resharpenable
								Tip cutter for vertical tip cutting. For fine wires.

Tip Cutters with Ergonomic Handles*





Model	L	Α	В	C	D	Max. Cu	Weight	Description
2282E	140 mm	20 mm	10 mm	5,8 mm	7 mm	ø 1,0 mm	70 g	
								Ergonomic tip cutter. Medium size. Ideal for working on PCB's or cutting component leads.


^{*}Ergonomic features see page 18



Pneumatic Side Cutters and Tip Cutters

Pneumatic Side Cutters and Tip Cutters

The Erem 1500BSF is a small lightweight air tool that can be fitted with a range of cutter heads making this tool extremely versatile. It is suitable for the cropping of conventional components, as well as small ductile or plastic parts.






Housing

Model	D	L	Weight	Description
1500BSF	28 mm	130 mm	130 g	Manual air tool
		(w.o. head)		Small precise pneumatic cutter housing. Improved lifetime and reliability. Easy interchangeable cutting heads. Requires 4- 6 bar oil-free, clean compressed air. New economical version.

Cutting Heads for 1500BSF



Side Cutters Oval Head



Model		А	В	С	Max. Cu	Weight	Description
1512N	10/1 34	10 mm	10,5 mm	6,5 mm	ø 1,6 mm	35 g	Semi flush cut, high grade tool steel, anti-glare finish, resharpenable
6	E E						Side cutter for universal use. Medium size. Economical line. Improved lifetime.
1522N	7.	10 mm	10,5 mm	6,5 mm	ø 1,6 mm	35 g	Flush cut, high grade tool steel, anti-glare finish,
	ER PAR						resharpenable Side cutter for universal use. Medium size. Economical line.
6	18						Improved lifetime.

34



Tapered Head



Tapered Head


Model	Α	В	С	Max. Cu	Weight	Description
1522NA	9 mm	10,5 mm	6,5 mm	ø 1,4 mm	35 g	Flush cut, high grade tool steel, anti-glare finish, resharpenable
						Side cutter for easier access. Medium size. Economical line. Improved lifetime.



Relieved Head

Model	Α	В	C	Max. Cu	Weight	Description
1522NB	9 mm	10,5 mm	6,5 mm	ø 1,2 mm	32 g	Flush cut, high grade tool steel, anti-glare finish, resharpenable
						Side cutter for confined areas. Medium size. Economical line. Improved lifetime.

Tip Cutters



Model	Α	В	С	D	Max. Cu	Weight	Description
1503E	12 mm	10,5 mm	6,5 mm	9 mm	ø 1,2 mm	38 g	₹30°, flush cut, high grade tool steel, anti-glare finish, resharpenable
							Tip cutter. Small size. For universal use.


Note: further head shapes available on request.




Distance Cutters

Distance Cutters

Erem distance cutters are available with fixed or adjustable cutting distance. The tips are brightly polished to avoid board damage







The Erem protective stop

screw increases the performance of the tip cutters:

Clearance B larger than the diameter = cut wire is ejected

Clearance B smaller than the wire diameter = cut wire is held

Adjust the protective stop screw D to set blade C does not hit the opposite side.

This improves the Lifetime of the blade.

Fixed Cutting Height

Model	L	Α	Е	F	Max. Cu	Weight	Description
530E	120 mm	20 mm	3 mm	1,5 mm (Standard)	ø 1,0 mm	67 g	Flush cut, high grade tool steel, polished tips, ESD safe
J611	\			(Standard)			Distance cutter. Cuts the lead to a predetermined length of 1,5 mm. Length from 0,5 mm to 2,5 mm on request, see price list. Reduces mechanical shock on components. With adjustable screw for possible wire holding.
549E	115 mm	20 mm	3 mm blade 4,5 mm	1,5 mm (Standard)	ø 1,0 mm	67 g	45°, flush cut, high grade tool steel, polished tips, ESD safe Distance cutter. Cuts the lead to a predetermined length of 1,5 mm. Lenght from 0,5 mm to 2,5 mm on request, see price list. Reduces mechanical shock on components.
500-108	120 mm	20 mm	3 mm	1,5 mm	ø 0,8 mm	67 g	Flush cut, high grade tool steel, polished tips, ESD safe
	- mand		<u>.</u>				Distance cutter. Cuts the lead to a predetermined length of 1,5 mm. Reduces mechanical shock on components.
530S	110 mm	10 mm	4 mm	1,5 mm (Standard)	ø 1,0 mm	65 g	30°, flush cut, high grade tool steel, polished tips, ESD safe Distance cutter. Cuts and flattens leads to prevent component from fallen off the circuit board. Predetermined length of 1,5 mm. Length from 0,5 mm to 2,5 mm on request.

Adjustable Cutting Height


Model	L	Α	E	F	Max. Cu	Weight	Description
530E15A	120 mm	20 mm	4,5 mm	1,2 - 6	ø 1,2 mm	70 g	Flush cut, high grade tool steel, polished tips, ESD safe
Jo A	F			mm			Distance cutter with adjustable cutting length from 1,2 mm to 6 mm with setting screw.
573EB	115 mm	23 mm	3,5 mm	0-5 mm	ø 0,8 mm	70 g	Flush cut, Plastic anvil. High grade tool steel, polished tips, ESD safe
	F	So o					Distance cutter with adjustable cutting length from 0 mm to 5 mm with setting screw. Replaceable synthetic stop, no risk of board damage.



Pliers

Pliers

Erem offer a range of pliers with standard and ergonomic handles.





Round Nose

Model	L	Α	В	С	Εø	G	Weight	Description
543E	120 mm	23 mm	9 mm	6,5 mm	0,8 mm	1,6 mm	67 g	High grade tool steel, anti-glare finish, ESD safe
								Round nose pliers with smooth jaws, very precise.

Needle Nose

Model	L	Α	В	C	E	G	Weight	Description
547	120 mm	23 mm	9 mm	6,5 mm	0,9 mm	1,2 mm	67 g	High grade tool steel, anti-glare finish, ESD safe
Man								Needle nose pliers with smooth jaws, very precise.

Flat Nose

Model	L	Α	В	С	E	G	Weight	Description
542E	120 mm	23 mm	9 mm	6,5 mm	2,4 mm	1,4 mm	67 g	High grade tool steel, anti-glare finish, ESD safe
- Ach								Flat nose pliers with smooth jaws.
531E	125 mm	23 mm	9 mm	6,5 mm	5 mm	3 mm	67 g	High grade tool steel/Nylon, anti-glare finish, ESD safe
CA								Flat nose pliers with replaceable Nylon inserts to prevent nicking e.g. for straightening precious metal, leads, etc.




Pliers

Chain Nose

Model	L	Α	В	С	E	G	Weight	Description
544E	120 mm	23 mm	9 mm	6,5 mm	1 mm	1,4 mm	67 g	High grade tool steel, anti-glare finish, ESD safe
								Chain nose pliers with smooth jaws.
29.1								
E44D	12F	22	0	6 F	1	4.4	67 ~	High grade tool stool anti-glave finish FCD cafe
544D	125 mm	23 mm	9 mm	6,5 mm	1 mm	1,4 mm	67 g	High grade tool steel, anti-glare finish, ESD safe
36 1								Chain nose pliers with smooth jaws, inside serrated.
546E	125 mm	24 mm	9 mm	6,5 mm	0,8 mm	0.8 mm	67 g	₹60°, high grade tool steel, anti-glare finish,
						.,.		ESD safe
								Chain nose pliers bent with smooth jaws.
		D	\mathcal{H}					D = 6,0 mm
-			Ğ					



Pliers with Ergonomic Handles*





Needle Nose

Model	L	Α	В	С	E	G	Weight	Description
2211P	165 mm	35 mm	10 mm	5,8 mm	1 mm	1,2 mm	80 g	High grade tool steel, anti-glare finish, ESD safe, Ergonomic
								Ergonomic needle nose pliers with smooth jaws.

Flat Nose

Model	L	Α	В	C	E	G	Weight	Description
2242E	160 mm	33 mm	10 mm	5,8 mm	3,5 mm	1,5 mm	80 g	High grade tool steel, anti-glare finish, ESD safe, Ergonomic
								Ergonomic flat nose pliers with long smooth jaws. Precise radiused edges.

^{*}Ergonomic features see page 18




EROP Cutters and Pliers

EROP Cutters and Pliers


The newly introduced EROP range from Erem offers a variety of side cutters and pliers at a budget price. The tools are manufactured from high quality tool steel have a box joint construction, burnished heads, robust opening leaf springs and replaceable soft ESD safe grips.





Side Cutters

Model	L	Α	В	С	Max. Cu	Weight	Description
EROP355	110 mm	11 mm	9,5 mm	7,5 mm	ø 1,0 mm	61 g	Semi flush cut, high quality tool steel, burnished, ESD safe
							Side cutter, tapered head, slim-line. Fine cutting edges for fine work.
EROP155	110 mm	13,5 mm	11 mm	7,5 mm	ø 1,0 mm	72 g	Semi flush cut, high quality tool steel, burnished, ESD safe
							Side cutter, round head. For assembly work on circuit boards, telephone and radio work.
EROP419	130 mm	18 mm	11 mm	8 mm	ø 2,0 mm	110 g	Semi flush cut, high quality tool steel, burnished, ESD safe
							Side cutter robust. Round head. For general use.
EROP357	110 mm	11 mm	9,5 mm	7,5 mm	ø 0,6 mm	61 g	Semi flush cut, high quality tool steel, burnished, ESD safe
							Side cutter, tapered head, slim-line. Fine cutting edges for cutting thin wires and cutting tiny components.



Tip Cutters


Model	L	Α	В	D	Max. Cu	Weight	Description
EROP331	120 mm	12 mm	12 mm	7,5 mm	ø 1,5 mm	81 g	≩ 40°, flush cut, high quality tool steel, burnished, ESD safe
4							Tip cutter bent, slim. Ideal for fine works. Exact guidance of cutting edges.



EROP Cutters

Model	L	Α	В	D	Max. Cu	Weight	Description
EROP330	130 mm	7,5 mm	7,5 mm	5,0 mm	ø 1,0 mm	84 g	₹40°, flush cut, high quality tool steel, burnished,
							ESD safe
							Tip cutter bent. For PCB applications.

EROP Pliers



Round Nose

Model	L	Α	В	C	Εø	G	Weight	Description
EROP172	125 mm	22,5 mm	9,5 mm	6 mm	0,8 mm	1,6 mm	63 g	High quality tool steel, burnished, ESD safe
								Round nose pliers. Smooth polished inside jaws for bending fine loops.

Needle Nose

Model	L	Α	В	C	E	G	Weight	Description
EROP174	120 mm	22,5 mm	9,5 mm	6,5 mm	1,5 mm	2 mm	66 g	High quality tool steel, burnished, ESD safe
								Needle nose pliers. Smooth polished inside jaws for gripping fine parts and forming wire.
EROP277	140 mm	39 mm	12 mm	7,5 mm	1,2 mm	1,8 mm	90 g	High quality tool steel, burnished, ESD safe
								Needle nose pliers. Serrated, for gripping, holding and forming wires and parts.
EROP280	170 mm	64 mm	13,5 mm	8 mm	1,8 mm	2 mm	113 g	High quality tool steel, burnished, ESD safe
								Needle nose pliers long. Oval pointed. Serrated. Robust but fine tips for work in confined areas.



EROP Pliers


Flat Nose

Model	L	Α	В	С	E	G	Weight	Description
EROP170	120 mm	22,5 mm	9,5 mm	6 mm	3 mm	1,2 mm	63 g	High quality tool steel, burnished, ESD safe
								Flat nose pliers. Slim smooth jaws for delicate work.
EROP171	120 mm	22,5 mm	9,5 mm	6 mm	4 mm	1,2 mm	67 g	High quality tool steel, burnished, ESD safe
								Flat nose pliers. Slim smooth jaws for delicate work. With larger gripping area.


Stripping Tools

High Precision Stripping Tools

Erem stripping tools are the most precise tools used in the electronic or aviation field. They are manufactured from high grade tool steel to ensure durability. To ensure that you have the correct tool for your application, send us samples of your wire and we will make recommendations.




Front Stripping



42



Stripping Tools



Side Stripping

Model	L	Α	E	F	G	Н	Wire ø	Weight	Description
552S	120 mm	21 mm	6,5 mm	6,7 mm	11 mm	9 mm	0,06 - 0,25 mm (AWG 42-30)	80 g	High grade tool steel, anti-glare finish, ESD safe, high precision Side stripping tool. Unique high precision tool. Strips one size at a time without scratching the cores. For all kind of insulation, PTFE, Tefzel, fibre optics or stranded wires. Diameter adjustable with screw plus screw stop.
		G	A		E	0			Replaceable cutting blades. Supplied with screwdriver and hex key.
502E30	120 mm	22 mm	3 mm	6,3 mm	2,4 mm	5 mm	0,25 mm (AWG 30)	67 g	High grade tool steel, anti-glare finish, ESD safe Combination side stripping tool. Fine replaceable cutting blades. Strips resistant insulations such as PTFE,, Tefzel, glass reinforced Fluoropolymere. This tool combines stripping, cutting and bending/gripping. For one specific wire diameter, AWG 30 (0,25 mm). Other diameters on request.
		Ø ® H	A F	<u> </u>			E		·

Special Stripping

Model	L	Α	D	Wire ø	Weight	Description
520E	120 mm	10 mm	11 mm	0,25 - 1,3 mm (AWG 30-16)	75 g	High grade tool steel, anti-glare finish, ESD safe, high precision
rion -						Strips one or several wires simultaneously. Particularly designed for mini or standard wire-wrapping work. Diameter adjustable with screw plus blocking nut.
	-		A	D		



Pre-Forming ToolsErem offers preforming tools for active and passive components.



For Passive Components

Model	L	Α	D	E	F	Weight	Description
554E	120 mm	13 mm	10 mm	10 mm	10 mm	70 g	High grade tool steel, anti-glare finish, ESD safe
1617							Bending pliers for component leads, etc. U-shape.
11							Max. lead ø: Diodes: 0,65 mm
*							Capacitors: 0,7 mm Resistors: 1/2 W
				→ \ ′	- 3 mm		nesistuis. 1/2 vv
			F		~		
			E		R2		
		<u> </u>	7				
		1	E +				
554A A	120 mm	23 mm	5,6 mm	4 mm	4,5 mm	70 g	High grade tool steel, anti-glare finish, ESD safe
16/10							Bending pliers for component leads, etc. U-shape. Axial forming action.
(6/1)							Max. lead ø:
8							Diodes: 0,65 mm
		A	\rightarrow	→ / /	← 4 max.		Capacitors: 0,7 mm Resistors: 1/2 W
			Ĭ		7		
			E		R 1.5		
		<u> </u>	E -				
554B	120 mm	23 mm	5,6 mm	2,5 mm	4,5 mm	70 g	High grade tool steel, anti-glare finish, ESD safe
Mon							Bending pliers with tapered nose. For component leads, etc. U-shape. Axial forming action.
							Max. lead ø: Diodes: 0,65 mm
		A		→ \ /*	← 4 max.		Capacitors: 0,7 mm Resistors: 1/2 W
			非 _		\\-\		
					R 1.5		
		D Ţ	E				
			-				



Model	L	Α	D	E	F	Weight	Description
554TX	120 mm	20 mm	6,5 mm	6,5 mm	4 mm	70 g	High grade tool steel, anti-glare finish, ESD safe
							Bending pliers for forming stress reliefs. One lead left, one lead right in one single operation. For stable insertion. Max. lead ø: Diodes: 0,65 mm
		- A	D D F		R 1.2		Capacitors: 0,7 mm Resistors: 1/2 W
50788	120 mm	23 mm	-	4 mm	3 mm	67 g	High grade tool steel, anti-glare finish, ESD safe, cut + bend
NO 19							Bending pliers. Cuts and bends leads of popular radial components to a specific length.
		 	A	+ +	-3		Max. lead ø: Diodes: 0,65 mm Capacitors: 0,7 mm
			L L	3 R	= 1.5	√ ↑ Min. 4	Resistors: 1/2 W
50789Z	120 mm	23 mm	3,3 mm	3,5 mm	-	67 g	High grade tool steel, anti-glare finish, ESD safe, cut + bend
							Bending pliers. Cuts and bends leads of various types of components.
							Max. lead ø:
	_					<u>_</u>	Diodes: 0,65 mm Capacitors: 0,7 mm Resistors: 1/2 W
		4	<u>t</u>	→ ← 2,5	7 → -	•	
		D 1	E				



Pre-Forming Tools for Active Components





For Active Components


Model	L	K	M I	Weight	Description		
500103A	120 mm	max.	3-12 mm -	85 g	High grade tool steel, anti-glare finish, ESD safe		
CA		15 mm			High precision preforming tool. Bends flat parts, contacts, power transistors, triac leads, etc. to a right angle. Adjustable with screw.		
	K	M		,			
500210E	120 mm	max.	3,8-15 mm -	85 g	High grade tool steel, anti-glare finish, ESD safe, cut + bend		
		11 mm			High precision preforming tool. Improved version of 500103A. Cuts and bends TO series, power transistor, LEDs, etc. simultaneously at 90° without stressing the component. Simple adjustment (M) and replaceable cutting blade.		
	ĸ	M					
500104A	120 mm	max.	3,5-15 mm 2,54	mm 85 g	3 leads, high grade tool steel, anti-glare finish, ESD safe		
		13 mm			High precision preforming tool for 3 leads. Bends TO 126, 218, 220, power transistor leads, etc. at 90° in two rows. Adjustable (M) with screw.		
	1,	K		·	_		
500104AI	120 mm	max.	3,5-15 mm 2,54	mm 85 g	3 leads, high grade tool steel, anti-glare finish, ESD safe, central lead backwards		
2.10					High precision preforming tool for 3 leads. Bends TO 126, 218, 220, power transistor leads, etc. at 90° in two rows. Adjustable (M) with screw. Central lead backwards.		
	l)						




For Active Components

Model	L	K	M	I	Weight	Description
500154A	120 mm	max.	4,5-9,5 mm	2,54 mm	90 g	5 leads, high grade tool steel, anti-glare finish, ESD safe
		13 mm				High precision preforming tool for 5 leads Bends TO 126, 218, 220, power transistor leads, etc. at 90° in two rows. Adjustable (M) with screw.
		K				
500154AI	120 mm	max. 13 mm	4,5-9,5 mm	2,54 mm	90 g	5 leads, high grade tool steel, anti-glare finish, ESD safe, opposite leads backwards High precision preforming tool for 5 leads Bends TO 126, 218, 220, power transistor leads, etc. at 90° in two rows. Adjustable (M) with screw. Opposite leads backwards.
	ļ	K				

For Flat Packs, Quads



For DIL / IC






IC and SMD Tools

IC and SMD Tools


Erem IC and SMD tools for inserting, extracting, straightening and cutting of ICs and SMDs



Inserting and Extracting

Model	L	Model	E	Wei	ght	Description
505	120 mm	505C 505E 505A 505BGC 505BG	20 mm 27 mm 32 mm 36 mm 36 mm	-		High grade tool steel, anti-glare finish, ESD safe Inserting and extracting pliers. Available sizes see chart. Adjustable with screw. Insertion: squeeze IC pins. Extraction: adjust jaws width so that pins stay in the middle of holes.
	Fins: 14-	16 22	.600	505BQC 28	505BG 28	

Straightening





IC and SMD Tools

Cutting

Model	L	Α	D	E	Weight	Description
670EP	110 mm	10 mm	3 mm	2 mm	48 g	Flush, high grade tool steel, anti-glare finish, ESD safe, resharpenable
						High precision tip cutter. For cutting leads of SMD micro packages up to 0,25 mm or fine pitch components less than 1/20". Cuts pins before heat desoldering. Essential SMD tool. No breakage guarantee. For µ-pitches below 0,5 mm model 670EPF is necessary. Please supply IC
			E			together with order.
593AE	115 mm	20 mm	4 mm	-	67 g	Flush, high grade tool steel, anti-glare finish, ESD safe, resharpenable High precision tip cutter bent. For cutting DIL leads from the rear. Ideal maintenance tool. Cuts pins before heat desoldering.
		D				

Trimming


Model	L	Α	D	E	F	Weight	Description
509E	120 mm	21 mm	3,5 mm	21,5 mm	1,5 mm	74 g	8 pins, high grade tool steel, anti-glare finish, ESD safe, trim
							Trimming pliers. Trims an entire row of 8 pins to the same length. The lead tips are cut flat. For multiple DIL / IC leads. Before insertion or after soldering.
	4	E		0	A F		




Fibre Optic Tools

Fibre Optic Tools

High precision tools for working on fibre optics.





Side Stripping

Model	L	Α	E	F	G	Н	Wire ø Weight	Description
5525	120 mm	21 mm	6,5 mm	6,7 mm	11 mm	9 mm	0,06 - 80 g 0,25	High grade tool steel, anti-glare finish, ESD safe, high precision
TO TO		G	A P O O	H	_ E <u> </u>	0	mm AWG 42 - 30	Side stripping tool. Unique high precision tool. Strips one size at a time without scratching the cores. For all kind of insulation, PTFE., Tefzel, fibre optics or stranded wires. Diameter adjustable with screw plus screw stop. With replaceable cutting blade. Supplied with screwdriver and hex key. Fixed standard Ø like 125 µ on request.

Cutting

Model	L	Α	В	C	Weight	Description
599FO	115 mm	11,5 mm	10,5 mm	6,5 mm	67 g	A unique high precision cutter for Kevlar® silks
						Cuts all silks even very close to fibre core. Avoid any other application.
599TFO	115 mm	15 mm	10,5 mm	6,5 mm	67 g	Semi flush cut, Tungsten Carbide blades, anti-glare finish, ESD safe
						Side cutter with Tungsten Carbide blades. For cutting Vectran braided wires, fibre optics, Kevlar and small stainless steel braids. Ask for special application.

Holding / Gripping

Model	L	Weight	Description
249SA	130 mm	20 g	Special stainless steel / PPS, anti-glare finish, non-magnetic, ESD safe, suitable for fibre optics
			Precision tweezers with serrated grips and synthetic tips (PPS). Heat resistant up to 250°C (480°F). Resistant to acids and solder. Waterproof, ESD safe. Does not damage fibre optic cores.

50



Kits

Kits

Erem kits offer a range of popular tweezers, cutters and pliers in different combinations.



Kit for SMD Handling

	L	Width	Thickness	Weight	Description
3900KC	130 mm	230 mm	30 mm	350 g	Black plastic case, cushioned, ESD safe, consists of:
					Tweezers 51SA Precision tweezers 115 mm, bent 30°, relieved. Very fine tips. Stainless steel, anti-glare finish, non-magnetic.
					102ACA SMD tweezers 115 mm, with angled head and blunted edges to



avoid board damaging. For handling of small components. Special stainless steel, anti-glare finish, non-magnetic.

103ACA SMD tweezers 115 mm, with angled head 45° and blunted edges to avoid board damaging. For horizontal handling of small components. Special stainless steel, anti-glare finish, non-magnetic.

150SAMB SMD tweezers 120 mm, bent 40°, serrated handles. For gripping small cylindrical parts \emptyset 1,2 - 2,5 mm, special stainless steel, anti-glare finish, non-magnetic.

150SAMF SMD tweezers 120 mm, straight, serrated handles. For gripping small cylindrical parts ø 1,2 – 2,5 mm, special stainless steel, anti-glare finish, non-magnetic.

Cutters

670EP High precision tip cutter 110 mm. For cutting leads of SMD micro packages up to 0,25 mm or fine pitch components less than 1/20". Flush cut, high grade tool steel, anti-glare finish, ESD safe.




Vacuum Manipulator

Vacuum Manipulator

The Erem 3000 series offers a vacuum micro manipulation system for precise handling of tiny components as well as flat parts. For use in mechanical assembly, laboratories, etc. The advantages are:

- easy pick up of components or silicon wafers
- immediate pick up and release of the parts
- full 360° rotating system
- direct axial air switch
- ergonomic shape reduces hand and wrist fatigue
- ESD safe





Housing

Model	L	Diameter	Weight	Description
3000ESD	140 mm	10 mm	35 g	Housing
				Housing with axial air switch, ergonomic shape, serrated grip area, ESD safe. Professional device.

Inserts for Housing 3000ESD Adapter

Model	L	Weight	Description
3200	25 mm	15 g	Adapter 360° rotating head for housing 3000ESD. With straight nozzle, stainless steel for direct pick-up or as adapter for suction tips or suction cups.
3231	5 mm	5 g	Adapter Adapter fix. For use with suction tips series 3300.
3232	15 mm total	3 g	Adapter Can be used with or without tips, fix. Holds either suction cup 2052E or tips 2040Z, 2041Z, 2044Z.



Vacuum Manipulator

Suction Tips Straight

Model	Outside ø	Inside ø	Description
2040Z	0,70 mm	0,15 mm	Suction tip straight,PTFE, tip
			For use with rotating head 3200 or fix adapter 3232.
2044Z	1,30 mm	0,90 mm	Suction tip straight, Polyethylene tip
			For use with rotating head 3200 or fix adapter 3232.
2041Z	2,0 mm	1,40 mm	Suction tip straight, Polyethylene tip
			For use with rotating head 3200 or fix adapter 3232.



Suction Needles

Model	Outside ø	Inside ø	Description
3303	0,30 mm	0,16 mm	Suction needle bent 45°, stainless steel For use with fix adapter 3231.
3305Z	0,50 mm	0,25 mm	Suction needle bent 45°, stainless steel For use with fix adapter 3231.
3310Z	1,0 mm	0,65 mm	Suction needle bent 45°, stainless steel For use with fix adapter 3231.
3315	1,5 mm	1,0 mm	Suction needle bent 45°, stainless steel For use with fix adapter 3231.
3330	3,0 mm	2,5 mm	Suction needle bent 45°, stainless steel For use with fix adapter 3231.


Suction Cups


Model	Diameter ø	Description
2052E	4,5 mm	Suction cup, Silicone rubber
		For use with rotating head 3200 or fix adapter 3232.



Wafer Handling

Wafer Handling . 3000 WESD 35003A







Accessories

Model	Description
3714Z	Pump
	Membrane pump 230V, silent running, air volume 5 l/min, max. vacuum -250 mbar. (not suitable for wafer pick up)
3008ESD	Tubing System
	Tubing system flexible, 1,8 m, ESD safe.
3717	Filter
	Filter for tubing system 3008ESD.
3740	Table Holder
	Table holder for 3000ESD and 3000WESD housing (without accessory).

Vacuum Kit

Model	Size	Weight	Description
3000KCESD	400 x 320 x 105 mm	2,2 kg	Black plastic case, cushioned, consists of:
			3000ESD Housing 3200 Head / adapter rotating 3231 Adapter fixed 3305Z, 3310Z, 3315 Suction needles bent 2052E suction cup Ø 4,5 mm KDS 260L suction cup Ø 9,5 mm 3740 Table holder for 3000ESD 3714Z Membran pump 230 V 3008ESD Tubing system 1,8 m 3717 Air filter 102ACA SMD tweezers 115 mm







Index Tweezers

Model	Page	Model	Page	Model	Page
024C	16	51SA	9 11	OOCSA .	
1SA		64SA			
2ASA		03A3A	10	vv2	
2ASARU	11 11	91SA	14		
2SASL		102ACA 102ACAX 103ACA	12		
3CBS					
3CSA 3CSASL 3CTA	5 5	140SA	14		
3SA	6	1413AFП			
ACA.	0	150SAD	12		
4SA		150SAMB 150SAMF 151SA 249SA	12		
5ASA	9 9	249CER			
5CSA	8	500ASA	14		
5SASL		600ASA	14		
7SA		940AS	13		
11N	6				
15AGS	15	AAS			
20AS		AAZ	6	6 (1)	
24SA	11	AM	7		carbone steel c) ergonomic handles
29W3029Y	15	E2ASA	11 11	M N PYR RU	Brass, soft material to avoid damage, no sparks Nickel-Silver alloy, absolut nicht Pyroplast coating anti adhesive coating
30SA	13	EOOSA	11	S SA, CA	stainless steel special stainless steel,
32BSA25	12	M4AS		SL TA	non-magnetic, acid resistant economy version Titanium, non-magnetic, lightweight, high temperature resistant
40SA	12			Z	Nickel plated



Index Cutters and Pliers

Model Pag	e Model	Page	Model Page
147A	599TFO		3305Z
500108			331553
500103A		22	3330
500104A			3503A
500154A			3714Z55
500154AI			371755
500210E		24	374055
502E30			3900KC
503ET			
503ETF			EROP155
504AE			EROP170
505A/BG/BGC/C/E		32, 49	EROP171
50788			EROP172
508Z			EROP277
509E	19		EROP280
510AE			EROP330
511E			EROP331
512E			EROP355
520E			EROP419
521E	80013C		
522E			
522N			
530E15A		24	
530S	86 884E		
531E			
532N			
542E			
544D			
544E	1500BSF		
546E			
547		34 34	
552E			
5525			
554A	14		
554B		F2	
554E			
555E			
570E	2052E		
572E			
573E		27 27	
575E			
576TX			
576Z	2232E	27	
577E		39	
582E			
592E			
593AE			
595E			
595T		54	
595TF			
599E			
599FO			
599T	3303	53	



Campbell[®] Caulk Master[®] Crescent[®] Diamond[®] Erem[®] Kahnetics[®] Lufkin[®] Nicholson[®] Plumb[®] H.K.Porter[®] Weller[®] Wire-Wrap[®] Wiss[®] Xcelite[®]

G E R M A N Y Cooper Tools GmbH Carl-Benz-Str. 2 74354 Besigheim Tel: (07143) 580-0 Fax: (07143) 580-108

Cooper Tools S.A.
25 Rue Maurice Chevalier BP 46
77832 Ozoir-la-Ferrière Cedex
Tel: (01) 60.18.55.40
Fax: (01) 64.40.33.05

GREAT BRITAIN
Cooper Tools LtD.
Suite 15. Coniston House
Town Centre
Washington, Tyne & Wear
NE38 7RN
Tel: (0191) 419 7700
Fax: (0191) 417 9421

Cooper Italia S.p.A. Viale Europa 80 20090 Cusago (MI) Tel: (02) 9033101 Fax: (02) 90394231 S W I T Z E R L A N D **Errem S.A.** Rue de la Roselière 8 1400 Yverdon les Bains Tel: (024) 426 12 06 Fax: (024) 425 09 77