Digital Fiber Sensors E3X-DA-S/MDA

CSM_E3X-DA-S_MDA_DS_E_9_1

OMRON's Next-generation Platform for a Wide Range of Detection

- Features a Power Tuning function that optimizes light reception at the press of a button.
- Combines newly developed 4-element LEDs with an APC circuit to ensure stable, long-term LED performance.
- Utilizes OMRON's innovative wire-saving connector.
- 2-channel models achieve the thinnest profile in the industry, at only 5 mm per channel.
- 2-channel models also offer AND/OR control output.

Be sure to read Safety Precautions on



Features


page 15.

Equipped with an Industry's First Power Tuning (Optimum Light Setting) Function

The E3X-DA-S/MDA features a Power Tuning function that optimizes power at the press of a button.

This function easily but securely resolves saturation due to short sensing distances or insufficient incident light due to long sensing distances.


In addition, the response speed does not change as mode selection has tuned the power.



Adoption of Newly Developed 4-Element LEDs and an APC (Auto Power Control) Circuit Achieves Long-term Reliable Detection at the Highest Level in the Industry

The long-term reliable detection at the highest level in the industry is achieved with the innovative APC circuit whose performance is proved by E3X-DA-N series and the newly developed high-power LEDs (4-element type) to ensure super stable, long-term LED performance.


Stable performance is always available without the ON/OFF setting of an APC circuit.



OMRON's Innovative Wire-saving Connector Inherited from the E3X-DA-N

The amplifier units with connectors supply the power to slave connectors via a master connector. This offers three following advantages.

 Greatly reduced wiring work
 Improved space usability due to the unnecessity of relay connectors
 Simple stock management due to the unnecessity of distinction between master and slave for amplifiers



Models available for a wide variety of applications at manufacturing sites

Industry Leading Two Amplifiers Loaded in a Small Body ···· 2-channel models

Two amplifiers are loaded in a 10 mm-wide body. Space usability can be approximately doubled. In addition, approximately 40% of the energy can be saved.

(compared to the value per channel of the former model)






UP/DOWN kevs

Simpler Digital Fiber Sensors Simple & Easy Single-function Models

Required performance and functions have been reviewed from basic points to improve high-performance but hard-to-use digital models. Digital fiber sensors, used in the sense as if using volume type sensors, are added to the basic functions such as an APC function and digital display.



High-speed and High-resolution Analog Output Supports Wide Variety of Applications

Analog Control Output

The voltage in the range of 1 to 5 V is output according to the incident level (digital display). Wide variety of applications is possible including positioning control or difference detection with multiple levels.



Area Output Function Area Judgment Is Possible ····Advanced, Twin-output Models


Only one sensor is enough for area judgment for height or others that has required multiple sensors.

Setting two threshold values allows easy output inside and outside range.

High-speed and High Resolution

Detection modes can be switched in accordance with applications. High-speed response of 80 μs (super-high-speed mode) supports the positioning controls that require high-speed control.








Sticker detection

Remote Input Function Sensors Controlled from Outside ····Advanced, Externalinput Models

Remote settings for teaching/power tuning/light OFF are possible with input signals. The remote input function meets the diversifying demands such as remote settings made for frequent teaching due to level change corresponding to workpiece change or remote operation check of sensors before operation.

Equipped with an Industry's First ATC Function that Resolves Problems at Manufacturing Sites ····Advanced ATC Models

OMRON's unique algorithm is equipped to distinguish dust or dirt and the change of workpieces. Automatic correction of threshold values by sensors in accordance with changes prevents malfunctions and improves the operating rates of machines. The ATC function is especially effective for the applications that require high-resolution detection.



····Advanced Analog Output Models

omron

Ordering Information

Amplifier Units

Amplifier Units with Cables (2 m) [Refer to Dimensions on page 17.]

Item		Appearance	Functions	Mc	Model		
nem	iciii		Appearance		PNP output		
Single-function models	Single-function models			E3X-DA11SE-S 2M	E3X-DA41SE-S 2M		
Standard models				E3X-DA11-S 2M	E3X-DA41-S 2M		
	Green LED		Timer, Response speed change	E3X-DAG11-S 2M	E3X-DAG41-S 2M		
Mark-detecting models (multiple color light sources)	Blue LED		Timer, Response speed change	E3X-DAB11-S 2M	E3X-DAB41-S 2M		
	Infrared LED			E3X-DAH11-S 2M	E3X-DAH41-S 2M		
	External-input models	Remote setting, counter, differential oper- ation		E3X-DA11RM-S 2M	E3X-DA41RM-S 2M		
Advanced models	Twin-output models		Area output, self-diagnosis, differential operation	E3X-DA11TW-S 2M	E3X-DA41TW-S 2M		
Advanced models	ATC function models	-	ATC (Threshold value automatic correc- tion)	E3X-DA11AT-S 2M	E3X-DA41AT-S 2M		
	Analog output models	-	Analog output models	E3X-DA11AN-S 2M	E3X-DA41AN-S 2M		
2-channel models			AND/OR output	E3X-MDA11 2M	E3X-MDA41 2M		

Amplifier Units with Connectors

Item		Appearance Functions		Model		
item	nem		Appearance Functions		PNP output	
Single-function models				E3X-DA6SE-S	E3X-DA8SE-S	
Standard models		+		E3X-DA6-S	E3X-DA8-S	
	Green LED	-	Timer, Beenenee anood shange	E3X-DAG6-S	E3X-DAG8-S	
Mark-detecting models (multiple color light sources)	Blue LED		Timer, Response speed change	E3X-DAB6-S	E3X-DAB8-S	
(maniple color light sources)	Infrared LED			E3X-DAH6-S	E3X-DAH8-S	
	External-input models		Remote setting, counter, differential op- eration	E3X-DA6RM-S	E3X-DA8RM-S	
Advanced models	Twin-output models		Area output, self-diagnosis, differential operation	E3X-DA6TW-S	E3X-DA8TW-S	
	ATC function models		ATC (Threshold value automatic correc- tion)	E3X-DA6AT-S	E3X-DA8AT-S	
2-channel models			AND/OR output	E3X-MDA6	E3X-MDA8	

Ratings and Specifications

				Contr	ol output/	/input	Functions						
		Light source	Response time	ON/OFF output	Input	Analog output	Power tuning	Timer	Interfer- ence pre- vention	Differen- tial detec- tion	counter	ATC	
Single-fund	ction models		1 ms	Ombu									
Standard r	nodels	Red LED	50 μs to 4 ms	Only main			0	0	0				
Mark- E3>	E3X-DA G-S	Green LED	50 1	0.1									
detecting	3X-DA B-S	Blue LED	50 μs to 4 ms	Only	main			0	0 0	0			
models	E3X-DA H-S	Infrared LED	4 1115	main									
	Twin-output models		50 μs to 4 ms	Only main	(1 line)						0		
Ad-	External-input models		80 µs to 4 ms	Main + sub (2 lines)						0			
vanced models	ATC function models	Red LED	130 μs to 4 ms				0	0	0			0	
	Analog output	-	80 μs to 4 ms	Only main		(1 line)							
2-channel	models	Red LED	130 μs to 4 ms	Main + main (2 inde- pendent lines)			0	0	0				

Amplifier Unit Connectors (Order Separately) Note: Protector seals are provided as accessories. [Refer to *Dimensions* on page 19.]

The constant and provided as accessiones. [refer to Dimensione on page 10.]							
Item	Item Appearance		No. of con- ductors	Model			
Master Connector			3	E3X-CN11			
		2 m	4	E3X-CN21			
Slave Connector		2	1	E3X-CN12			
Slave Connector			2	E3X-CN22			

Combining Amplifier Units and Connectors

Amplifier Units and Connectors are sold separately. Refer to the following tables when placing an order.

Model	NPN output	PNP output		Master Connector	Slave Connector	
Single-function models	E3X-DA6SE-S	E3X-DA8SE-S	_			
Standard models	E3X-DA6-S	E3X-DA8-S	_			
Mark-detecting models (multiple color light	E3X-DAG6-S	E3X-DAG8-S		E3X-CN11	E3X-CN12	
	E3X-DAB6-S	E3X-DAB8-S	_			
sources)	E3X-DAH6-S	E3X-DAH8-S				
	E3X-DA6TW-S	E3X-DA8TW-S			Fox 0100	
Advanced models	E3X-DA6RM-S	E3X-DA8RM-S	_	E3X-CN21		
	E3X-DA6AT-S	E3X-DA8AT-S		E3X-CINZ I	E3X-CN22	
2-channel models	E3X-MDA6	E3X-MDA8				

Amplifier Units (5 Units)

+ 1 Master Connector + 4 Slave Connectors

Mobile Console (Order Separately) [Refer to Dimensions on page 20.]

Appearance	Model	Remarks
	E3X-MC11-SV2 (model number of set)	Mobile Console with Head, Cable, and AC adapter pro- vided as accessories
	E3X-MC11-C1-SV2	Mobile Console
	E3X-MC11-H1	Head
	E39-Z12-1	Cable (1.5 m)

Note: Use the E3X-MC11-SV2 Mobile Console for the E3X-DA-S/MDA-series Amplifier Units.

The E3X-MC11-SV2 is an upgraded version of the E3X-MC11-S that is fully interchangeable with the older model.

Accessories (Order Separately)

Mounting Bracket [Refer to E39-L/F39-L/E39-S/E39-R.]						
Appearance	Model	Quantity				
Contraction of the second seco	E39-L143	1				

End Plate [Refer to PFP-...]

Appearance	Model	Quantity
	PFP-M	1

Ratings and Specifications

Refer to pages 17 to 20 for dimensions.

Amplifier Units

	_	Single-function	Standard	Mark-detecting	models (multiple col	or light sources)		
	Туре	models	models	Green LED	Blue LED	Infrared LED		
Item	Model	E3X-DA SE-S	E3X-DA S	E3X-DAG -S	E3X-DAB -S	E3X-DAH -S		
Light sour	ce (wavelength)	Red LED (635 nm)	35 nm) Green LED (525 nm) Blue LED (470 nm) Infrared LED (870nm)					
Power sup	oply voltage	12 to 24 VDC ±10%,	ripple (p-p) 10% max.	1		1		
Power cor	nsumption	960 mW max. (curren	t consumption: 40 mA	max. at power supply	voltage of 24 VDC)			
Control ou	ıtput		oltage: 26.4 VDC; NPN nax.; residual voltage:					
Remote co	ontrol input	No-voltage input (contact/non-contact)		-				
Protection	circuits	Reverse polarity for p	ower supply connectio	n, output short-circuit				
	Super-high- speed mode		Operate: 48 µs, reset	: 50 μs *1, *2				
Re- sponse	High-speed mode		Operate/reset: 250 μs	3				
time	Standard mode	Operate or reset: 1 m	s					
	High-resolution mode		Operate or reset: 4 m	S				
Sensitivity	setting	Teaching or manual r						
	Power tuning		•	and reception gain, dig				
	Timer function	 Select from OFF-delay, ON-delay, or one-shot timer. 1 ms to 5 s (1 to 20 ms set in 1-ms increments, 20 to 200 ms set in 10-ms increments, 200 ms to 1 s set in 100-ms increments, and 1 to 5 s set in 1 s-increments) 						
Func- tions	Automatic power control (APC)	High-speed control method for emission current						
	Zero-reset	Negative values can be displayed. (Threshold value is shifted.)						
	Initial reset	Settings can be returned to defaults as required.						
	Mutual interfer- ence prevention	Possible for up to 10	Units *3					
Display		Operation indicator (orange)	Operation indicator (orange), Power Tuning indicator (orange)					
Digital dis	play	incident level + threshold	Select from incident level + threshold or other 6 patterns					
Display or	ientation	Switching between normal/reversed display is possible.						
Ambient il (Receiver	lumination side)		,000 lux max.					
Ambient te	emperature range	Operating: Groups of 1 to 2 Amplifiers: -25°C to 55°C Groups of 3 to 10 Amplifiers: -25°C to 50°C Groups of 11 to 16 Amplifiers: -25°C to 45°C Storage: -30°C to 70°C (with no icing or condensation)						
Ambient h	umidity range	Operating and storag	e: 35% to 85% (with no	condensation)				
Insulation	resistance	20 $M\Omega$ min. (at 500 V	DC)					
Dielectric	strength	1,000 VAC at 50/60 H						
Vibration	resistance			ble amplitude for 2 hrs	each in X, Y and \overline{Z} dir	ections		
Shock res			, for 3 times each in X,					
-	protection		Protective Cover attac	ched)				
Connectio		Pre-wired or amplifier						
Weight (pa	acked state)			nit connector model: A	pprox. 55 g			
Materials	Case	Polybutylene terephth	alate (PBT)					
Access	Cover	Polycarbonate (PC)						
Accessori	65	Instruction manual						

*1. Communications are disabled if the detection mode is selected during super-high-speed mode, and the communications functions for mutual interference prevention and the Mobile Console will not function.
*2. PNP output is as follows: Operate: 53 µs, reset: 55 µs.
*3. Mutual interference prevention can be used for only up to 6 Units if power tuning is enabled.

			Advance	Advanced models						
	Туре	External input mod- els	Twin output mod- els	ATC function mod- els	Analog output mod- els	2-channel models				
Item	Model	E3X-DA RM-S	E3X-DA TW-S	E3X-DA□AT-S	E3X-DA AN-S	E3X-MDA				
Light so	urce (wavelength)	Red LED (635 nm)								
Power s	upply voltage	12 to 24 VDC ±10%, ri	ople (p-p) 10% max.							
Power c	onsumption	1,080 mW max. (curren	nt consumption: 45 m	A max. at power supply	v voltage of 24 VDC)					
	ON/OFF output	Load power supply voltage: 26.4 VDC; NPN/PNP open collector; load current: 50 mA max.; residual voltage: 1 V max.								
Con- trol output	Analog output									
	control input	No-voltage input (contact/non-contact) *1								
Protecti	on circuits	Reverse polarity for power supply connection, output short-circuit								
	Super-high-	Operate: 48 μs,	Operate or reset:	Operate or reset:	Operate or reset:	Operate or reset:				
_	speed mode	reset: 50 μs *2, *3, *4	80 μs *2	130 μs *2	80 μs *2	130 μs *2, *5				
Re- sponse	High-speed mode	Operate or reset: 250 µ	Operate or reset: 450 µs							
time	Standard mode	Operate or reset: 1ms								
	High-resolution mode	Operate or reset: 4ms								
Sensitiv	ity setting	Teaching or manual m	ethod							
	Power tuning	Light emission power a	nd reception gain, dig	gital control method						
	Differential de- tection	Switchable between sin Single edge: Can be se Double edge: Can be s	-							
	Timer function	Select from OFF-delay 1 ms to 5 s (1 to 20 ms increments, and 1 to 5	set in 1-ms increment	ts, 20 to 200 ms set in 1	10-ms increments, 200 m	is to 1 s set in 100-ms				
Func-	Automatic pow- er control (APC)	High-speed control me		,						
tions	Zero-reset	Negative values can be	e displayed. (Thresho	ld value is shifted.)						
	Initial reset	Settings can be returned	ed to defaults as requi	red.						
	Mutual interfer- ence prevention	Possible for up to 10 U	nits *6			Possible for up to 9 Units (18 channels) *				
	Counter	Switchable between up counter and down counter. Set count: 0 to 9,999,999								

	Contact input (relay or switch)	Non-contact input (transistor)
NPN	ON: Shorted to 0 V (sourcing current: 1 mA max.). OFF: Open or shorted to Vcc.	ON: 1.5 V max. (sourcing current: 1 mA max.) OFF: Vcc - 1.5 V to Vcc (leakage current: 0.1 mA max.)
PNP	ON: Shorted to Vcc (sinking current: 3 mA max.). OFF: Open or shorted to 0 V.	ON: Vcc - 1.5 V to Vcc (sinking current: 3 mA max.) OFF: 1.5 V max. (leakage current: 0.1 mA max.)

*2. Communications are disabled if the detection mode is selected during super-high-speed mode, and the communications functions for mutual interference prevention and the Mobile Console will not function.
*3. PNP output is as follows: Operate: 53 µs, reset: 55 µs.
*4. When counter is enabled: 80 µs for operate and reset respectively.
*5. When differential output is selected for the output setting, the second channel output is 200 µs for operation and reset respectively.
*6. Mutual interference prevention can be used for only up to 6 Units if power tuning is enabled.
*7. Mutual interference prevention can be used for up to 5 Units (10 channels) if power tuning is enabled.

			Advance	d models				
	Туре	External input models	Twin-output mod- els	ATC function mod- els	Analog output models	2-channel models		
Item	Model	E3X-DA RM-S	E3X-DA TW-S	E3X-DA AT-S	E3X-DA AN-S	E3X-MDA		
Func- tions	I/O setting	External input set- ting (Select from teaching, power tun- ing, zero reset, light OFF, or counter re- set.)	Output setting (Select from channel 2 output, area out- put, or self-diagno- sis.)	Output setting (Se- lect from channel 2 output, area output, self-diagnosis out- put, or ATC error output)	Analog output set- ting (offset voltage adjustable)	Output setting (Select from channel 2 output, AND, OR, leading edge sync, falling edge sync, or differential output)		
Display		Operation indicator (orange), Power Tuning indicator (or- ange)		Operation indicator for channel 1 (orange), Operation indicator for channel 2 (orange) Power Tuning indi- cator (orange)				
Digital dis	play	Select from incident level + threshold or other 7 patterns	Select from incident lo	Select from incident level for channel 1 + incident level for channel 2 or other 7 patterns				
Display or	ientation	Switching between normal/reversed display is possible.						
Ambient ill (Receiver		Incandescent lamp: 10,000 lux max. Sunlight: 20,000 lux max.						
Ambient te	emperature range	Operating: Groups of 1 to 2 Amplifiers: -25°C to 55°C Groups of 3 to 10 Amplifiers: -25°C to 50°C Groups of 11 to 16 Amplifiers: -25°C to 45°C Storage: -30°C to 70°C (with no icing or condensation)						
Ambient h	umidity range	Operating and storage: 35% to 85% (with no condensation)						
Insulation	, ,	$20 \text{ M}\Omega$ min. (at 500 V						
Dielectric	strength	1,000 VAC at 50/60 H	,					
Vibration r	`	Destruction: 10 to 55	Hz with a 1.5-mm doul	ble amplitude for 2 hrs	each in X, Y and Z dir	rections		
Shock resi	istance	Destruction: 500 m/s ²	, for 3 times each in X	, Y and Z directions				
Degree of	protection	IEC 60529 IP50 (with	Protective Cover attac	ched)				
Connectio	n method	Pre-wired or amplifier						
Weight (pa	cked state)	Pre-wired model: App	rox. 100 g, Amplifier u	nit connector model: A	pprox. 55 g			
Materials	Case	Polybutylene terephth	alate (PBT)					
	Cover	Polycarbonate (PC)						
Accessorie	es	Instruction manual						

Amplifier Unit Connectors

Item	Model	E3X-CN11/21/22	E3X-CN12					
Rated	current	2.5 A						
Rated	voltage	50 V						
Contac	ct resistance	20 m Ω max. (20 mVDC max., 100 mA max.) (The figure is for connection to the Amplifier Unit and the adjacent Connector. It does not include the conductor resistance of the cable.)						
No. of	insertions	Destruction: 50 times (The figure for the number of insertions and the adjacent Connector.)	s is for connection to the Amplifier Unit					
Mate-	Housing	Polybutylene terephthalate (PBT)						
rials								
Weigh (packe	t d state)	Approx. 55 g	Approx. 25 g					

Mobile Console

Item Model	E3X-MC11-SV2
Applicable Sensors	E3X-DA-S E3X-MDA E3C-LDA E2C-EDA
Power supply voltage	Charged with AC adapter
Connection method	Connected via adapter
Weight (packed state)	Approx. 580 g (Console only: 120 g)

Refer to *Instruction Manual* provided with the Mobile Console for details.

(Unit: mm)

Sensing Distance Through-beam Models

		Model		E3X-D	DA⊡-S		E3X-MDA				
Туре			High- reso- lution mode	Stan- dard mode	High- speed mode	Super- high- speed mode	High- reso- lution mode	Stan- dard mode	High- speed mode	Super- high- speed mode	
		E32-T11R/E32-T12R/E32-T15XR/ E32-TC200BR(B4R)	700	530	350	140	450	350	230	140	
	Flexible (new	E32-T14LR/E32-T15YR/E32-T15ZR	270	210	130	50	170	130	85	50	
	standard)	E32-T21R/E32-T22R/E32-T222R/ E32-T25XR/E32-TC200FR(F4R)	160	130	75	30	100	75	50	30	
		E32-T24R/E32-T25YR/E32-T25ZR	60	50	25	10	35	27	18	10	
		E32-TC200/E32-T12/E32-T15X/ E32-TC200B(B4)	1,000	760	500	200	650	500	330	200	
Standard		E32-T14L/E32-T15Y/E32-T15Z	600	460	300	120	390	300	200	120	
models	Standard	E32-TC200A	900	680	450	180	580	450	300	180	
		E32-TC200E/E32-T22/E32-T222/ E32-T25X/E32-TC200F(F4)	270	220	125	50	170	130	85	50	
		E32-T24/E32-T25Y/E32-T25Z	160	130	75	30	100	70	45	30	
	Break-	E32-T11/E32-T12B/E32-T15XB	900	680	450	180	580	450	300	180	
	resistant	E32-T21/E32-T221B/E32-T22B	240	200	110	45 35	150	110	70	45 35	
	Fluorine coating	E32-T25XB E32-T11U	180 900	150 680	85 450	35 180	125 580	95 450	60 300	35 180	
	locating	E32-T17L	20,000*1	20,000*1	10,000	4,000	13,000	10,000	6,500	4,000	
		E32-TC200 + E39-F1	4,000*2	4,000*2	2,600	1,500	4,000	3,700	2,400	1,500	
		E32-T11R + E39-F1	4,000*2	3,700	2,400	970	3,100	2,400	1,600	970	
	Long- distance, high power	E32-T11 + E39-F1	4,000*2	3,600	2,300	930	3,000	2,300	1,500	930	
		E32-T14	4,000*2	3,400	2,250	900	2,900	2,200	1,450	900	
		E32-T11L/E32-T12L	1,700	1,330	870	350	1,100	870	580	350	
		E32-T11L + E39-F2	910	800	500	180	600	520	340	180	
		E32-T11R + E39-F2	520	400	250	100	330	260	170	100	
		E32-T11 + E39-F2	820	660	430	160	530	430	280	160	
		E32-T21L/E32-T22L	540	440	250	100	340	260	170	100	
	Ultracom-	E32-T223R	160	130	75	30	110	85	55	30	
Special-	pact,	E32-T33-S5	53	44	25	10	35	28	18	10	
beam models	ultrafine sleeve	E32-T333-S5	12	10	6	4	8	6	5	4	
models	SICCVC	E32-T334-S5	6	5	3	2	4	3	2	2	
	Fine beam	E32-T22S	2,500	1,900	1,250	500	1,600	1,250	830	500	
		E32-T24S	1,750	1,300	870	350	1,100	870	580	350	
		E32-T16PR	1,100	840	560	220	730	560	370	220	
		E32-T16P	1,500	1,100	750	300	970	750	500	300	
		E32-T16JR	980	750	480	190	600	480	320	190	
	Area sensing	E32-T16J	1,300	1,000	650	260	800	650	430	260	
	Area sensing	E32-T16WR	1,700	1,300	850	340	1,100	860	570	340	
		E32-T16W	2,300	1,800	1,150	450	1,400	1,100	730	450	
		E32-T16	3,700	2,800	1,850	740	2,400	1,800	1,200	740	
		E32-M21	750	610	350	140	470	360	240	140	

*1. The optical fiber for the E32-T17L is 10 m long on each side, so the value is 20,000 mm
*2. The optical fiber is 2 m long on each side, so the sensing distance is 4,000 mm.

		Model		E3X-D	A□-S		E3X-MDA				
Туре			High- reso- lution mode	Stan- dard mode	High- speed mode	Super- high- speed mode	High- reso- lution mode	Stan- dard mode	High- speed mode	Super- high- speed mode	
		E32-T51	1,000	760	500	200	650	500	330	200	
		E32-T54	300	230	150	60	190	150	100	60	
	llest	E32-T81R-S	360	280	180	70	230	180	120	70	
	Heat- resistant	E32-T61-S + E39-F2	600	450	300	120	390	300	200	120	
		E32-T61-S + E39-F1	4,000	3,400	2,200	900	3,000	2,200	1,450	900	
		E32-T84S-S	1,750	1,300	870	350	1,100	870	570	350	
		E32-T61-S	600	450	300	120	390	300	200	120	
Environ-		E32-T11F	2,500	2,000	1,300	520	1,600	1,300	850	520	
ment resistant	Ohamiaal	E32-T12F	4,000*	3,000	2,000	800	2,600	2,000	1,300	800	
models	Chemical resistant	E32-T14F	500	400	250	100	320	250	160	100	
	resistant	E32-T51F	1,800	1,400	900	350	1,190	920	600	350	
		E32-T81F-S	920	700	460	190	600	460	300	190	
		E32-T51V	260	200	130	50	170	130	85	50	
		E32-T51V + E39-F1V	1,350	1,000	680	260	850	650	430	260	
	Vacuum resistant	E32-T54V	210	130	100	35	110	85	55	35	
	resistant	E32-T54V + E39-F1V	660	500	330	180	420	320	210	180	
		E32-T84SV	630	480	320	130	410	310	200	130	

* The optical fiber for the E32-T12F is 2 m long on each side, so the sensing distance is 4,000 mm.

Reflective Models

(Unit: mm)

Model				E3X-D	DA⊡-S		E3X-MDA				
Туре	Туре			Stan- dard mode	High- speed mode	Super- high- speed mode	High- reso- lution mode	Stan- dard mode	High- speed mode	Super- high- speed mode	
		E32-D11R/E32-D12R/E32-D15XR/ E32-DC200BR(B4R)	300	170	120	50	170	120	80	50	
		E32-D14LR	80	45	30	14	45	33	22	14	
	Flexible (new stan-	E32-D15YR/E32-D15ZR	70	40	26	12	40	29	19	12	
	dard)	E32-D211R/E32-D21R/E32-D22R/ E32-D25XR/E32-DC200FR(F4R)	50	30	20	8	30	22	14	8	
		E32-D24R	26	15	10	4	15	10	6	4	
		E32-D25YR/E32-D25ZR	14	8	5	2	8	5	3.3	2	
	Standard	E32-DC200/E32-D15X/ E32-DC200B(B4)	500	300	200	90	300	210	130	90	
- · · ·		E32-D12	400	230	160	70	230	160	100	70	
Standard models		E32-D14L	200	110	80	36	110	80	50	36	
models		E32-D15Y/E32-D15Z	170	100	65	30	100	70	45	30	
		E32-D211/E32-DC200E/E32-D22/ E32-D25X/E32-DC200F(F4)	130	80	50	22	80	55	35	22	
		E32-D24	50	30	20	8	30	22	14	8	
		E32-D25Y/E32-D25Z	35	20	12	6	20	14	9	6	
		E32-D11/E32-D15XB	300	170	120	50	170	125	80	50	
	Break-	E32-D21B/E32-D221B	110	70	45	20	70	50	30	20	
	resistant	E32-D21/E32-D22B	50	30	20	8	30	22	14	8	
		E32-D25XB	85	50	30	15	50	35	23	15	
	Fluorine coating	E32-D11U	300	170	120	50	170	125	80	50	

		Model		E3X-D	DA⊡-S		E3X-MDA					
Туре			High- reso- lution mode	Stan- dard mode	High- speed mode	Super- high- speed mode	High- reso- lution mode	Stan- dard mode	High- speed mode	Super- high- speed mode		
		E32-D16	40 to 1,000	40 to 700	40 to 450	40 to 240	40 to 600	40 to 490	40 to 300	40 to 240		
	Long distance, high power	E32-D11L	650	400	260	110	400	270	180	110		
		E32-D21L/E32-D22L	210	130	80	35	130	85	55	35		
	Ultracom- pact, ultrafine	E32-D33	25	16	10	4	16	10	6	4		
	sleeve	E32-D331	5	3	2	0.8	3	2	1.3	0.8		
		E32-CC200R	250	150	100	45	150	105	65	45		
	Coaxial/small spot	E32-CC200	500	300	200	90	300	210	140	90		
		E32-D32L	250	150	100	45	150	100	65	45		
Special-		E32-C31/E32-D32	120	75	50	22	75	50	30	22		
beam models		E32-C42 + E39-F3A	Spot diameter variable in the range 0.1 to 0.6 mm at distances in the range 6 to 15 mm.									
		E32-D32 + E39-F3A	Spot diameter variable in the range 0.5 to 1mm at distances in the range 6 to 15 mm.									
		E32-C41 + E39-F3A-5	0.1-mm dia. spot at a distance of 7 mm.									
		E32-C31 + E39-F3A-5 0.5-mm dia. spot at a distance of 7 mm.										
		E32-C41 + E39-F3B	0.2-mm dia. spot at a distance of 17 mm. 0.5-mm dia. spot at a distance of 17 mm.									
		E32-C31 + E39-F3B E32-C31 + E39-F3C	Spot		of 4 mm r					0 mm		
	Area sensing	E32-D36P1	250	150	100	45	150 stances	100 100	9e 0 10 2 65	45		
	Retroireflec-	E32-R21 + E39-R3 (provided)	200	100	100	10 to		100	00			
	tive	E32-R16 + E39-R1 (provided)				150 to	1,500					
		E32-L25/E32-L25A				3.	3					
	0	E32-L24S				0 t	o 4					
	Convergent- reflective	E32-L24L				2 to 6 (c	,					
		E32-L25L			5		enter 7.2)				
		E32-L86				4 to						
	Heat	E32-D51 E32-D81R-S	400	230	160	72	230	165	110	72		
Environ-	Heat- resistant	E32-D81R-S	150	90	60	27	90	63	40	27		
ment-		E32-D73-S	100	60	40	18	60	40	25	18		
resistant models	Chemical-	E32-D12F	160	95	65	30	95	70	45	30		
	resistant	E32-D14F	70	40	30	10	40	28	18	10		

Application-specific Models									(Ur	nit: mm)		
	Model				DA⊡-S		E3X-MDA					
Туре			High- reso- lution mode	Stan- dard mode	High- speed mode	Super- high- speed mode	High- reso- lution mode	Stan- dard mode	High- speed mode	Super- high- speed mode		
	Label	E32-G14	10									
	detection	E32-T14	4,000*	3,400	2,250	900	2,900	2,200	1,450	900		
		E32-L25T	Applicat mm and	ole tube: a recom	Transpar mended	ent tube v wall thick	vith a dia ness of 1	meter in t mm	he range	8 to 10		
		E32-D36T	Applicat	ole tube:	Transpar	ent tube (no restric	tion on d	iameter)			
	Liquid-level detection	E32-A01				ent tube w thickness		neter of 3	.2, 6.4, or	9.5 mm		
		E32-A02	Applicable tube: Transparent tube with a diameter in the range 6 to mm and a recommended wall thickness of 1 mm							6 to 13		
		E32-D82F1(F2)	Liquid-contact model									
		E32-L16-N	0 to 15 0 to 12			0 to 15			0 to 12			
Applica- tion-	Glass- substrate	E32-A08		10 to 20			10 to 20					
specific models	alignment	E32-A07E1(E2)		15 to 25			15 to 25					
		E32-L66	5 to	18	5 to 16		5 to	18	5 to 14			
	Glass- substrate	E32-A09/E32-A09H		15 to 38				15 to 38				
	Mapping	E32-A09H2		20 to 30				20 to 30				
		E32-A03/E32-A03-1	1,150	890	600	250	750	580	380	250		
	Wafer mapping	E32-T24S	1,750	1,300	870	350	1,100	870	580	350		
		E32-A04/E32-A04-1	460	340	225	100	300	220	145	100		
	Soda glass with reflection	E32-L64		1 to 5				1 to 5	2 to 4			
	factor If 7%	E32-A10	0 t	08	0 to 6	0 to 4	0 to 8	0 to 6	0 t	o 4		


* The optical fiber for the E32-T14 is 2 m long on each side, so the sensing distance is 4,000 mm.

Green, Blue, and Infrared Light Sources (Unit: mm										nit: mm)
		Model	E3X-DAG -S/DAB -S				E3X-DAH□-S			
Туре				Stan- dard mode	High- speed mode	Super- high- speed mode	High- reso- lution mode	Stan- dard mode	High- speed mode	Super- high- speed mode
		E32-T11R/E32-T12R/E32-T15XR/ E32-TC200BR(B4R)	65	50	35	30	280	190	130	55
Through-	Standard	E32-T14LR/E32-T15YR/E32-T15ZR	25	20	22	12	100	75	80	21
beam models	Standard	E32-TC200/E32-T12/E32-T15X/ E32-TC200B(B4)	100	75	50	45	400	280	180	80
		E32-T14L/E32-T15Y/E32-T15Z	50	40	30	25	240	160	110	45
	Special beam	E32-T11L/E32-T12L	150	120	85	75	700	490	320	140
	Standard	E32-D11R/E32-D12R/E32-D15XR/ E32-DC200BR(B4R)	17	14	10	8	120	90	60	21
		E32-D14LR	4.4	3.5	2.5	2.2	32	24	16	5.5
		E32-D15YR/E32-D15ZR	4.2	3.3	2.2	2.1	28	20	13	5
		E32-DC200/E32-D15X/ E32-DC200B(B4)	32	25	16	16	200	150	100	35
Reflective		E32-D14L	11	9	6	5.5	80	60	40	14
models		E32-D15Y/E32-D15Z	10	8	5.5	5	65	50	33	11
		E32-D11L	44	35	22	22	260	190	130	45
		E32-CC200R	15	12	8	7.5	100	75	50	17
	Special beam	E32-CC200	32	25	16	16	200	150	100	35
		E32-D32L	15	12	8	7.5	100	75	50	17
		E32-C31/E32-D32	7.5	6	4	3.5	50	37	25	8.5
Applica- tion-	Label	E32-T14	320	260	220	160	1,800	1,200	820	360
specific models	detection	E32-G14		1	0		10			
		Refer to E32 Series for	details o	n Fiber l	Jnits.					

Output Circuit Diagrams


NPN Output

Model	Operation mode	Timing charts	Operation selector	Output circuit
E3X-DA11-S E3X-DA6-S E3X-DAG11-S E3X-DAG6-S	Light-ON	No incident light No incident light Operation (orange) OFF Output ON transistor OFF Load (relay) Operate (Between brown and black leads)	LIGHT ON (L-ON)	Display Operation indicator Display (orange) Brown tuning Indicator Brown Indicator Black Load Indicator Control output 12 to
E3X-DAB11-S E3X-DAB6-S E3X-DA11SE-S E3X-DA6SE-S	Dark-ON	Incident light	DARK ON (D-ON)	Blue Blue
E3X-DA11TW-S E3X-DA6TW-S E3X-MDA11	Light-ON	CH1/ Incident light CH2 No incident light Operation ON indicator OFF (orange) ON Output transistor OFF Load (relay) Reset (Between brown and black leads)	LIGHT ON (L-ON)	Display Operation indicator Operation indicator ch 1 Competence of the second
E3X-MDA6 E3X-DA11AT-S E3X-DA6AT-S	-S CH1/ Incident light		Sensor CO CO CO CO CO CO CO CO CO CO	
E3X-DA11RM-S E3X-DA6RM-S	Light-ON	Incident light No incident light Operation ON (orange) OFF Output ON transistor OFF Load Operate (relay) Reset (Between brown and black leads)	LIGHT ON (L-ON)	Operation indicator Display tuning indicator indicator photo- (orange) Photo- (orange) Photo- (orange) Complexity Photo- (orange) Complexity Comple
	Dark-ON	Operation OFF indicator OFF OFF ON Output transistor Operate Load (relay) (Between brown and black leads)	DARK ON (D-ON)	Blue
E3X-DA11AN-S	Light-ON	Incident light No incident light Operation ON (orange) OFF Uage OFF Load Operate (relay) Reset (Between brown and black leads)	LIGHT ON (L-ON)	Display Power Control output Control output
	Dark-ON	Incident light No incident light Operation ON (orange) OFF Uad Operate (relay) Reset (Between brown and black leads)	DARK ON (D-ON)	Constraint Sensor Main Constraint Constraint Constra
DA TW-S are LIGHT ON: ON channels 1 and DARK ON: OFI channels 1 and	as follows: when the inciden 2. when the inciden 2.	s settings are used with the E3 t level is between the threshold nt level is between the threshol Settings (T: Set Time)	ds for Cl Ids for Cl	3. Control Output (AND, OR, Sync) and Timing Chart for Timer Settings (T: Set Time) H1 OFF CH1 OFF CH2 ON OFF
ON delay	OFF	delay One-shot	(A	ND) OFF (AND) OF
Incident light No incident light L-ON OFF D-ON OFF	L-ON OF D-ON OF	→T+→ D-ON OF OF		UT ON OFF delay ON OFF OFF delay ON OFF UT ON T ON OFF UT ON OFF (AND) OFF



Note: The ON/OFF regions when areas settings are used with the E3X-DA TW-S are as follows: LIGHT ON: ON when the incident level is between the thresholds for channels 1 and 2. DARK ON: OFF when the incident level is between the thresholds for channels 1 and 2.

Nomenclature



Safety Precautions

Refer to Warranty and Limitations of Liability.

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.

Precautions for Correct Use

Do not use the product in atmospheres or environments that exceed product ratings.

Amplifier Unit • Designing

Operation after Turning Power ON


The Sensor is ready to detect within 200 ms after the power supply is turned ON. If the Sensor and load are connected to separate power supplies, be sure to turn ON the Sensor first.

Mounting


Connecting and Disconnecting Connectors

Mounting Connectors

1. Insert the Master or Slave Connector into the Amplifier Unit until it clicks into place.



2. Attach the protector seals (provided as accessories) to the sides of master and slave connectors that are not connected.




Note: Attach the seals to the sides with grooves.

E3X-DA TW-S E3X-DA AT-S E3X-MDA Sub-Display (Green) Threshold, function settings Operation Kevs Main Display (Red) Incident level, funct Function setting operations Õ UP Lock lever Locks the fiber. MODE O Channel Selecto Use to switch bet 1 and 2. Operation indicator for Operation indicator for Mode Selector Use to select SET or RUN mode channel 1 (orange) ON when output is ON. channel 2 (orange) ON when output is ON OFF when output is OFF OFF when output is OFF.

Removing Connectors


- 1. Slide the slave Amplifier Unit(s) for which the Connector is to be removed away from the rest of the group.
- After the Amplifier Unit(s) has been separated, press down on the lever on the Connector and remove it. (Do not attempt to remove Connectors without separating them from other Amplifier Units first.)




Adding and Removing Amplifier Units

Adding Amplifier Units

1. Mount the Amplifier Units one at a time onto the DIN track.



2. Slide the Amplifier Units together, line up the clips, and press the Amplifier Units together until they click into place.




Removing Amplifier Units

Slide Amplifier Units away from each other, and remove from the DIN track one at a time. (Do not attempt to remove Amplifier Units from the DIN track without separating them first.)

- Note: 1. The specifications for ambient temperature will vary according to the number of Amplifier Units used together. For details, refer to *Ratings and Specifications*.
 - 2. Always turn OFF the power supply before joining or separating Amplifier Units.


Mounting the End Plate (PFP-M)

An End Plate should be used if there is a possibility of the Amplifier Unit moving, e.g., due to vibration. If a Mobile Console is going to be mounted, connect the End Plate in the direction shown in the following diagram.



Mounting the Mobile Console Head

Leave a gap of at least 20 mm between the nearest Amplifier Unit and the Mobile Console head.




Fiber Connection

The E3X Amplifier Unit has a lock button for easy connection of the Fiber Unit. Connect or disconnect the fibers using the following procedures:


1. Connection

Open the protective cover, insert the fibers according to the fiber insertion marks on the side of the Amplifier Unit, and lower the lock lever.




Note: If one of the fibers from the Fiber Unit has a white line, such as with a Coaxial Sensor, that fiber is for the Emitter. Insert it into the Emitter section. Refer to Dimensions for the Fiber Unit to see if there is an Emitter fiber.

Fibers with E39-F9 Attachment




Fibers That Cannot Be Free-Cut (with Sleeves)



2. Disconnecting Fibers

Remove the protective cover and raise the lock lever to pull out the fibers.



Note: 1. To maintain the fiber properties, confirm that the lock is released before removing the fibers.

 Be sure to lock or unlock the lock button within an ambient temperature range between -10°C and 40°C.

Adjusting

Mutual Interference Protection Function

There may be some instability in the digital display values due to light from other sensors. If this occurs, decrease the sensitivity (i.e., decrease the power or increase the threshold) to perform stable detection.

EEPROM Writing Error

If the data is not written to the EEPROM correctly due to a power failure or static-electric noise, initialize the settings with the keys on the Amplifier Unit. ERR/EEP will flash on the display when a writing error has occurred.

Optical Communications

Several Amplifier Units can be slid together and used in groups. Do not, however, slide the Amplifier Units or attempt to remove any of the Amplifier Units during operation.

Others

Protective Cover

Always keep the protective cover in place when using the Amplifier Unit.


Mobile Console


Use the E3X-MC11-SV2 Mobile Console for the E3X-DA-S-series Amplifier Units.

Dimensions


(Unit: mm) Tolerance class IT16 applies to dimensions in this data sheet unless otherwise specified.


Amplifier Units





Amplifier Unit Connectors





Read and Understand This Catalog

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranty and Limitations of Liability

WARRANTY

OMRON's exclusive warranty is that the products are free from defects in materials and workmanship for a period of one year (or other period if specified) from date of sale by OMRON.

OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, REGARDING NON-INFRINGEMENT, MERCHANTABILITY, OR FITNESS FOR PARTICULAR PURPOSE OF THE PRODUCTS. ANY BUYER OR USER ACKNOWLEDGES THAT THE BUYER OR USER ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. OMRON DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED.

LIMITATIONS OF LIABILITY

OMRON SHALL NOT BE RESPONSIBLE FOR SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED ON CONTRACT, WARRANTY, NEGLIGENCE, OR STRICT LIABILITY.

In no event shall the responsibility of OMRON for any act exceed the individual price of the product on which liability is asserted.

IN NO EVENT SHALL OMRON BE RESPONSIBLE FOR WARRANTY, REPAIR, OR OTHER CLAIMS REGARDING THE PRODUCTS UNLESS OMRON'S ANALYSIS CONFIRMS THAT THE PRODUCTS WERE PROPERLY HANDLED, STORED, INSTALLED, AND MAINTAINED AND NOT SUBJECT TO CONTAMINATION, ABUSE, MISUSE, OR INAPPROPRIATE MODIFICATION OR REPAIR.

Application Considerations

SUITABILITY FOR USE

OMRON shall not be responsible for conformity with any standards, codes, or regulations that apply to the combination of products in the customer's application or use of the products.

At the customer's request, OMRON will provide applicable third party certification documents identifying ratings and limitations of use that apply to the products. This information by itself is not sufficient for a complete determination of the suitability of the products in combination with the end product, machine, system, or other application or use.

The following are some examples of applications for which particular attention must be given. This is not intended to be an exhaustive list of all possible uses of the products, nor is it intended to imply that the uses listed may be suitable for the products:

- · Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this catalog.
- Nuclear energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
- · Systems, machines, and equipment that could present a risk to life or property.

Please know and observe all prohibitions of use applicable to the products.

NEVER USE THE PRODUCTS FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCTS ARE PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

PROGRAMMABLE PRODUCTS

OMRON shall not be responsible for the user's programming of a programmable product, or any consequence thereof.

Disclaimers

CHANGE IN SPECIFICATIONS

Product specifications and accessories may be changed at any time based on improvements and other reasons.

It is our practice to change model numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the products may be changed without any notice. When in doubt, special model numbers may be assigned to fix or establish key specifications for your application on your request. Please consult with your OMRON representative at any time to confirm actual specifications of purchased products.

DIMENSIONS AND WEIGHTS

Dimensions and weights are nominal and are not to be used for manufacturing purposes, even when tolerances are shown.

PERFORMANCE DATA

Performance data given in this catalog is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of OMRON's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to the OMRON Warranty and Limitations of Liability.

ERRORS AND OMISSIONS

The information in this document has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical, or proofreading errors, or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company

http://www.ia.omron.com/