


1					2					3					4				
COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE			COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE		
△										△									
△										△									
△										△									



NOTE 1 ROTATION EXAMPLES OF REF.NO. 1 AND 8 ARE SHOWN.
2 THE RECOMMENDED TORQUE OF REF.NO. 8: 2 TO 3N·m.
3 THE RECOMMENDED TORQUE OF REF.NO. 11: 0.3 TO 0.4N·m.

4	DIALYL PHTHALATE	(BLACK) UL94V-0	11	STEEL	NICKEL PLATING
3	DIALYL PHTHALATE	(BLACK) UL94V-0	10	BRASS	NICKEL PLATING
2	COPPER ALLOY	SILVER PLATING 2μm min	9	ZINC ALLOY	MATTE FINISH NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATING	8	ZINC ALLOY	MATTE FINISH NICKEL PLATING
			7	BRASS	NICKEL PLATING
			6	BERYLLIUM COPPER	NICKEL PLATING
			5	BRASS	MATTE FINISH NICKEL PLATING

CODE NO. (OLD) CL		DRAWN T. Suguchi 21.06.03	DESIGNED T. Suguchi 21.06.03	CHECKED H. Kobayashi 21.06.07	APPROVED T. Konatsu 21.06.09	RELEASED
DRAWING NO. EDC4-112322-76-00		PART NO. RM12BPE-5PH(76)				
SCALE 2 : 1		CODE NO. CL109-0420-1-76				
UNITS mm		1/1				