


## General Features



### Properties of the TOCON\_ABC9

- Broadband pre-amplified SiC UV detector in TO5 housing with attenuator
- 700 mW/cm<sup>2</sup> peak radiation results a voltage of approx. 2 V
- RoHS compliant
- Applications: curing lamp control


### The TOCON pre-amplified UV photodetectors

The TOCON devices are using modern hybride technology to cancel unwanted signal disturbances caused by moisture or electromagnetic radiation. The stable 0...5V output voltage can be directly connected to a SPC controller or a voltage multimeter. No external amplifier is needed.


## Specifications

Parameter	Symbol	Value	Unit
<b>Maximum Ratings</b>			
Operating Temperature Range	$T_{opt}$	-25 ... +85	°C
Storage Temperature Range	$T_{stor}$	-40 ... +100	°C
Soldering Temperature (5s)	$T_{sold}$	300	°C
<b>General Characteristics (T=25° C, V<sub>supply</sub>=+5 V)</b>			
Supply voltage	$V_{supply}$	2,5 ... 5,0	V
Saturation voltage	$V_{sat}$	$V_{supply}$	V
Dark offset voltage	$V_{offset}$	50	µV
Temperature coefficient	$T_C$	<+0,3	%/K
Current consumption	$I$	0,8	mA
Bandwidth (-3 dB)	$\theta$	15	Hz
Risetime (63%) (other risetimes on demand)	$t_{rise}$	10	ms
<b>Spectral Characteristics (T=25° C, V<sub>supply</sub>=+5 V)</b>			
Sensitivity at peak	$S_{max}$	2,8	mV/mW/cm <sup>2</sup>
Wavelength of max. spectral sens.	$\lambda_{max}$	300	nm
Sensitivity range (S=0,1*S <sub>max</sub> )	-	210 ... 380	nm
Visible blindness (S <sub>max</sub> / S <sub>&gt;405nm</sub> )	VB	>10 <sup>10</sup>	-


## Spectral Response



## Drawing



## Field of View



## TOCON Product Portfolio

Selection of TOCONs with UV broadband sensitivity:

Option	Approx. min irradiance	Approx. max irradiance (V <sub>supply</sub> = 5 V)
TOCON_ABC1	1,8 pW/cm <sup>2</sup>	18 nW/cm <sup>2</sup>
TOCON_ABC2	18 pW/cm <sup>2</sup>	180 nW/cm <sup>2</sup>
TOCON_ABC3	180 pW/cm <sup>2</sup>	1,8 μW/cm <sup>2</sup>
TOCON_ABC4	1,8 nW/cm <sup>2</sup>	18 μW/cm <sup>2</sup>
TOCON_ABC5	18 nW/cm <sup>2</sup>	180 μW/cm <sup>2</sup>
TOCON_ABC6	180 nW/cm <sup>2</sup>	1,8 mW/cm <sup>2</sup>
TOCON_ABC7	1,8 μW/cm <sup>2</sup>	18 mW/cm <sup>2</sup>
TOCON_ABC8	18 μW/cm <sup>2</sup>	180 mW/cm <sup>2</sup>
<b>TOCON_ABC9</b>	<b>180 μW/cm<sup>2</sup></b>	<b>1,8 W/cm<sup>2</sup> this device</b>
TOCON_ABC10	1,8 mW/cm <sup>2</sup>	18 W/cm <sup>2</sup>

TOCONs are also available with other spectral sensitivity (UVA, UVB, UV-Index, UVC).

## Upgrades

### TOCON housings for easy mounting of the TOCON\_ABC9

#### TOCON\_housing



#### Advantages of the TOCON\_housing

- Easy to mount and connect
- Robust stainless steel M12x1 thread body, length 32 mm
- Integrated sensor connector (Binder 5-Pin plug)
- Comes with 2 m connector cable

#### TOCON\_PTFE\_housing



#### Advantages of the TOCON\_PTFE\_housing

- Easy to mount and connect, cleanable
- Dirt-repellant, water proof at wet side (IP 68)
- Teflon (PTFE) M12x1 thread body, length 31 mm
- Wide field of view
- Integrated sensor connector (Binder 5-Pin plug)
- Comes with 2 m connector cable

*The PTFE housing reduces the signal output by 95 %.*

### Sensor Monitor 5.0 for monitoring, datalogging and process control with TOCON\_ABC9



The **Sensor Monitor 5.0** series are measurement and control modules for monitoring and automation of irradiation processes. They display radiation, dose and state information.

A selection of devices with one or two channels, optional USB & RS232 data output and computer software is offered.

### UVMICROLOG for datalogging and permanent measurements with TOCON\_ABC9



The **UVMICROLOG** is designed for logging of ultraviolet radiation, temperature, pressure and acceleration.

Sophisticated microcontroller technology and low noise SiC TOCON based UV detectors allow up to 3 months of permanent measurement and logging without battery charging. The unit can be mounted with a belt or screws.