

# PRODUCT Data Sheet

## CAIG Rosin Soldering Flux For electrical and electronic soldering applications

### 1. Part No.:

RSF-R80

### 2. Container Size:

RSF-R80-8G	syringe	8 g
RSF-R80-2	jar	56 g
RSF-R80-8	jar	226 g
RSF-R80-40	pail	18.1 Kg



### 3. Product Description:

RSF Rosin Flux is a mildly-activated rosin flux that is considerably more active than water-white rosin. Although its activity closely approaches that of fully activated rosins, it still conforms to all of the requirements of Type RMA (Rosin Core, Mildly Activated) of Federal Specification QQ-S-571. The RSF paste flux meets DOD-STD-2000 & also the IPC-J-004 standard for type ROL0, the lowest residue corrosivity category. Thermal stability enabling excellent wetting and reduced carbonization at soldering temperatures. RSF-R80 Rosin Flux is MADE IN USA.

### 4. Application:

The active ingredients in RSF-R80 are non-ionic and non-conductive even in the presence of moisture. Like rosin, it becomes active only at elevated temperatures, reverting to an inactive state at room temperature. It is recommended for all applications where post-soldering cleaning is not feasible, and the residue must be highly insulating.

### 5. Specifications:

Softening Point	160oF (71oC)
Rosin Grade	WW per Fed. Spec. LLL-R-626
Acid No. (of Rosin)	150
Water Extract Resistivity	110,000 ohm-cm
Effect on Copper Mirror	None
Fungus Resistance	Per MIL-E-5272
Nonflammable, noncorrosive.	



Home of the DeoxIT® family of  
Environmentally-Safer Contact Cleaners and  
Connector Enhancing Treatments  
Made in USA



Audio/Video



Computers



Automotive



Communications



Marine



Electrical



Energy



Photography



Security



Medical



Avionics

### 6. Formulation:

50-60%	WW Gum Rosin
15-25%	Dymerex Rosin
15-25%	Diethylene Glycol Dibutyl Ether

### 7. Residue Removal:

In applications requiring cleaning, RSF-R80 flux residues can be readily removed using an aqueous saponifier cleaning process. Can be removed by wiping with a cloth or with cleaning solvent (Radio Shack® Precision Electronic Cleaner #644345 or DeoxIT® Flux WASH #DFW-V710).

### 8. Safety:

RSF-R80 is not considered toxic; however, its use in typical soldering processes will generate a small amount of decomposition and reaction product fumes. These fumes must be adequately exhausted for operator safety and comfort.

### 9. Shipping and Additional Information:

Hazardous: No, Not regulated

### 10. Other Information:

RoHS Compliant:	YES
VOC Compliant:	YES
<b>MSDS Link, RSF-R80</b>	<a href="http://store.caig.com/s.nl/sc.18/category.233/f">http://store.caig.com/s.nl/sc.18/category.233/f</a>
Product Sheet:	<a href="http://store.caig.com/s.nl/sc.2/category.2341/f">http://store.caig.com/s.nl/sc.2/category.2341/f</a>




### 11. MANUFACTURER DISCLAIMER:

To the best of our knowledge, the information contained herein is accurate. However, neither CAIG Laboratories, Inc., or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. All materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist. All service performed on internal parts and equipment should be provided by qualified technicians.



**CAIG Laboratories, Inc.**  
 12200 Thatcher Court, Poway, CA 92064 U.S.A.  
**P:** 858/486-8388 | **E:** info@caig.com  
**WEB:** www.caig.com | www.deoxit.com





Audio/Video



Computers



Automotive



Communications



Marine



Electrical



Energy



Photography



Security



Medical



Avionics

## 12. Contact Information:



**Website:** [www.caig.com](http://www.caig.com)  
[www.deoxit.com](http://www.deoxit.com)

**General email:** [info@caig.com](mailto:info@caig.com)

**Technical email:** [tech@caig.com](mailto:tech@caig.com)

### North America (Headquarters):

**CAIG Laboratories, Inc.**

12200 Thatcher Court  
Poway, CA 92064 USA

Tel: (858) 486-8388

Fax: (858) 486-8398

### Distributors (Domestic & International):

<http://store.caig.com/s.nl/sc.15/f>



**CAIG Laboratories, Inc.**

12200 Thatcher Court, Poway, CA 92064 U.S.A.

**P:** 858/486-8388 | **E:** [info@caig.com](mailto:info@caig.com)

**WEB:** [www.caig.com](http://www.caig.com) | [www.deoxit.com](http://www.deoxit.com)

