

Vermason		Product Information No: PIS 037		
	Page 1 of 1	Issue No 6	Date: July 2003	Approved by

STATIC DISSIPATIVE SERVICE KIT

Code J726*B (blue) or J726*R (red)

FEC Code 877682

Purpose of Field Service Kit

To create a temporary ESD Protected Area (EPA). An EPA is a working space where electrostatic discharge sensitive devices (ESDS) may be unpacked, handled and packed with the minimum risk of being damaged by static electricity.

Contents of kit

- Service mat, Code J727R or J727B. Size when open 590x545mm
- Straight ground cord, Code J6455
- Crocodile clip, Code J5118
- Wrist band, Code JA48Y
- Coiled cord, Code J4221Y
- Pouch, Code J728B
- Total weight of kit: 0.4kg

Instructions for use

- Remove kit from pouch
- Open mat and place on a flat stable surface with the stud facing upwards.
- Connect straight ground cord using snap fastener to the stud on the mat.
- Connect 4 mm plug of the straight ground cord to Earth or to an earthed terminal of the equipment. If necessary use the crocodile clip to do so.
- Put on wrist band. Ensure wrist band fits snugly. Separate instructions for use are supplied with band.
- Connect coiled cord by snap fastener to wrist band.
- Plug the other end of coiled cord into straight cord. Alternatively, the coiled cord can be connected to Earth or the equipment Earth terminal, possibly using the crocodile clip.
- The EPA is now ready for use.

General Instructions

- Always replace kit in pouch after use.
- Do not clean mat with solvents. Use Vermason bench top cleaner or mild detergent and warm water.
- Pouches sewn into mat are suitable for holding components, PCBs and ESD compatible tools.
- If possible test the overall resistance to Earth of the personnel regularly. This can be effected by preparing the kit for use and measuring the resistance from the operator's finger tips to Earth. The resistance should be approximately 3 MΩ, but certainly be at least 0.75 but less than 35 MΩ.

General

- The surface resistivity of both sides of the mat is approximately $10^8 \Omega$ per square.

Please direct all inquiries to Technical Services & Development
on fax: +44 (0) 1462 670440 or e-mail: tsnd@vermason.co.uk
Vermason Limited, Birds Hill, Letchworth, Hertfordshire SG6 1HX UK
www.vermason.co.uk