

SPECIALTY CHEMICALS (Cont.)

Chem



Silicone Dielectric Compound

Soft, inert silicone grease with excellent dielectric properties. Usable over a wide range of temperatures. Its consistency is vaseline-like and it is clear translucent in color. It provides an excellent dielectric coating which excludes moisture and prevents high voltage arcing. Applicable to components in the high voltage section of TV receivers. Protects ignition systems in automobiles and boats, in addition to providing an outstanding corrosion resistant coating on exposed metal surfaces, such as TV antenna terminals as well as general rustproofing. This compound also makes an excellent lubricant for rubber or plastic.

- | |
|---|
| Part No. 10-8101 1 fl. oz. Tube
N.S.N. 6850-00-268-7963 |
| Part No. 10-8102 1 gal. Can |
| Part No. 10-568 1/3 fl. oz. Chem-O-Jector |



Belt & Drive Non-Slip

Prevents slippage in mechanical or electro-mechanical devices which are driven with cords, belts, pulleys and drives. Restores proper functions on belts and drive pulleys in turntables, record changers and tape recorders, especially where the rubber parts have hardened and/or become slick and cause slippage.

Part No. 10-8602 2 fl. oz. Bottle w/ Brush

ACCESSORIES



Part No. 19-780

Squeeze Bottle & Squeeze Riser

These reliable bottles accurately dispense solvents in the required amounts in the proper location. For use with GC Bulk Chemicals, wipes and brushes. Can be used safely with all GC chemicals. The squeeze riser professionally dispenses chemicals without using an aerosol.

- | |
|---|
| Part No. 19-780 4 oz. Squeeze Bottle |
| Part No. 19-781 4 oz. Squeeze Riser |



Part No. 19-781



GC Touch Dispenser

Stops waste. Dispense only as much fluid as needed for the job. Saves time and effort. No stopper or cap to remove. One-handed touch on the dish dispenses the required amount of fluid, leaving the other hand free. Prevents contamination. Liquid in bottle stays clean until used. Fluid pumped into dish doesn't drip back into bottle. Hinged lid protects dish when not in use. Use with all GC cleaner/degreaser and defluxing solvents. Not for use with iodine, acids or bases.

- | |
|---|
| Part No. 19-764 4 oz. Bottle with Pump |
| Part No. 19-766 6 oz. Bottle with Pump |
| Part No. 19-768 8 oz. Bottle with Pump |



1oz. Glass Bottle

GC glass bottle with plastic cap allows safe storage for when you want to work with smaller quantities of oils, contact cleaners, and other liquids.

Part No. 10-285 1 oz. Glass Bottle with Cap