

SERIES 67B Hall Effect Joystick

FEATURES

- Proportional output joystick, pushbutton, & momentary rotary select in one device
- · Shaft and panel seal to IP67
- Rugged and compact: 1.25 inch diameter
- · Long operational life
- RoHS compliant
- i²c output (see www.grayhill.com for User Manual)


APPLICATIONS

- Medical imaging X-ray, CT scanner, MRI patient tables
- Military vehicles display navigation
- · Handheld remote control devices
- · Material handling equipment and crane operations




Actual Size


DIMENSIONS in inches [millimeters]



DIMENSIONS in inches [millimeters]



BLOCK DIAGRAM & JOYSTICK OUTPUT WAVEFORM



SPECIFICATIONS

Electrical Ratings

Supply Voltage (VVD): $3.3V \pm .0.3V$ High Level Input Voltage (VIH, Min): 0.7^*VDD on SCL & SDA / $0.25^*VDD+0.8$ on Al Low Level Input Voltage (VIL, Max): 0.3^*VDD on SCL & SDA / 0.15^*VDD on Al Current Draw In Active Mode (IDDI): 3mA Maximum @ VDD = 3.3V (J & P options only) Current Draw In Sleep Mode (IDD2): 100uA Maximum @ VDD = 3.3V (J & P options only) Current Draw in Active Mode (IDD3): 4mA Maximum @ VDD = 3.3V (R option has active mode only)

Typical Operating Current: 4.0 mA at Vcc = 3.3V, T = 25°C

Maximum Operating Current: 7.0 mA over $3.0 \le Vcc \le 3.6V$, $-40^{\circ}C \le T \le 85^{\circ}C$ Maximum Current Sunk By Any I/O Pin: 25mA

Leakage Current: ±5 nA Typ., ±125 nA Max Low Level Output Voltage (VOL): 0.6V On INTn & SDA @ IOL = 6mA, @ VDD = 3.3V Measurement Frequency (Active Mode): 50 Samples/Sec

Response Time, Active Mode (T1): 20ms* Response Time, Sleep Mode (T2): 80ms* Output @ Maximum Joystick Deflection (XMax, YMax): 50 Units

Output With Joystick Shaft Released

(Center Position): (0,0)

Nominal Startup Time (TP, W): 300ms

Physical & Mechanical Ratings

Vibration: Random, Meets MIL-STD-810G,

Method 514.6, Procedure I

Mechanical Shock: Meets per MIL-STD 202, Method 213B Test Condition A

Transit Drop: Meets per MIL-ST-810G,

Method 516.6, Procedure II

Terminal Strength: 10 lbs. Minimum, Tested per MIL-STD-202, Method 211A

Push-Out Force: 60 lbs. Minimum Pull-Out Force: 60 lbs. Minimum

Shaft Impact: 0.5 lb. Weight dropped 20x from

height of 1m

Shaft Side-Load: 45 lbs. Minimum

Mounting Torque: 3-5 in-lbs recommended, 8

in-lbs. Maximum

Joystick Actuation Force: 300g Peak ± 25% Joystick Life: 1 million cycles minimum** Pushbutton Life: 1 million actuations, minimum

Rotational Life: 1 million turns, minimum in

each direction

Materials and Finishes

Housing: Thermoplastic Backplate: Thermoplastic Lockwashers: 304 Stainless Steel Hex Nuts: 303 Stainless Steel Shim Washers: 304 Stainless Steel Shaft: 303 Stainless Steel

Cable Assembly: 26 AWG Stranded Copper

Conductors

Connector Body: Thermoplastic Terminals: Phosphor Bronze O-Rings: Fluorosilicone

Sealing Boot: Silicone Rubber Molded over

Thermoplastic Insert

Environmental Ratings

Seal: IP67, Meets IEC 60529 (sealed version only)
Altitude: Tested per MIL-STD 202, Method 105C
Thermal Shock: Meets MIL-STD 202, Method 107G

Onor

Operating High Temperature: +85°C, Tested per

IEC 68-2-14, Test Na

Operating Low Temperature: -40°C, Tested per

IEC 68-2-14, Test Na

Storage High Temperature: +100°C, Tested per IEC 68-2-2, Method Ba

Storage Low Temperature: -55°C, Tested per

IEC 68-2-1, Method Aa

Humidity: Meets MIL-STD 202, Method 103B **Humidity, 85/85:** 500 hours tested per MIL-STD

202, Method 103B

Solar Radiation: Tested per MIL-STD 810G,

Method 505.5, Procedure II

Chemical Resistance: Meets ISO 16750-5 Dielectric: Meets MIL-STD 202G, Method 301 Insulation Resistance: Tested per MIL-STD

202G, Method 302

EMC Ratings

Radiated Immunity: Meets IEC 61000-4-3, 10

V/m,80 MHz-1000 MHz

Conducted Immunity: Meets IEC 61000-4-6,

10 V RMS, 150 KHz to 80 MHz

Radiated Emissions: Meets ANSI C63.4, Class B

Conducted Emissions: Meets EN 55022,

Class B **Electrostatic Discharge:** Meets IEC 61000-4-2.


8 kV contact/15 kV air discharge

Power Frequency Magnetic Field: Meets IEC

61000-4-8, 30 A/m

*Response time is the time from jovstick movement to when new X.Y position data is available.

**One cycle is defined as a complete revolution of the shaft around the fixed perimeter, or one actuation in each of the 4 main directions, with return to center between each actuation.



For prices and custom configurations, contact a local sales office, an authorized distributor, or Grayhill's sales department.



Grayhill, Inc • 561 Hillgrove Avenue • LaGrange, Illinois • 60525-5997 • USA Phone: 708-354-1040 • Fax: 708-354-2820 • www.grayhill.com