



9900-1201-23

Amber Power LED Screw thread design Lambertian radiation pattern



Typical Device Characteristics @ 350mA

95 lumens **Luminous Flux**

Dominant Wavelength 590 nm

Forward Voltage 2.30 V

Viewing Angle 130°

Product Features


- Solder-Free mechanical attachment for easy installation and replacement
- Annular contact arrangement eliminates need for radial alignment
- Excellent thermal coupling to lighting system
- Large LED chip allows high drive current
- Outstanding light output
- Wide viewing angle
- UV resistant cover lens
- RoHS Compliant

Form 9900-1201-23, Rev 7/12/06


Device Characteristics Forward Current = 350mA, Junction Temperature, T_J = 25°C **Typical Minimum** Maximum Luminous Flux (\phi v) 68 lm 95 lm Dominant Wavelength (λ_D) 583 nm 590 nm 597 nm Peak Wavelength (λ_P) 594 nm Spectral Half-Width ($\Delta \lambda^{1/2}$) 18 nm Viewing Angle (201/2) 130° Forward Voltage (V_F) 2.00 V 2.30 V 3.00 V Dynamic Resistance (R_D) 0.7 Ω Thermal Resistance ($R\Theta_{J-c}$) 10°C/W

| Absolute Maximum Ratings | |
|-----------------------------|-----------------|
| DC Forward Current | 750 mA |
| Peak Pulsed Forward Current | 1 A |
| Maximum Pulse Duty Cycle | 50% |
| Maximum Pulse Duration | 10 ms |
| Reverse Voltage | > 5 V |
| LED Junction Temperature | 125°C |
| Operating Temperature Range | -40°C to +85°C |
| Storage Temperature Range | -40°C to +100°C |

Mechanical Dimensions




Spatial Distribution Pattern




Spectral Power Distribution

Wavelength (nm)


Wavelength vs. Forward Current



Forward Voltage vs. Forward Current



Luminous Flux vs. Forward Current





A product of Weldon | 3656 Paragon Drive | Columbus, Ohio 43228 USA 800.989.2718 | 614.529.7230 | FAX 614.527.3547 | http://www.v-led.com

Weldon Technologies reserves the right to make changes at any time to product specifications without notice.